




# 42U SmartRack Standard-Depth Rack Enclosure Cabinet with doors, side panels & shock pallet shipping

# MODEL NUMBER: SR42UBSP1







# **Description**

42U SmartRack Enclosure ships mounted on a special pallet that features additional reinforcement and shock-absorbing material. The pallet's protective cushion safeguards the enclosure and the precision components it contains during re-shipping. Reinforced pallets and reusable packaging provide the flexibility to fully configure rack enclosures in a centralized location and safely re-ship them to remote sites, saving significant service costs. They also allow the freedom to custom-configure enclosures with network and server hardware along with UPS systems, PDUs, KVM switches and a variety of other devices prior to final installation.

SmartRack enclosures are designed for secure, high density server and networking applications in IT environments. Designed with provisions to integrate cooling, power distribution and cable management, SmartRack enclosures make ideal homes for mission-critical equipment. Vendor-neutral square hole/cage nut mounting for guaranteed compatibility with all EIA-310-D compliant 19" equipment. Enclosures ship fully assembled for rapid deployment and roll into place on heavy-duty casters. Toolless mounting slots allow quick installation of PDUs and vertical cable managers. Adjustable mounting rails include an easy-view depth index to eliminate time-consuming measurements. Lightweight modular doors and side panels provide safe, convenient service access. Integrated baying tabs facilitate combining enclosures in rows for standard data center baying applications. SmartRack enclosures hold up to 3500 lbs (1588 kgs) and support cooling, cable management, power distribution and monitoring features that keep critical servers and network equipment operating nonstop. Perforated doors permit massive front to rear airflow that exceeds servers manufacturer requirements. Enclosures are fully compatible with hot-aisle / cold-aisle data center configurations.

#### **Features**

- This special version of the 42U SmartRack Enclosure (SR42UB) ships mounted on a "shock pallet" that features additional reinforcement and shock-absorbing material for safe loading and re-shipping
- · Heavy-duty ramps (included) allow enclosure to be rolled on and off the pallet during configuration
- Shipping Capacity: shock-pallet supports up to 1250 pounds (566.9 kg) (281 pounds (127.5 kg)
   SmartRack Enclosure weight + up to 969 pounds (439.5 kg) of additional equipment), enabling safe loading and re-shipping
- Final Installation Capacity: SmartRack Enclosure supports up to 3500 pounds (1588 kg) of equipment stationary and 2250 pounds (1020.6 kg) rolling.
- Ships fully assembled for rapid deployment and roll into place on heavy-duty pre-installed casters.
- Front and rear sets of equipment mounting rails adjust in 1/4" increments. Adjustment is quick and convenient. The easy-view depth index ensures consistent rail placement without requiring timeconsuming measurements.

# **Highlights**

- Standard 42U SmartRack enclosure with additional shock pallet and loading ramps.
- 4 interior vertical posts with unthreaded square hole openings
- Standard 24" (600mm) width and 42" (1050mm) depth for optimizing floor space
- · Ships fully assembled
- Massive front to rear ventilation capacity
- 3500 lbs (1588 kgs) stationary / 2250 lbs (1020.6 kgs) rolling load capacity
- Locking, removable, reversible front and rear doors
- Locking, removable side panels keyed alike with doors
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

# **Package Includes**

- SR42UB Rack Enclosure
- (4) side panels
- (4) side panel locks
- (2) door & side panel keys
- (50) M6 screws
- (50) M6 washers
- (50) M6 cage nuts
- Owner's Manual





- Toolless accessory mounting rails (2 rails per enclosure) include slots for quick installation of compatible PDUs and vertical cable managers. Mounting slots are arranged in an industry-standard pattern compatible with a wide variety of accessories. Each rail can accommodate two vertical PDUs or cable managers side-by-side (four items per enclosure).
- Enclosure includes mounting hardware of 50 pieces of M6 cage nuts and 50 pieces of M6 screws.
- Textured powder coat finish for tough resistance to environmental concerns such as deployment in warehouses.
- Massive front to rear ventilation capacity. 65+% open space in door perforation pattern meets or exceeds server manufacturer requirements.
- Maximum usable internal depth of 37 inches/94 cm (front to rear rail).
- Weight ratings of 3500 pounds (1588 kg) stationary and 2250 pounds (1020.6 kg) rolling.
- Front door is locking, reversible and removable.
- Rear doors are locking and reversible. Split rear door design reduces clearance requirements for service entry allowing the enclosure to be placed closer to a wall.
- Locking removable side panels are 'half size' to make them smaller and lighter improving ease of
  installation and servicing. Two side panels per side (4 panels total). Side panels are keyed alike to the
  front and rear doors.
- Built in baying tabs allow enclosures to be combined securely in rows. Center-to-center width can be set at 600mm or 24" to match standard data center floor tiles.
- Casters are pre-installed and support a rolling load capacity of 2250 pounds (1020.6 kg), allowing the
  enclosures to be pre-configured and rolled to the final installation location. Casters are removable.
- Leveling feet extend to allow enclosure to be positioned on uneven floors. Levelers are removable.
- · Compact design allows the enclosure to roll through standard height commercial doorways.
- Convenient grounding system. All components are grounded to the enclosure frame which includes
  multiple connections for facility ground. Front and rear doors include quick-release ground wires.
- · Open bottom for cable access.
- Top panel has generous cable access holes. Panel can be removed toollessly in seconds without having to disconnect cables first.
- Included stabilizing brackets are used for shipment and can be reattached at the bottom of the
  enclosure frame on the inside or outside of the rack.
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard)
   Compliance
- Compatibility with airflow optimization accessories as well as cable management accessories.

# **Specifications**

OVERVIEW		
UPC Code	037332137401	
Device Compatibility	Patch Panel; Network Switch; UPS; Server	
Rack Type	Enclosure	
PHYSICAL		
Color	Black	
Rack Height	42U	
Rack Depth	Standard	
Factory Preset Rack Depth (in.)	27.75	
Factory Preset Rack Depth (cm)	70.5	





Factory Preset Rack Depth (mm)	705	
Maximum Device Depth (cm)	93.98	
Maximum Device Depth (in.)	37	
Maximum Device Depth (mm)	940	
Minimum Device Depth (cm)	10.16	
Minimum Device Depth (in.)	4	
Minimum Device Depth (mm)	102	
Shipping Dimensions (hwd / in.)	85.00 x 26.00 x 45.50	
Shipping Dimensions (hwd / cm)	215.90 x 66.04 x 115.57	
Shipping Weight (lbs.)	336.00	
Shipping Weight (kg)	152.41	
Unit Dimensions (hwd / in.)	78.500 x 23.630 x 43.000	
Unit Dimensions (hwd / cm)	199.39 x 60.02 x 109.22	
Unit Weight (lbs.)	286	
Unit Weight (kg)	129.73	
Weight Capacity - Rolling (kg)	1,021	
Weight Capacity - Rolling (lbs.)	2250	
Weight Capacity - Stationary (kg)	1,588	
Weight Capacity - Stationary (lbs.)	3500	
Number of Vertical Mounting Rails	4	
FEATURES & SPECIFICATIONS		
Grounding Details	Front and rear door frames	
Built-in Cable Management	Yes	
Extra Wide	No	
Pre-Installed Casters	Yes	
STANDARDS & COMPLIANCE		
Product Certifications	UL 60950-1	
Product Compliance	RoHS; CE (Europe)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	5-year limited warranty	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2025 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.