

Important Note

The SRCOOL2KWM is recommended for wall-mount rack enclosures with ventilated doors and/or side panels. Cooling air delivered to equipment is lessened in an open frame application. Condenser must be ducted.

AC Unit for Wall Mount Network Racks - 2,000 BTU (0.6 kW), 120V

MODEL NUMBER: SRCOOL2KWM



Self-contained 2,000 BTU wall-mount server rack cooling system filters, dehumidifies and cools air and directs it toward equipment stored in wall-mount rack enclosures and network closets with no access to facility air conditioning.

Description

The self-contained SRCOOL2KWM SmartRack® 120V Wall-Mount Rack Air Conditioner mounts to the top of your wall-mount rack enclosure and delivers 2,000 BTU of close-coupled cooling power to the equipment mounted within the cabinet. The space-saving, energy-efficient SRCOOL2KWM filters and dehumidifies air, then cools the air and directs it through the ventilated front door or side panel of the cabinet. This helps prevent shutdowns and other equipment failures caused by overheating.

Recommended for server rooms and other IT environments with limited floor space, the SRCOOL2KWM is more efficient than units that cool an entire room, because the magnetic air scoop attached to the front of the unit pushes the cool air directly toward your equipment. A built-in evaporator eliminates condensation, so no water collection tank or floor drain is required. No plumbing or special circuits are needed, so setup is quick and easy.

The 6-ft. (1.83 m) power cord with NEMA 5-15P plug connects to a standard 120V AC outlet. The SRCOOL2KWM restarts automatically after power failures. The user-friendly control panel lets you schedule unattended shutdowns and restarts, adjust the temperature and set other operating conditions. Adding the optional SRCOOLNET2LX module (sold separately) turns the SRCOOL2KWM into a managed network device via web browser, NMS or telnet. It allows you to monitor and adjust temperature and humidity remotely, access activity logs and receive alerts via email, SMS or SNMP.

Features

Compact and Efficient Cooling of Rack Equipment Mounts to most wall-mount rack enclosures with ventilated door or side panels. Close-coupled energy-saving cooling directed at equipment instead of whole room. Recommended for IT environments with limited floor space. 2,000 BTU (0.6 kW) of cooling capacity. Prevents equipment shutdowns, malfunctions and failures caused by overheating and temperature fluctuations. Eco-friendly R134A refrigerant meets environmental standards.

Convenient Operation Magnetic front scoop directs cool air through rack's ventilated door or side panel to cool overheated rack equipment. Magnetic door panel prevents warm air from entering cabinet. Restarts automatically after power failures. Intuitive push-button control panel features LCD display and diagnostic

Highlights

- Mounts to most wall-mount rack enclosures with ventilated door
- Provides 2,000 BTU (0.6 kW) of cooling capacity
- 6-ft. (1.83 m) power cord with NEMA 5-15P plug
- User-friendly control panel with LCD display and diagnostic LEDs
- Temperature control 63-86 degF
- Supports optional remote management via Ethernet

Package Includes

- SRCOOL2KWM SmartRack Wall-Mount Server Rack Cooling Unit - 2,000 BTU, 120V
- (2) Adjustable exhaust panels
- Exhaust duct adapter
- Directional output vent
- Exhaust duct
- Extra drainage plug
- Magnetic door panel
- (4) M6 x 16 screws
- (8) M4 x 10 screws
- (4) Self-tapping screws
- Magnetic vinyl
- Mounting brackets
- Owner's manual

LEDs Operates at noise levels comparable to an average office setting Temperature control 63-86 degF

Optional Remote Management SRCOOLNET2LX accessory (sold separately) allows you to monitor temperature and humidity, receive alerts, review logs and control settings remotely via SNMP, web, SSH or telnet

Simple Installation 6-ft. (1.83 m) power cord with NEMA 5-15P plug attaches to standard AC outlet Built-in evaporator eliminates condensation—no floor drain or water collection tank needed Magnetic air scoop attaches to rack enclosure's front door to optimize airflow Mounting hardware included

Specifications

OVERVIEW	
UPC Code	037332199928
INPUT	
Electrical Consumption (Max)	276 Watts
Nominal Input Voltage(s) Supported	120V AC
Nominal Input Voltage Description	120V AC 60 Hz
Input Connection Type	NEMA 5-15P
Input Plug Features	NEMA 5-15P
Voltage Compatibility (VAC)	120
Input Frequency	60 Hz
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
COOLING	
Airflow	Evaporator = 78 CFM / Condenser = 130 CFM
Cooling Type	Active
Cooling Capacity (BTUs)	2000
Cooling Capacity (kW)	0.6
Refrigerant	R134A
Refrigerant Amount	7.76 oz.
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	2-digit LCD displays numerical temperature readout
Front Panel LEDs	Push-button control panel with multiple LEDs for operational configuration
PHYSICAL	
Color	Black
Material of Construction	Steel



Powering Business Worldwide



Form Factors Supported	Wall Mount
Shipping Dimensions (hwd / in.)	16.90 x 19.60 x 23.60
Shipping Dimensions (hwd / cm)	42.93 x 49.78 x 59.94
Shipping Weight (lbs.)	53.00
Shipping Weight (kg)	24.04
Unit Dimensions (hwd / in.)	11.100 x 13.500 x 13.500
Unit Dimensions (hwd / cm)	28.19 x 34.29 x 34.29
Unit Weight (lbs.)	35
Unit Weight (kg)	15.88
COMMUNICATIONS	
SNMP Compatibility	SRCOOLNET2 (Optional) remote management accessory for remote monitoring and control
FEATURES & SPECIFICATIONS	
Compressor Type	Rotary
Dehumidifier	0.83 liters / hour
Sound Level (Noise)	< 55dB
Amp Draw Nominal	2.47A
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-22.2 No. 117-1970 (Canada); NOM (Mexico); UL 484
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.