




Powering Business Worldwide

# SmartRack 42U Standard-Depth Standard-Width Heavy-Duty Rack Enclosure Cabinet for AI Servers, White

MODEL NUMBER: **SRH422442W**



Heavy-duty rack houses, organizes and secures heavy AI servers used in edge computing, enterprise and other mission-critical IT applications.

## Features

### Heavy-Duty 42U Rack Cabinet Accommodates Servers Used in AI Applications

This SmartRack® 42U rack enclosure is constructed from heavy-duty steel 2.5 millimeters thick with reinforced structural elements, including extra welds and gussets for greater strength, extra connection points, and upgraded casters and levelers to support more weight. This cabinet has a maximum stationary load capacity of 5000 pounds (2268 kilograms) and a maximum rolling load capacity of 3500 pounds (1588 kilograms).

### Keeps AI Servers and Other Equipment Secure

The reversible front door, split rear doors and removable side panels lock securely with the included keys to help prevent damage, tampering or theft. The doors and side panels are designed for quick release, making it simple to access connected equipment and cabling with little effort. The removable roof panel has strategically placed pass-throughs to accommodate cables from vertical 0U PDUs and other equipment. The perforated front and split rear doors allow generous airflow from front to rear to help keep your equipment cool and functioning at its peak.

### White Server Rack Improves Visibility for Easier Maintenance

The SRH422442W features a white powder-coated finish both inside and outside. This white rack makes it easier to see the equipment mounted inside high-density installations. Improved visibility of ports and cables allows easier, faster installation and maintenance and helps reduce accidental disconnections.

### Easy Enclosure and Equipment Installation

This 42U server rack comes fully assembled for quick deployment with pre-installed casters that let you maneuver it over a level surface, where it can be stabilized by adjusting the levelers. Toolless 0U mounting rails allow quick installation of compatible PDUs and vertical cable managers. Built-in baying brackets allow the combination of two or more rack cabinets in a row.

### Meets Payment Card Industry Standards

The SRH422442W provides physical equipment and media security needed for PCI DSS (Payment Card Industry Data Security Standard) compliance. This is essential for companies that process, store and/or send credit card information.

## Highlights

- Maximum capacity: 5000 lb. (2268 kg) stationary, 3500 lb. (1588 kg) rolling load
- 2.5 mm thick steel frame includes extra welds and gussets for greater strength
- White powder-coated finish makes it easier to see ports and cables inside
- Ships fully assembled for immediate deployment and equipment mounting
- Provides physical equipment and media security needed for PCI DSS compliance

## Package Includes

- SRH422442W 42U Server Rack
- (4) Side panels
- (8) Side panel locks
- (2) Keys
- (60) Phillips-head mounting screws (M6 x 5/8 in.)
- (60) Nylon cup washers
- (60) Cage nuts
- Owner's manual



Powering Business Worldwide

## Specifications

| OVERVIEW                            |  |
|-------------------------------------|--|
| UPC Code                            | 037332290137                                     |
| Device Compatibility                | AI Server (extra deep); PDU; Patch Panel; Server |
| Rack Type                           | Enclosure  |
| PHYSICAL                            |  |
| Color                               | White  |
| Material of Construction            | Steel  |
| Rack Height                         | 42U  |
| Rack Depth                          | Standard   |
| Factory Preset Rack Depth (in.)     | 29.5   |
| Factory Preset Rack Depth (cm)      | 74.9   |
| Factory Preset Rack Depth (mm)      | 749  |
| Maximum Device Depth (cm)           | 104.14   |
| Maximum Device Depth (in.)          | 41   |
| Maximum Device Depth (mm)           | 1,041  |
| Minimum Device Depth (cm)           | 10.16  |
| Minimum Device Depth (in.)          | 4  |
| Minimum Device Depth (mm)           | 102  |
| Shipping Form Factor                | Factory Assembled                                |
| Unit Dimensions (hwd / in.)         | 79.508 x 23.622 x 44.165                         |
| Unit Dimensions (hwd / cm)          | 199.39 x 60.02 x 109.22                          |
| Unit Weight (lbs.)                  | 431  |
| Unit Weight (kg)                    | 195.50   |
| Weight Capacity - Rolling (kg)      | 1,588  |
| Weight Capacity - Rolling (lbs.)    | 3500   |
| Weight Capacity - Stationary (kg)   | 2,268  |
| Weight Capacity - Stationary (lbs.) | 5000   |
| Number of Vertical Mounting Rails   | 4  |
| Assembly Required                   | No   |
| FEATURES & SPECIFICATIONS           |  |
| Grounding Details                   | Front and rear door frames                       |
| Built-in Cable Management           | No   |
| Leveling Feet                       | Yes  |

|                                     |  |
|-------------------------------------|--|
| Extra Wide                          | No                                     |
| Locking                             | Yes                                    |
| Pre-Installed Casters               | Yes                                    |
| Outdoor Use                         | No                                     |
| STANDARDS & COMPLIANCE              |  |
| Product Certifications              | UL 62368-1; UL 2416                    |
| Product Compliance                  | CE (Europe); EIA/ECA-310-E; RoHS; UKCA |
| WARRANTY & SUPPORT                  |  |
| Product Warranty Period (Worldwide) | 5-year limited warranty                |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.