

SmartPro 120V 3kVA 2.25kW Line-Interactive Sine Wave UPS, Tower, Network Card Options, USB, DB9 Serial

MODEL NUMBER: **SMART3000SLT**



Description

3000VA line-interactive tower UPS system for server, networking and telecommunications equipment. Upright tower form factor. Offers sine wave 120V nominal output in both AC and battery modes. Switches to battery-derived AC output during power failures and extreme voltage variations. Line-interactive automatic voltage regulation (AVR) provides voltage boost/cut during brownouts/overvoltages to maintain regulated 120V nominal output over an input voltage range of 83-145V. Includes NEMA L5-30P input plug and 7 UPS-supported output receptacles (6 x 5-15/20R, 1 x L5-30R). Network-grade AC surge and noise suppression. Network management interfaces support simultaneous communications via USB port, DB9 serial port and installed Network Management Card. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all three network interfaces. PowerAlert power management software is available via free download. Three-stage metered current monitoring and battery charge status LEDs. Utility power and voltage regulation, and battery warning LEDs. Audible alarm. Self-test. Field-replaceable, hot-swappable internal batteries. Attractive all-black color scheme.

Features

- SmartPro line-interactive UPS system is ideal for voice, data, medical and industrial networking applications
- Line-interactive voltage regulation maintains selectable 120V nominal output during brownouts as low as 83V and overvoltages to 145V
- Enables continuous operation through blackouts, voltage fluctuations and surges
- Line-interactive automatic voltage regulation (AVR) provides 12% and 24% voltage boost during brownouts and a 12% voltage cut during overvoltages

Highlights

- 3kVA / 3000VA line interactive tower UPS; Sine wave output
- 120V nominal output during brownouts to 83 and overvoltages to 145V
- USB, RS232, EPO and Network Management Card options
- Front panel status LEDs with detailed load and battery capacity display
- NEMA L5-30P input; 6 NEMA 5-15/20R & 1 L5-30R outlets

Package Includes

- SMART3000SLT UPS System
- USB & DB9 Cables
- Owner's manual



- Standard internal battery set offers 9 min. runtime at half load (1125W) and 3.5 min. at full load (2250W)
- Intelligent battery management system extends battery life
- Space-saving upright tower format
- Built-in USB, RS-232 and slot for Network Management Card option; Compatible with Tripp Lite UPS management card options WEBCARDLX, RELAYIOCARD and SNMPWEBCARD
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- UPS interface supports on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery capacity, timed inverter shutoff, activate self-test and output power control
- NEMA L5-30P input plug/6 x NEMA 5-15/20R and 1 x NEMA L5-30R output receptacles
- Front panel LEDs provide current monitoring, voltage regulation, battery charge level and battery warning information
- UPS ships fully assembled in full compliance with DOT regulations; no time-consuming connection of internal batteries by user required

Specifications

OVERVIEW	
UPC Code	037332125767
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	20A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	L5-30P
Input Circuit Breakers	30A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A 120V
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	3000
Output kVA Capacity (kVA)	3



Output Watt Capacity (Watts)	2250
Output kW Capacity (kW)	2.25
Power Factor	0.8
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18% / +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Circuit Breakers	20A branch rated (x2) - each breaker protects 3 5-15/20R outlets, L5-30R is unbreakered
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15/20R; (1) L5-30R
Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	3.5 min. (2250w)
Half Load Runtime (min.)	9 min. (1125w)
Expandable Runtime	No
DC System Voltage (VDC)	48
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90% (typical, full load discharge)
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	 RBC54
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 145
Overvoltage Correction	Input voltages between 127 and 145 are reduced by 12%; Voltage setpoints ±5% tolerance
Undervoltage Correction	Input voltages between 96 and 108V are boosted by 12%; Voltage setpoints ±5% tolerance
Severe Undervoltage Correction	Input voltages between 83 and 95V are boosted by 24%; Voltage setpoints ±5% tolerance
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation



Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Audible alarm indicates power failure and overload conditions
LED Indicators	9 LEDs indicate line power, battery power, AVR, overload and replace battery status - with a 3-LED level meter for load and battery charge level
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Cooling Method	Fan
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
Primary UPS Depth (mm)	318
Primary UPS Height (mm)	267
Primary UPS Width (mm)	226
Shipping Dimensions (hwd / cm)	38.86 x 45.21 x 34.80
Shipping Dimensions (hwd / in.)	15.30 x 17.80 x 13.70
Shipping Weight (kg)	34.25
Shipping Weight (lbs.)	75.50
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	26.67 x 22.61 x 31.75
UPS Power Module Dimensions (hwd, in.)	10.5 x 8.9 x 12.5
UPS Power Module Weight (kg)	25.85
UPS Power Module Weight (lbs.)	57
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	320
Battery Mode BTU / Hr. (Full Load)	1251
AC Mode Efficiency Rating (100% Load)	96%



Audible Noise	Audible Noise < 50 dBA at Front Side 1 Meter
COMMUNICATIONS	
Network Management Cards	 SNMPWEBCARD ; WEBCARDLX ; RELAYIOCARD ;
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	145
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
STANDARDS & COMPLIANCE	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required ;for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance ;

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>