


SmartRack Monitor Rack-Mount Bracket, 4U, for LCD Monitor up to 17-19 in.

MODEL NUMBER: SRLCDMOUNT



Durable VESA bracket allows rack mounting of a flat-panel LCD monitor in a 19 in. floor rack enclosure or open frame rack.

Features

Easy Mounting of LCD Monitors or Televisions up to 19 in. This rack-mount monitor bracket is compliant with multiple VESA patterns, making it compatible with a wide range of retail LCD displays and touch-screen monitors up to 44 pounds. The SRLCDMOUNT supports LCD monitors up to 17 inches, which allows the display to fit snugly within a closed rack. If closing rack doors isn't an issue, simply reverse the rack-mount monitor bracket so that it's facing outward. With this configuration, the SRLCDMOUNT supports LCD monitors up to 19-inches. Compatible VESA mounting-hole patterns are 75 x 75 mm, 100 x 100 mm and 100 x 150 mm.

Includes Necessary Hardware for Mounting in 4U of Rack Space This VESA bracket fits all EIA-compliant 19-inch open frame racks and floor-standing rack enclosures. It's made from durable cold-rolled steel with a black powder-coated finish that blends seamlessly with your rack décor. Rack-mounting hardware is included, as well as a convenient Quick Start Guide that walks you through the simple rack-mounting process.

2-Year Warranty and Environmentally Responsible Design The SRLCDMOUNT comes with a 2-year warranty. It's manufactured in compliance with strict RoHS specifications.

Highlights

- Fits 75 x 75, 100 x 100 and 100 x 150 VESA patterns to match wide variety of displays
- Compatible with all standard 19 in. open frame racks and floor rack enclosures
- Durable cold-rolled steel construction designed to stand up to heavy use over time
- Rack-mounting hardware included for immediate installation
- Supports LCD and touch-screen monitors up to 17-19 in. and 44 lb.

Applications

- Install an LCD display in an open frame or floor rack to monitor essential server-room or console information
- Mount a touch-screen display for instant on-site operation and control of rack equipment

System Requirements

- LCD display with 75 x 75 mm, 100 x 100 mm or 100 x 150 mm VESA plate

Package Includes

- LCD Mounting Plate
- (2) Rack Brackets
- (8) M6 x 16 Screws
- (8) M6 Cup Washers
- (8) M6 Cage Nuts
- (8) M5 x 10 Screws
- (8) M5 Flat Washers
- Installation Guide

Specifications

OVERVIEW	
UPC Code	037332213419
Device Compatibility	Monitor/HDTV
Accessory Type	Mounting Bracket
Accessory Class	Rack Accessories



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Rack Height	4U
VESA Pattern (mm)	100x100; 100x150; 75x75
Maximum Weight Capacity (lbs.)	44
Maximum Weight Capacity (kg)	20
Number of Displays	1
Shipping Dimensions (hwd / in.)	8.00 x 19.20 x 20.80
Shipping Dimensions (hwd / cm)	20.32 x 48.77 x 52.83
Shipping Weight (lbs.)	15.60
Shipping Weight (kg)	7.08
Unit Dimensions (hwd / in.)	4.880 x 18.880 x 15.810
Unit Dimensions (hwd / cm)	17.7 x 48.2 x 11.5
Unit Weight (lbs.)	3.57
Unit Weight (kg)	1.62
Weight Capacity - Stationary (kg)	18
Weight Capacity - Stationary (lbs.)	40
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.