


# Wall Support Kit for 12 in. Cable Runway, Straight and 90-Degree - Hardware Included

MODEL NUMBER: SRLWALLSPPT12



Easy-to-connect wall support kit safely and securely mounts to a wall surface to support 12 in. cable runway.

## Features

**Cable Ladder Bracket Kit Secures Your Data Center's Runway System on a Wall** This SmartRack cable runway wall support kit creates a secure connection between your server rack and the wall of your server room or data center. All mounting and installation hardware is included for attaching a ladder to a wall, except for appropriate fasteners to secure the durable steel wall bracket. The mounting surface must be able to support the combined equipment load safely. Be sure to use suitable mounting means when installing to cinder block, concrete, drywall or wooden studs. The SRLWALLSPPT12 is designed for use with 12-inch (305-millimeter) SRCABLELADDER, SRL90BEND12 and other compatible straight and 90-degree ladder sections.

## Highlights

- Securely connects cable management ladders to the wall of your data center
- Ladders can be safely routed from the wall to outside an enclosure or open frame rack
- Compatible with both 12 in. (305 mm) straight and 90-degree-bend ladder sections
- Works with all 12 in. SmartRack® ladder system accessories and runways

## Applications

- Secure a ladder runway system against the wall of your data center or server room.

## System Requirements

- Compatible with 12 in. (305 mm) straight and 90-degree-bend ladder sections, including SRCABLELADDER and SRL90BEND12

## Package Includes

- Wall bracket
- (2) M8 J-bolts
- (2) M8 lock washers
- (2) M8 hex nuts
- Installation guide

# Specifications

OVERVIEW	
UPC Code	037332214492
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Shipping Dimensions (hwd / in.)	3.54 x 16.53 x 3.54
Shipping Dimensions (hwd / cm)	9.00 x 42.00 x 9.00
Shipping Weight (lbs.)	2.36
Shipping Weight (kg)	1.07



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Dimensions (hwd / in.)	3.543 x 16.535 x 3.543
Unit Dimensions (hwd / cm)	8.99 x 41.99 x 8.99
Unit Weight (lbs.)	1.70
Unit Weight (kg)	0.77
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.