

## SmartPro 120V 750VA 600W Line-Interactive Sine Wave UPS, 2U, Extended Run, WEBCARDLX, LCD, USB, DB9

MODEL NUMBER: SMART750RML2UN



Line-interactive UPS offers complete power protection for small network applications, including telecom, security and digital signage.

### Features

**750VA/600W/120V Battery Backup for PC Networks, Security Systems or Digital Signage**The SmartPro® line-interactive SMART750RML2UN UPS system with AVR provides reliable battery backup and AC power protection against blackouts, brownouts, overvoltages, surges and line noise that can damage valuable electronics or destroy data. The six-outlet 120V battery backup is ideal protection for small networks, wiring closets, security systems, telecom, high-end PC gaming, digital signage equipment and other professional applications, including retail, casino and hotel/motel management.

**Reliable, Expandable Battery Backup Keeps You Operational Through Power Outages**The user-replaceable, hot-swappable internal battery provides 20.7 minutes of support at half load (300W) and 8.5 minutes at full load (600W), allowing you to work through short power failures and giving you enough time to safely save files and shut down your system in case of a prolonged blackout. For mission-critical applications demanding scalable extended runtime, the UPS supports external battery packs, such as Tripp Lite's BP24V36-2US (sold separately). The intelligent battery management system extends battery life.

**WEBCARDLX Network Interface Offers 24/7 Remote Access for Monitoring and Control**The Java-free HTML5-based WEBCARDLX enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Automated alerts help prevent accidental overloads, power loss and downtime. WEBCARDLX allows you to use the Auto Probe feature, which can prevent costly service calls by automatically rebooting non-responsive network devices.

**6 NEMA Outlets Protect Your Connected Components**Six 5-15R outlets provide battery backup, 570 joules of surge protection and voltage regulation for your crucial components. Two independently switched two-outlet load banks enable both scheduled and real-time remote rebooting and load shedding.

**Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage Conditions**AVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts and overvoltages. The SMART750RML2UN can correct brownouts as low as 83V and overvoltages as high as 147V back to nominal 120V power continuously, all while keeping the battery fully charged and ready to take over in case of power failure.

**Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better**This UPS system filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

**Designed for High Efficiency to Help You Save Money and Protect the Environment**A 95% efficiency

### Highlights

- Protects equipment against blackouts, brownouts, overvoltages, surges and line noise
- Keeps AC power running during blackouts to allow time for file saves and safe shutdown
- Maintains continuous 120V nominal output during brownouts and overvoltages
- Pre-installed WEBCARDLX network interface supports Auto Probe feature
- Easy-to-read LCD allows real-time monitoring of voltage, battery status and other data

### Applications

- Protect your small network server and other network components against power surges, line noise, brownouts, overvoltages and blackouts
- Operate essential equipment during short-term power outages using battery backup power
- Shut down desktop PCs and other equipment without data loss during long-term power outages
- Connect high-end security systems, casino gaming machines or digital signage in a small network

### Package Includes

- SMART750RML2UN 120V 750VA 600W Line-Interactive



rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

**Silenceable Alarm and Easy-to-Read LCD Keep You Informed Around the Clock** The front-panel LCD lets you monitor important data, such as load level, power factor, voltage, battery charge and estimated runtimes. It rotates for comfortable viewing in both rack and tower configurations. The audible alarm sounds for power failure, low battery and overloads. You may silence it using the built-in switch or disable it.

**Advanced Communications Ports Allow for Automatic Saves and Shutdowns** RS-232 and HID-compliant USB ports connect to a computer running Tripp Lite's free downloadable PowerAlert® software to enable safe unattended file saves and system shutdown in case of a prolonged power failure. The EPO port supports emergency shutdown in large facilities. Cables are included.

**Versatile Installation Options** Hardware is included for mounting the Tripp Lite SmartPro UPS system in 2U of space in an EIA-standard 19-inch 4-post rack. Using optional mounting accessories (sold separately), you can adapt the SMART750RMXL2UN for 2-post (2POSTRMKITWM), front-rail (UPSHDEARKIT), 4-post short-depth (4POSTRAILKITWM), tower (2-9USTAND) or wall mounting (2POSTRMKITWM). The 10-foot power cord with NEMA 5-15P plug connects to any compatible AC outlet.

UPS with 6 Outlets

- WEBCARDLX network management card
- USB cable
- DB9 cable
- EPO cable
- Rack-mounting hardware
- Owner's manual

## Specifications

| OVERVIEW                                 |  |
|--|--|
| UPC Code                                 | 037332256409   |
| UPS Type                                 | Line-Interactive   |
| INPUT                                    |  |
| Rated input current (Maximum Load)       | 7.5A   |
| Nominal Input Voltage(s) Supported       | 120V AC  |
| UPS Input Connection Type                | 5-15P  |
| Input Circuit Breakers                   | 10A  |
| UPS Input Cord Length (ft.)              | 10   |
| UPS Input Cord Length (m)                | 3.1  |
| Recommended Electrical Service           | 15A 120V   |
| Input Phase                              | Single-Phase   |
| OUTPUT                                   |  |
| Output Volt Amp Capacity (VA)            | 750  |
| Output Watt Capacity (Watts)             | 600  |
| Output Capacity Details                  | Output is reduced to 450 watts maximum when used with external battery packs |
| Power Factor                             | 0.8  |
| Nominal Voltage Details                  | 120v nominal output in battery mode  |
| Frequency Compatibility                  | 60 Hz  |
| Output Voltage Regulation (Line Mode)    | -21%, +8%  |
| Output Voltage Regulation (Battery Mode) | +/- 5%   |



|  |  |
|--|--|
| Load Management Receptacles                  | Two switchable two-outlet 5-15R load banks   |
| Output AC Waveform (AC Mode)                 | Sine wave  |
| Output AC Waveform (Battery Mode)            | Pure Sine wave   |
| Nominal Output Voltage(s) Supported          | 110V; 115V; 120V   |
| Output Receptacles                           | (6) 5-15R  |
| Individually Controllable Load Banks         | Yes  |
| <b>BATTERY</b>                               |  |
| Full Load Runtime (min.)                     | 8.5 min. (600w)  |
| Half Load Runtime (min.)                     | 20.7 min. (300w)   |
| Expandable Battery Runtime                   | Extended runtime supported via optional external battery packs   |
| External Battery Pack Compatibility          | &nbsp;<a class="productLink" href="//www.tripplite.com/External-24V-2U-Rack-Tower-Battery-Pack-for-select-Tripp-Lite-UPS-Systems~BP24V15RT2U">BP24V15RT2U</a>&nbsp;<small>(limit 1)</small>&nbsp;<a class="productLink" href="//www.tripplite.com/External-24V-2U-Rack-Tower-Battery-Pack-select-Tripp-Lite-UPS-Systems~BP24V28-2U">BP24V28-2U</a>&nbsp;<small>(limit 1)</small>&nbsp;<a class="productLink" href="//www.tripplite.com/External-24V-3U-Rack-Tower-Battery-Pack-select-Tripp-Lite-UPS-Systems~BP24V70-3U">BP24V70-3U</a>&nbsp;<small>(multi-pack compatible)</small>&nbsp;<a class="productLink" href="//www.tripplite.com/external-24v-2u-rack-mount-battery-pack-for-tripp-lite-ups-systems-SMART750-SU750-SU1000-SUINT1000-and-more~BP24V36-2US">BP24V36-2US</a>&nbsp;<small>(multi-pack compatible)</small> |
| DC System Voltage (VDC)                      | 24   |
| Battery Recharge Rate (Included Batteries)   | Less than 4.5 hours from 10% to 90% (typical, full load discharge)   |
| Internal UPS Replacement Battery Cartridge   | &nbsp;<a class="productLink" href="//www.tripplite.com/2U-UPS-Replacement-Battery-Cartridge-for-Select-Tripp-Lite-UPS~RBC24V-LCD">RBC24V-LCD</a>&nbsp;<small>(limit 1)</small>   |
| Battery Access                               | Front panel battery access door  |
| Battery Replacement Description              | Hot-swappable, user replaceable batteries  |
| Expandable Runtime                           | Yes  |
| <b>VOLTAGE REGULATION</b>                    |  |
| Voltage Regulation Description               | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147   |
| Overvoltage Correction                       | Input voltages between 128 and 147 are reduced by 12%  |
| Undervoltage Correction                      | Input voltages between 83 and 107 are boosted by 14%   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |  |
| Switches                                     | 3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions   |
| Alarm Cancel Operation                       | Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available   |
| Audible Alarm                                | Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions  |
| LED Indicators                               | Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)  |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

| <b>SURGE / NOISE SUPPRESSION</b>                              |  |
|---|--|
| UPS AC Suppression Joule Rating                               | 570  |
| EMI / RFI AC Noise Suppression                                | Yes  |
| <b>PHYSICAL</b>   |  |
| Cooling Method  | Fan  |
| Included Mounting Accessory Description                       | Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)  |
| Installation Form Factors Supported with Included Accessories | 4 post 19 inch rackmount   |
| Installation Form Factors Supported with Optional Accessories | 2 post rackmount ( <a href="//www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> ); 2-4 post front rail rackmount ( <a href="//www.tripplite.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT">UPSHDEARKIT</a> ); 4 post rackmount short-depth ( <a href="//www.tripplite.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4POSTRAILKITWM</a> ); Tower ( <a href="//www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> ); Wallmount ( <a href="//www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> );   |
| Minimum Required Rack Depth (cm)                              | 41.15  |
| Minimum Required Rack Depth (inches)                          | 16.2   |
| Optional Mounting Accessory Notes                             | Optional <a href="//www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> ; enables upright tower UPS placement; <a href="//www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> ; enables wall-mount and 2-post rackmount installation; <a href="//www.tripplite.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4POSTRAILKITWM</a> ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); <a href="//www.tripplite.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT">UPSHDEARKIT</a> ; enables installation in 2 or 4-post racks using front vertical rails only, without rear support |
| Primary Form Factor   | Rackmount  |
| Primary UPS Depth (mm)  | 334  |
| Primary UPS Height (mm)                                       | 88   |
| Primary UPS Width (mm)  | 441  |
| Rack Height   | 2U   |
| Shipping Dimensions (hwd / in.)                               | 8.70 x 18.60 x 23.30   |
| Shipping Weight (kg)  | 20.64  |
| UPS Housing Material  | Steel  |
| UPS Power Module Dimensions (hwd, in.)                        | 3.45 x 17.35 x 13.15   |
| UPS Power Module Weight (kg)                                  | 16.06  |
| UPS Power Module Weight (lbs.)                                | 35.4   |
| <b>ENVIRONMENTAL</b>  |  |
| Operating Temperature Range                                   | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius  |



|   |  |
|---|--|
| Storage Temperature Range                                   | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius   |
| Relative Humidity   | 0 to 95%, non-condensing   |
| AC Mode BTU / Hr. (Full Load)                               | 109  |
| AC Mode Efficiency Rating (100% Load)                       | 95%  |
| Audible Noise   | 45 dBA maximum, front side 1m  |
| <b>COMMUNICATIONS</b>                                       |  |
| Network Management Cards                                    | &nbsp;<a class="productLink" href="//www.tripplite.com/Web-Management-Accessory-Card-WEBCARDLX">WEBCARDLX</a>&nbsp;</td>   |
| Network Monitoring Port Description                         | Pre-installed WEBCARDLX network management card; Supports detailed monitoring of UPS and site power conditions   |
| PowerAlert Software   | For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a> |
| Communications Cable  | USB and DB9 cabling included   |
| WatchDog Compatibility                                      | Supports Watchdog application, OS and hard-reboot restart options for remote applications  |
| Communications Interface                                    | DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface; USB (HID enabled)  |
| <b>LINE / BATTERY TRANSFER</b>                              |  |
| Transfer Time   | 4 milliseconds (AC to battery mode), 2 milliseconds (Battery to AC mode)   |
| Low Voltage Transfer to Battery Power (Setpoint)            | 83   |
| High Voltage Transfer to Battery Power (Setpoint)           | 147  |
| <b>SPECIAL FEATURES</b>                                     |  |
| Grounding Lug   | Back panel grounding lug   |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported   |
| High Availability UPS Features                              | Hot swappable batteries; Auto Probe Monitoring and Reboot (included)   |
| <b>STANDARDS &amp; COMPLIANCE</b>                           |  |
| UPS Certifications  | Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)   |
| Certification Details                                       | UL 1778: 2014 R8.15 (5TH EDITION); CAN/CSA-C22.2 NO. 107.3-14  |
| <b>WARRANTY</b>   |  |
| Product Warranty Period (Worldwide)                         | 2-year warranty, 3 year with registration. Note:&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/product-warranty-registration">Registration is required</a>&nbsp;</td>      |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico)  | \$250,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;</td>   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>