


SmartRack Cantilever Fixed Steel Rack Shelf - 1U, Vented, 7 in. (17.8 cm) Deep, Holds up to 40 lb. (18 kg)

MODEL NUMBER: SRSHELF2P1USHRT



Vented shelf is 7 in. deep to house a wireless access point or other non-rack device and save space in your server room or network closet.

Features

1U Vented Cantilever Rack Shelf Secures Non-Rack Equipment in Your Data Center

This SmartRack® fixed shelf supports monitors, wireless access points, tower units and other IT equipment not typically stored in a rack. Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the SRSHELF2P1USHRT has a maximum load capacity of 40 pounds (18 kilograms). It mounts easily into 1U of space in an EIA-standard 19-inch 2-post or 4-post enclosure or open frame rack using the included hardware.

Maximizes Rack Space and Saves Desk or Floor Space in a Busy Office

The steel shelf is seven inches (17.8 centimeters) deep for organizing network and other non-rack equipment in your small office or server room. The vented surface allows generous airflow to keep your equipment cool and functioning at its peak. You may mount two SRSHELF2P1USHRT shelves back-to-back in your rack to create a deeper shelf in the same 1U rack space.

Highlights

- Cantilever 1U rack shelf secures non-rack equipment like WAPs and monitors
- Heavy-duty cold-rolled steel construction with maximum load capacity of 40 lbs (18 kgs)
- Vented design maximizes airflow to protect equipment against excessive heat
- 2 units can be installed back-to-back to create a deeper shelf in same 1U rack space

Package Includes

- SRSHELF2P1USHRT 1U Fixed Shelf, 7 in. Deep (17.8 cm)
- (4) 12-24 screws
- (4) Cup washers
- Instruction sheet

Specifications

OVERVIEW	
UPC Code	037332263155
Product Type	Accessories / Shelf
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	
Rack Height	1U
Maximum Weight Capacity (lbs.)	40



Powering Business Worldwide

TRIPP LITE
SERIES

Maximum Weight Capacity (kg)	18
Unit Dimensions (hwd / in.)	1.730 x 18.990 x 7.310
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 18.56
Unit Weight (lbs.)	2.5
Unit Weight (kg)	1.13
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.