


## SmartRack 12U Vertical Extension Top Hat for Server Racks - 42 in. Deep, Doors & Side Panels Included

MODEL NUMBER: SRTH12UB



Attaches to the top of your Tripp Lite floor-standing rack enclosure to add 12U without taking up any additional floor space.

### Features

#### Standard-Depth 12U Top Hat Expands Your Rack Application without Adding Floor Space

This SmartRack® 12U vertical expansion rack is ideal for users who want to add rack equipment, but have limited floor space in their server room or data center. The SRTH12UB attaches to the top of your already existing SmartRack floor-standing rack, allowing you to expand vertically without taking up any additional floor space. Hardware for assembly and mounting is included.

#### Expanding Upward Keeps Your Costs Down

Adding a vertical extension to your existing rack is a practical alternative to expensive upgrades. By adding 12U to the top of your enclosure, you save the time, hassle and expense of purchasing and installing a new larger rack and moving all the equipment.

#### Easy to Integrate into Your Current Application

The SRTH12UB is compatible with standard-depth Tripp Lite floor-standing racks (600 millimeters wide, 1050 millimeters deep) with a removable roof panel. Extensions require assembly on top of the rack, allowing the installation of one component at a time. Multiple grounding points are included on the extensions. **Note:** *You do not have to remove the roof panel of the original rack to install the top hat.*

#### Keeps Important Equipment Secure

The adjustable mounting rails accommodate standard 19-inch rack equipment. The reversible front door, split rear doors and side panels lock securely to help prevent damage, tampering or theft. The doors, side panels and roof panel are designed for quick release, making it easy to access connected equipment and cabling with little effort. Convenient top access ports and an open bottom allow easy cable routing through the cabinet.

#### Meets Payment Card Industry Standards

The SRTH12UB provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance. This is essential for companies that process, store and/or transmit credit card information.

### Highlights

Compatible with all standard-depth and width (600mm x 1050mm) Tripp Lite floor racks with removable roof doors and side panels lock securely to help prevent damage, tampering or theft Fully grounded vertical extension rack comes with all hardware included Top access ports and open bottom allows easy cable routing throughout Provides physical equipment and media security required for PCI DSS compliance

### Applications

- Add 12U of space to your existing rack without compromising valuable floor space in your server room or data center
- Increase the amount of rack equipment in your application without an expensive upgrade to a larger rack

### System Requirements

- Compatible with Tripp Lite floor-standing rack enclosures with a removable roof and the standard 600 mm width and 1050 mm depth
- Does not work with Deep or Wide specialty rack cabinets

### Package Includes

- SRTH12UB Vertical Extension Top Hat
- (2) Keys
- (16) M6 x 12 screws
- (41) M4 x 8 screws with lock washers
- (4) 8.8 flange head cap screws
- (6) Ground wires
- Assembly instructions
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332264121
Device Compatibility	Network Switch; PDU; Patch Panel; Router; Server; UPS
Rack Type	Enclosure
Accessory Type	Rack-Mount
Accessory Class	Rack Accessories
PHYSICAL	
Color	Black
Rack Height	12U
Rack Depth	Standard
Factory Preset Rack Depth (in.)	27.75
Factory Preset Rack Depth (cm)	70.5
Factory Preset Rack Depth (mm)	705
Maximum Device Depth (cm)	93.98
Maximum Device Depth (in.)	37
Maximum Device Depth (mm)	940
Minimum Device Depth (cm)	10.16
Minimum Device Depth (in.)	4
Minimum Device Depth (mm)	102
Cable Access Hole Measurement (inches)	3.25
Shipping Dimensions (hwd / in.)	24.41 x 15.35 x 39.17
Shipping Weight (kg)	59.87
Unit Dimensions (hwd / in.)	23.878 x 23.622 x 43.000
Unit Dimensions (hwd / cm)	60.65 x 60.00 x 109.22
Unit Weight (lbs.)	132.00
Unit Weight (kg)	59.87
Weight Capacity - Rolling (kg)	0
Weight Capacity - Rolling (lbs.)	0
Weight Capacity - Stationary (kg)	0
Weight Capacity - Stationary (lbs.)	0
Number of Vertical Mounting Rails	4

FEATURES & SPECIFICATIONS	
Grounding Lug	Front and back door frames
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	EN 55022; EN 55024; UL 60950-1
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty