

SMX3000XLRT2U is available in Mexico only

SmartPro 230V 3kVA 2.25kW Line-Interactive Sine Wave UPS, 2U Rack/Tower, Extended Run, Network Card Options, USB, DB9 Serial

MODEL NUMBER: **SMX3000XLRT2U**



Description

Tripp Lite's SMX3000XLRT2U intelligent, line interactive rack/tower uninterruptible power supply prevents data loss, downtime and equipment damage due to power outages, voltage fluctuations and transient surges. Requires only two rack spaces (2U) in a standard rack enclosure. Large internal batteries offer 11 minutes half load runtime and 4 minutes at full load. Runtime is expandable with optional BP48V24-2U or BP48V60RT-3U external battery packs. Maintains regulated 230V nominal output without using battery power during brownouts and overvoltages from 158 to 278V. 3000VA/2250 watt power handling capability and full time sine wave output offers guaranteed compatibility with networking, telecom and other sensitive electronic applications. Includes a total of 9 outlets with 3 load banks that are individually switchable via software interface to reboot select equipment on demand or shed less significant loads to extend battery runtime for more critical equipment. Supports simultaneous remote monitoring of UPS and site power conditions via built-in USB and DB9 monitoring ports. Includes PowerAlert UPS monitoring and unattended shutdown software with complete cabling. Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX, SNMPWEBCARD and RELAYIOCARD. Emergency Power Off (EPO) interface offers option for instantaneous power-off of UPS and connected equipment in the case of fire or emergency. Multi-function audible alarms and set of 5 front panel LEDs offer at-a-glance notification of UPS and line power status. Network-grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges and line noise. Attractive all-black color scheme.

Features

- SMX3000XLRT2U line interactive UPS offers battery derived sine wave AC output during power outages, voltage regulation during brownouts and overvoltages, plus network-grade AC surge suppression
- 3000VA/2250 watt power handling capability with full-time sine wave output offers guaranteed compatibility with networking, telecom and other sensitive electronic devices
- Supports 2U rackmount installation in 4 post equipment racks, 2 post rackmount installation requires 2POSTRMKITWM, upright tower installation requires 2-9USTAND accessory
- Large internal batteries support a half load of 1500VA for 11 minutes and a full load of 3000VA for 4

Highlights

- 3kVA / 3000VA / 2250W line interactive 2U rack/tower UPS; Sine wave output
- 230V nominal output during brownouts to 151V and overvoltages to 282V
- USB, RS232, EPO & optional SNMP/Web card are available for simultaneous use
- Extended runtime options up to 1600W
- Detailed status LEDs; 3 switched output load banks
- C20 inlet; 8 C13 & 1 C19 outlets; Includes 3 C13 to C14 cables

Package Includes

- SMX3000XLRT2U UPS System
- PowerAlert software with USB and DB9 cables
- Mounting hardware for 4 post rackmount applications
- Cable for Emergency Power Off interface
- Instruction manual with warranty information



minutes

- Runtime is further expandable with the addition of external battery packs BP48V24-2U (limit 1), BP48V60RT-3U (multi-pack compatible) and BP48V27-2US (multi-pack compatible)
- Some external battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Intelligent battery management system extends battery life
- Maintains regulated 230V nominal output during brownouts and overvoltages from 158 to 278V
- Includes 9 UPS supported outlets arranged in 3 individually controllable load banks (2 outlets per bank) that can be powered off and back on again via software interface
- IEC320-C20 input connection accepts a variety of detachable cordsets to match country or site-specific wall receptacles
- PowerAlert UPS monitoring and unattended shutdown software enables configurable network broadcast messaging, email notification, event logging and running user-defined script commands.
- Offers simultaneous monitoring through included USB and DB9 interface ports, or the monitoring by any number of additional servers over IP with included PowerAlert monitoring software.
- Communications ports support messaging of UPS and line power status, including on-battery, low-battery, power restored, AC line voltage, DC battery voltage and remaining battery capacity
- Emergency Power Off (EPO) interface with cable
- Supports timed inverter shutoff after unattended shutdown, activate self-test and UPS output power control for delayed or immediate reboot of connected devices
- Supports Tripp Lite's WatchDog software application to restore operation to locked equipment through soft reboot of application, OS or hard power off/on reboot of connected equipment - ideal for unattended kiosk applications (requires optional WATCHDOGSW)
- Built-in accessory slot supports SNMP with optional SNMPWEBCARD adapter
- Emergency Power Off (EPO) interface with cable
- Multi-function audible alarms and set of 5 front panel LEDs
- Network-grade AC surge suppression
- Attractive all-black color scheme
- Optional PDUBHV20 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- UPS battery set ships fully assembled, no time consuming connection of internal batteries by user is necessary

Specifications

| OVERVIEW | |
|----------|------------------|
| UPC Code | 037332120502 |
| UPS Type | Line-Interactive |



| INPUT | |
|--|---|
| Rated input current (Maximum Load) | 15A |
| Nominal Input Voltage(s) Supported | 230V AC |
| UPS Input Connection Type | C20 inlet |
| UPS Input Connection Description | User supplies input cabling with C19 output connection |
| Input Circuit Breakers | 20A |
| Input Phase | Single-Phase |
| OUTPUT | |
| Output Volt Amp Capacity (VA) | 3000 |
| Output kVA Capacity (kVA) | 3 |
| Output Watt Capacity (Watts) | 2250 |
| Output kW Capacity (kW) | 2.25 |
| Output Capacity Details | Output is reduced to 1600W maximum when used with external battery packs |
| Power Factor | 0.75 |
| Nominal Voltage Details | 230v nominal inverter output voltage |
| Frequency Compatibility | 50 / 60 Hz |
| Frequency Compatibility Details | Automatic frequency selection |
| Output Voltage Regulation (Line Mode) | 230V (-15%, +6%) |
| Output Voltage Regulation (Battery Mode) | +/- 5% |
| Included Output Power Cables | Includes 3 C13 to C14 output power cables |
| Load Management Receptacles | Three switchable two-outlet C13 load banks |
| Output Circuit Breakers | 10A (x2) - each breaker protects 4 C13 outlets, C19 outlet does not include a breaker |
| Output AC Waveform (AC Mode) | Sine wave |
| Output AC Waveform (Battery Mode) | Pure Sine wave |
| Nominal Output Voltage(s) Supported | 220V; 230V; 240V |
| Output Receptacles | (8) C13; (1) C19 |
| Individually Controllable Load Banks | Yes |
| BATTERY | |
| Battery Type | Valve Regulated Lead Acid (VRLA) |
| Full Load Runtime (min.) | 4 min. (2250w) |
| Half Load Runtime (min.) | 11 min. (1125w) |



| | |
|---|--|
| Expandable Battery Runtime | Extended runtime supported via optional external battery packs |
| Expandable Runtime | Yes |
| External Battery Pack Compatibility | BP48V24-2U (limit 1); BP48V60RT-3U (multi-pack compatible); BP48V27-2US (multi-pack compatible) |
| DC System Voltage (VDC) | 48 |
| Battery Recharge Rate (Included Batteries) | Less than 4.5 hours from 10% to 90% (typical, full load discharge) |
| Battery Access | Front panel battery access door |
| Internal UPS Replacement Battery Cartridge | RBC94-2U |
| Battery Replacement Description | Hot-swappable, user replaceable batteries |
| VOLTAGE REGULATION | |
| Voltage Regulation Description | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 158 to 278 |
| Overvoltage Correction | Input voltages between 244 and 278 are reduced by 12% |
| Undervoltage Correction | Input voltages between 182 and 206 are boosted by 12% |
| Severe Undervoltage Correction | Input voltages between 158 and 182 are boosted by 24% |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | 2 Switches control off/on power status and alarm-cancel/self-test operation; Rear dip-switch for charger rate adjustment |
| Alarm Cancel Operation | Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status |
| Audible Alarm | Audible alarm indicates power-failure, overload and low-battery conditions |
| LED Indicators | 5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status |
| SURGE / NOISE SUPPRESSION | |
| UPS AC Suppression Joule Rating | 480 |
| UPS AC Suppression Response Time | Instantaneous |
| EMI / RFI AC Noise Suppression | Yes |
| PHYSICAL | |
| Cooling Method | Fan |
| Included Mounting Accessory Description | Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm) |
| Installation Form Factors Supported with Included Accessories | 4 post 19 inch rackmount |



| | |
|---|---|
| Installation Form Factors Supported with Optional Accessories | 2 post rackmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM); 2-4 post front rail rackmount (Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT); 4 post rackmount short-depth (4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM); Tower (2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND); Wallmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM); |
| Minimum Required Rack Depth with External Battery Pack (cm) | 66 |
| Minimum Required Rack Depth with External Battery Pack (in.) | 26 |
| Minimum Required Rack Depth without External Battery Pack (cm) | 57 |
| Minimum Required Rack Depth without External Battery Pack (in.) | 22.5 |
| Optional Mounting Accessory Notes | Optional 2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND ; enables upright tower UPS placement; 2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM ; enables wall-mount and 2-post rackmount installation; 4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT ; enables installation in 2 or 4-post racks using front vertical rails only, without rear support |
| Primary Form Factor | Rackmount |
| Primary UPS Depth (mm) | 483 |
| Primary UPS Height (mm) | 89 |
| Primary UPS Width (mm) | 445 |
| Rack Height | 2U |
| Shipping Dimensions (hwd / cm) | 22.86 x 60.32 x 51.44 |
| Shipping Dimensions (hwd / in.) | 9.00 x 23.75 x 20.25 |
| Shipping Weight (kg) | 32.93 |
| Shipping Weight (lbs.) | 72.60 |
| UPS Housing Material | Steel |
| UPS Power Module Dimensions (hwd, cm) | 8.89 x 44.45 x 48.26 |
| UPS Power Module Dimensions (hwd, in.) | 3.5 x 17.5 x 19 |
| UPS Power Module Weight (kg) | 29.03 |
| UPS Power Module Weight (lbs.) | 64 |
| ENVIRONMENTAL | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius |
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius |
| Relative Humidity | 0 to 95%, non-condensing |



| | |
|---|--|
| AC Mode BTU / Hr. (Full Load) | 236.6 |
| AC Mode Efficiency Rating (100% Load) | 97% |
| Audible Noise | 45 dBA maximum, front side 1m |
| COMMUNICATIONS | |
| Network Monitoring Port Description | Supports detailed monitoring of UPS and site power conditions; 1 USB port and 1 DB9 serial port. |
| PowerAlert Software | Included |
| Communications Cable | USB and DB9 cabling included |
| WatchDog Compatibility | Supports Watchdog application, OS and hard-reboot restart options for remote applications |
| Communications Interface | DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled) |
| LINE / BATTERY TRANSFER | |
| Transfer Time | 4 ms (AC to Battery); 2 ms (Battery to AC) typical |
| Low Voltage Transfer to Battery Power (Setpoint) | 151 |
| High Voltage Transfer to Battery Power (Setpoint) | 282 |
| SPECIAL FEATURES | |
| Grounding Lug | Back panel grounding lug |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported |
| High Availability UPS Features | Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Expandable battery backup; Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection |
| Green Energy-Saving Features | Greater than 95% efficiency - GREEN UPS; Individually controllable load banks |
| STANDARDS & COMPLIANCE | |
| UPS Certifications | CE; Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances) |
| Certification Details | CE / IEC 62040-1, EN62040-2 (EMC) |
| WARRANTY | |
| Product Warranty Period (International) | 2-year limited warranty |
| Product Warranty Period (Mexico) | 2-year limited warranty |
| Product Warranty Period (Puerto Rico) | 2-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>