


# SmartRack 4U Vertical Wall-Mount Rack Bracket, Knock Down Version

MODEL NUMBER: SRWALLBRKT4UKD



Allows vertical mounting of rack-mount equipment up to 175 lb. in a closet or back office.

## Features

### Wall-Mount Bracket Allows Installation of a Rack-Mount Device Without a Rack

This SmartRack® 4U rack bracket is recommended for home offices and small businesses with a need for rack-mount equipment, but no available space on the premises for a standard wall-mount rack. The SRWALLBRKT4UKD provides open and unrestricted access to equipment and cabling, and hangs flush against the wall for unrestricted out-of-the-way access. It ships in an unassembled “knock down” version.

### Attaches to the Wall with User-Supplied Hardware

Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the SRWALLBRKT4UKD easily mounts to the wall of your back office or closet with user-supplied hardware. Wall-mounting holes are spaced 16 inches part to match standard wall-stud placement. You can also install the bracket horizontally beneath a desk or workbench for instant access.

### Compatible with Standard 19 in. 2-Post Rack Equipment

Hardware is included for mounting 4U rack equipment. The bracket’s horizontal mounting rails support square-hole mounting. The maximum load capacity is 175 pounds (79.4 kilograms).

## Highlights

- Ideal for installing rack-mount equipment without the cost of buying a rack
- Provides open, unrestricted access to all mounted equipment and cabling
- Black cold-rolled steel bracket hangs flush against the wall for out-of-the-way access
- Includes all necessary hardware for mounting equipment up to 175 lb.
- Knock-down version ships to you in an unassembled version

## Package Includes

- SRWALLBRKT4UKD 4U Vertical Wall-Mount Rack Bracket
- (12) M6 screws
- (12) M6 cup washers
- (12) M6 cage nuts
- Installation guide

## Specifications

OVERVIEW	
UPC Code	037332283214
Device Compatibility	Network Switch; Patch Panel
Rack Type	Bracket
PHYSICAL	
Color	Black
Rack Height	4U



Powering Business Worldwide

TRIPP LITE  
SERIES

Rack Depth	Shallow
Maximum Device Depth (cm)	121.92
Maximum Device Depth (in.)	48
Maximum Device Depth (mm)	1,219
Maximum Weight Capacity (lbs.)	175
Maximum Weight Capacity (kg)	79
Shipping Dimensions (hwd / in.)	21.46 x 9.84 x 2.56
Shipping Dimensions (hwd / cm)	54.51 x 24.99 x 6.50
Shipping Weight (lbs.)	8.75
Shipping Weight (kg)	3.97
Unit Dimensions (hwd / in.)	7.670 x 19.690 x 7.560
Unit Dimensions (hwd / cm)	19.46 x 50.01 x 19.46
Unit Weight (lbs.)	5.29
Unit Weight (kg)	2.40
Weight Capacity - Stationary (kg)	79
Weight Capacity - Stationary (lbs.)	175
Number of Vertical Mounting Rails	2
Assembly Required	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
Built-in Cable Management	No
Extra Wide	No
Locking	No
Pre-Installed Casters	No
Outdoor Use	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.