


# Protect It! Surge Protector with 6 Right-Angle Outlets, 6 ft. (1.83 m) Cord, 540 Joules, Diagnostic LED

MODEL NUMBER: **SPIKESTIK**



### Highlights

- 6 right-angle outlets
- 6-ft. (1.83 m) cord
- 540 joule rating

### Package Includes

- SPIKESTIK Surge Suppressor
- Child Safety Covers
- Instruction manual and Warranty information

### Description

The SPIKESTIK Surge Suppressor has six right-angle outlets and a six-foot (1.8 meters) cord. The unit has 540 joules of surge energy absorption to handle the strongest surges.

### Features

- 6 right-angle outlets
- 6-ft. (1.83 m) cord
- Surge energy absorption: 540 joules; 27,000 amps
- 15 amp circuit breaker
- EMI/RFI noise filtering
- Keyhole supports for wall mounting
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada & Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

OVERVIEW	
UPC Code	037332010292
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge



Powering Business Worldwide

**TRIPP-LITE**  
by **EATON**

Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Two position on/off power switch
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Surge Current Rating	27,000 amps
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic



Powering Business Worldwide



Power Cord Color	Gray
Housing Color	Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	114.6 mm
Outlets Measurement (Center to Center)	28.6mm
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	11.90 x 1.75 x 0.70
Shipping Dimensions (hwd / cm)	30.23 x 4.44 x 1.78
Shipping Weight (lbs.)	1.30
Shipping Weight (kg)	0.59
Unit Dimensions (hwd / in.)	10.250 x 2.700 x 1.520
Unit Dimensions (hwd / cm)	26 x 6.9 x 3.9
Unit Weight (lbs.)	1.25
Unit Weight (kg)	0.57
Input Cord Color	Gray
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 21 (Canada); CAN/CSA-C22.2 No. 269.3 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.