

SmartRack 12U Heavy-Duty Flat-Pack Low-Profile Switch-Depth Wall-Mount 2-Post Open Frame Rack

MODEL NUMBER: SRWO12UHD



Open frame rack stores 12U of 19-inch rack equipment up to 18 inches deep in network closets and other locations with limited floor space where a locked enclosure is not required. Allows easy access to equipment and cabling.

Description

The SRWO12UHD SmartRack 12U Heavy-Duty Flat-Pack Low-Profile Switch-Depth Wall-Mount 2-Post Open Frame Rack stores and organizes EIA-standard 19-inch rack equipment compatible with 2-post mounting in network wiring closets, back offices and other secure areas with limited floor space where a locked enclosure is not required. Constructed from heavy-duty steel with a durable black powder-coated finish, the rack has a maximum load capacity of 200 lbs (90.7 kgs).

The open frame design allows unrestricted access for installing, configuring and servicing equipment and cabling. The rack is simple to assemble and mount to the wall. Threaded 12-24 mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails accommodate equipment up to 18 inches deep, such as network switches and patch panels. Assembly and equipment-mounting hardware is included.

Features

Saves Valuable Workspace

- Perfect for network wiring closets, back offices and other secure areas with limited floor space where a locked enclosure is not required
- Stores and organizes EIA-standard 19 in. rack equipment compatible with 2-post mounting in 12U of space
- Maximum load capacity of 200 lbs (90.7 kgs)

2-Post Open Frame Design

- Allows easy access for installing, configuring and servicing equipment and cabling

Easy Assembly and Installation

- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Vertical mounting rails accommodate equipment up to 18 in. deep, such as network switches and patch panels

Highlights

- Maximum load capacity of 200 lbs (90.7 kgs)
- Allows easy access to equipment and cabling
- Stores 12U of 19 in. rack equipment up to 18 in. deep
- Simple to assemble and mount
- Assembly and equipment-mounting hardware included

Package Includes

- (24) 12-24 equipment mounting screws
- (8) M5 button-head cap screws
- (8) M6 x 12 Phillips-head screws
- (2) Support straps
- (2) Vertical mounting rails
- (2) Top/bottom panel frames
- 3 mm hex key
- Owner's manual

- Rails support threaded-hole equipment mounting
- Rack spaces numbered for easy reference
- Includes assembly and equipment-mounting hardware

Specifications

OVERVIEW	
UPC Code	037332182654
Device Compatibility	Patch Panel; Network Switch
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	12U
Rack Depth	Shallow
Maximum Device Depth (cm)	45.72
Maximum Device Depth (in.)	18
Maximum Device Depth (mm)	457
Shipping Dimensions (hwd / in.)	4.10 x 22.80 x 21.30
Shipping Dimensions (hwd / cm)	10.41 x 57.91 x 54.10
Shipping Weight (lbs.)	15.10
Shipping Weight (kg)	6.85
Unit Dimensions (hwd / in.)	24.800 x 20.110 x 18.240
Unit Dimensions (hwd / cm)	62,992 x 51,05 x 46,33
Unit Weight (lbs.)	14.3
Unit Weight (kg)	6.49
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

5-year limited warranty