

Adapter Kit for Mounting 19 in. Rack Equipment in 23 in. Racks

MODEL NUMBER: SR2319ADAPT



Highlights

- Attaches to rack's vertical mounting rails
- Includes mounting hardware
- Made from cold-rolled steel with black finish
- Maximum load capacity of 20 lbs (9.1 kgs)

Package Includes

- (2) Adapter brackets
- (4) M6 screws
- (4) M6 cage nuts
- (6) 12-24 screws
- Owner's manual

Attaches to a 23 in. rack in order to mount 19 in. rack equipment into it.

Description

The SR2319ADAPT Mounting Adapter Kit allows you to mount 19-inch rack equipment in a 23-inch rack. Attach the adapter brackets to the rack's vertical mounting rails using the included hardware. Then, attach 19-inch equipment to the brackets using the included hardware or your own. The cold-rolled steel brackets support a maximum load capacity of 20 lbs (9.1 kgs).

Features

Mount 19 in. Rack Equipment in a 23 in. Rack

- Adapter brackets attach to rack's vertical mounting rails
- Mounting hardware included
- Made from cold-rolled steel with black finish
- Maximum load capacity of 20 lbs (9.1 kgs)

Specifications

OVERVIEW	
UPC Code	037332188434
Product Type	Rackmount Kit
Accessories Type	Rackmount Kit
PHYSICAL	
Shipping Dimensions (hwd / cm)	3.00 x 8.00 x 4.50



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	1.18 x 3.15 x 1.77
Shipping Weight (kg)	0.16
Shipping Weight (lbs.)	0.35
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>