

## SmartRack 24U Standard-Depth Rack Enclosure Cabinet for Harsh Environments

MODEL NUMBER: SR24UBFFD



Ideal storage for sensitive rack-mounted equipment that needs extra protection from harsh conditions. Perfect for factories, construction areas, warehouses and other areas high in moisture, dust and debris. Fully compliant with IP54 standards.

### Description

The SR24UBFFD SmartRack 24U Standard-Depth Rack Enclosure Cabinet is ideal for storing sensitive 19-inch rack equipment in factories, power stations, water treatment plants, construction areas, shipping facilities, warehouses, transport hubs and other working environments high in moisture, dust and debris.

Constructed from heavy-duty steel in a durable black powder-coat finish, the SR24UBFFD supports a maximum load capacity of 1000 pounds. The louvered front door and built-in dust filters prevent drips, splashes and airborne contaminants from getting inside the enclosure. You can replace the filters with standard 20 x 24 x 1-inch furnace filters.

Eight high-performance fans are built into the door to pull air through the enclosure and keep your equipment cool. Dust- and drip-resistant top and bottom ports allow easy cable routing through the enclosure. To ensure your valuable equipment stays secure, the reversible front and rear doors and removable side panels lock tight.

The SR24UBFFD comes fully assembled and ready to use with removable casters and levelers for smooth deployment and placement. Installing equipment within the enclosure is easy with its square holes and numbered rack spaces. The front and rear vertical mounting rails adjust to accommodate equipment from 3 to 32.5 inches deep.

### Features

#### Ideal for Physically Tough Working Environments

- Perfect for factories, power stations, water treatment plants, construction areas, shipping facilities,

### Highlights

- Supports a maximum load capacity of 1000 lb.
- 8 high-performance fans keep equipment cool
- Built-in dust filters protect interior from airborne particles
- Louvered door keeps out drips, splashes and falling debris
- Adjustable mounting rails house equipment from 3 to 32.5 in. deep

### Package Includes

- SR24UBFFD SmartRack 24U Standard-Depth Rack Enclosure Cabinet
- (50) M6 cage nuts
- (50) M6 screws
- (50) Cup washers
- (2) Removable/replaceable dust filters
- (4) Casters
- (4) Leveling feet
- (1) C13 to NEMA 5-15 power cord, 10'
- (2) Keys
- Owner's manual



warehouses, transport hubs and other working environments high in moisture, dust and debris

- Houses standard 19 in. rack equipment in 24U of space
- Supports maximum load capacity of 1000 lb.

#### **Protects Against Harsh Conditions**

- 8 high-performance fans built into front door pull air through enclosure and cool equipment
- Louvered front door blocks drips, splashes and falling debris from entering enclosure
- Built-in dust filters keep out airborne contaminants
- Filters can be removed and replaced with standard 20 x 24 x 1 in. furnace filters
- Fans powered by detachable 10 ft. AC cord with NEMA 5-15P plug

#### **Keeps Important Equipment Secure**

- Reversible doors and removable side panels lock tight
- Convenient ports with removable covers allow cable routing through top and bottom

#### **Easy Enclosure and Equipment Installation**

- Ships fully assembled and ready to use
- Front and rear mounting rails accommodate equipment from 3 to 32.5 in. deep
- Rails adjust easily—unscrew them, slide them to desired depth, and screw them back in
- Rails support square-hole mounting
- Rack spaces numbered for easy reference
- Removable casters and levelers help with minor position adjustments and stabilization
- Mounting hardware included

#### **Meets Payment Card Industry Standards**

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

## **Specifications**

<b>OVERVIEW</b>	
UPC Code	037332188786
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Enclosure
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Nominal Input Voltage Description	120V 50/60 Hz
Input Plug Type	NEMA 5-15P



Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
<b>PHYSICAL</b>	
Color	Black
Factory Preset Rack Depth (cm)	26.5
Factory Preset Rack Depth (in.)	10.42
Factory Preset Rack Depth (mm)	265
Maximum Device Depth (cm)	82.55
Maximum Device Depth (in.)	32.5
Maximum Device Depth (mm)	826
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Rack Height	24U
Shipping Dimensions (hwd / cm)	130.35 x 63.50 x 100.51
Shipping Dimensions (hwd / in.)	51.32 x 25.00 x 39.57
Shipping Weight (kg)	110.00
Shipping Weight (lbs.)	242.50
Unit Dimensions (hwd / cm)	118.87 x 59.95 x 97.79
Unit Dimensions (hwd / in.)	46.8 x 23.6 x 38.5
Unit Weight (kg)	95.00
Unit Weight (lbs.)	209.43
Weight Capacity - Rolling (kg)	454
Weight Capacity - Rolling (lbs.)	1000
Weight Capacity - Stationary (kg)	454
Weight Capacity - Stationary (lbs.)	1000
Rack Depth	Mid
Number of Vertical Mounting Rails	4
<b>SPECIAL FEATURES</b>	
Grounding Lug	Front and back door frames
Built-in Cable Management	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Approvals	EIA-310-E, IEC 60297-3-100, IP54 Protection Rating, RoHS



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>