

UPS Maintenance Bypass Panel for Tripp Lite S3M100K, SV100KL and SV120KL 3-Phase UPS Systems - 3 Breakers

MODEL NUMBER: SU120KMBPK



UPS bypass panel reroutes power to keep essential equipment operational while the UPS is inoperative or under maintenance.

Features

UPS Maintenance Bypass Panel Keeps Equipment Powered During UPS Maintenance This wall-mount three-breaker maintenance bypass panel is compatible with Tripp Lite's S3M100K, SV100KL and SV120KL 3-phase UPS systems. It allows you to reroute power around the UPS, providing an alternate path for electricity that keeps the connected load operational while the UPS is offline for maintenance or repairs.

Features 3 Built-In Circuit Breakers to Isolate Loads Three circuit breakers – an AC input breaker, a maintenance bypass breaker and a maintenance isolation breaker – are connected to heavy-duty buswork and isolate the UPS system from its connected load with no loss of network availability. This allows the load to remain continuously powered without costly downtime. A Kirk-key interlock system enhances safety and security. Removable handles allow the panel's trim cover to be removed for internal access. The 400A unit has a kAIC rating of 10K.

Switching Between Normal and Bypass Modes Is Easy When a UPS needs maintenance, this UPS bypass panel keeps power supplied to components via its mechanical interlock system by switching power to the external bypass breaker. Simply unscrew the interlock switch, rotate the switch from the UPS AC input breaker (SW1) to the bypass breaker (SW2), then turn on the bypass breaker and turn off the UPS and isolation breaker (SW3) to perform UPS maintenance without service interruption.

Convenient Wall-Mount Installation Made of galvanized steel, the service bypass panel has rear mounting holes for installation on a smooth, solid wall (mounting hardware not included).

Specifications

OVERVIEW	
UPC Code	037332241054

Highlights

- Isolates UPS from connected loads for maintenance without losing network availability
- Maintenance bypass panel mounts to wall next to UPS for convenient access
- 400A 10 kAIC unit has 3 built-in circuit breakers connected to heavy-duty buswork
- Secure Kirk-key interlock system prevents unauthorized access to power
- Compatible with Tripp Lite S3M100K, SV100KL and SV120KL 3-phase UPS systems

Applications

- Bypass a compatible offline 3-phase UPS system to continue powering mission-critical equipment without interruption

System Requirements

- Tripp Lite S3M100K, SV100KL and SV120KL 3-phase UPS system

Package Includes

- SU120KMBPK UPS Maintenance Bypass Panel - 3 Breakers
- Installation and Operation Manual



Product Type	Bypass Panel
Accessories Type	Bypass Panel
INPUT	
Nominal Input Voltage(s) Supported	120/208V 3-PH Wye
Voltage Compatibility (VAC)	120
PHYSICAL	
Form Factors Supported	Wallmount
Shipping Dimensions (hwd / cm)	91.44 x 106.68 x 35.56
Shipping Dimensions (hwd / in.)	36.00 x 42.00 x 14.00
Shipping Weight (kg)	71.67
Shipping Weight (lbs.)	158.00
Unit Dimensions (hwd / cm)	80.1 x 97.7 x 19.1
Unit Dimensions (hwd / in.)	31.5 x 38.5 x 7.8
Unit Weight (kg)	49.90
Unit Weight (lbs.)	110
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>