

## SmartOnline 3000VA 2700W 120V Double-Conversion UPS - 7 Outlets, Extended Run, Network Card Included, LCD, USB, DB9, 2U Rack/Tower

MODEL NUMBER: **SU3000RTXLCD2UN**



Provides pure sine wave output in education, healthcare, military, government and other IT applications in small or mid-size networks.

### Features

#### Double-Conversion UPS Protects Equipment Against Damage, Downtime and Data Loss

This on-line double-conversion UPS system maintains perfect output by converting AC input to DC, then re-converting UPS output to fully regulated sine wave AC. Constant on-line operation completely isolates sensitive equipment from every power problem on the AC line. The SmartOnline® SU3000RTXLCD2UN provides the highest level of power protection and battery backup for education, healthcare, military, government and other mission-critical IT applications where space is limited, but premium power reliability is essential.

#### Reliable, Expandable Battery Backup Keeps You Operational Through Power Outages

The field-replaceable, hot-swappable VRLA battery modules allow you to work through short power failures and give you enough time to safely save files and shut down your system in case of a prolonged blackout. Zero transfer time between on-line and battery modes maintains continuous operation of connected equipment without interruption or rebooting. Extra runtime is available by connecting up to four optional extended battery modules (BP72RT, sold separately).

#### Pre-Installed LX Platform Network Management Card Allows Remote Access 24/7

The WEBCARDLXE network interface enables full remote configuration and management, including load shedding, reboots of connected equipment and safe shutdowns. The IP-based Auto Probe feature ensures continuous network uptime by communicating with other network devices, detecting lost connectivity and automatically rebooting IT equipment. Optional EnviroSense2 modules (E2MT, E2MTDO and E2MTHDI, all sold separately) provide a variety of environmental monitoring and control options.

#### NEMA Outlets Protect Your Connected Components

One L5-30R and six 5-20R outlets provide connected equipment with pure sine wave AC output and allow you to manage power consumption down to the outlet group level. Power provided by these outlets is filtered to protect connected equipment against damaging surges and line noise. Four 5-20R outlets are grouped into two load banks that let you shed non-critical loads to extend runtime for critical loads.

#### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

### Highlights

- Updated design for 2023
- Protects equipment against blackouts, brownouts, transient surges and line noise
- Keeps equipment running during outages to allow time for file saves and safe shutdown
- Zero transfer time between on-line and battery modes for uninterrupted operation
- Included WEBCARDLXE network card enables full remote access and control 24/7
- Menu-driven LCD keeps you up to date with status info and other vital analytics

### Package Includes

- 3000VA 2700W 120V Double-Conversion UPS
- WEBCARDLXE network management card
- USB cable
- DB9 cable
- Rack-mounting hardware
- Tower support stands
- Safety instructions
- Quick start guide

This UPS system filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

#### Clear LCD Interface Keeps You Informed at a Glance

The menu-driven front-panel LCD provides detailed alarms and notifications to help diagnose any issues. It provides system status, event logs, battery and power module status, usage analytics, serial number, firmware update info and more. Audible alarms can be disabled through the front menu when the UPS goes to battery power. The LCD rotates to accommodate both rack-mount and tower installation.

#### Advanced Communications Ports Allow for Automatic Saves and Shutdowns

RS-232 and USB ports connect to a device for a variety of communication options (cables are included). A dry-contact relay port can be programmed through the LCD to provide reliable communications to automation and industrial components. The RPO/ROO port permits emergency shutdown or remote restart of all connected equipment.

#### Automatically Turns Back On After Power Is Restored

Battery-independent restart ensures automatic UPS power-up without user interaction after lengthy power outages, even after a complete battery discharge.

#### Versatile Installation Options

You can mount the SU3000RTXLCD2UN in just 2U of space in an EIA-standard 19-inch rack using the included hardware. You can also adapt it for tower installation using the included support stands or add the optional RK2PC (sold separately) for 2-post rack mounting. The eight-foot power cord with NEMA L5-30P plug connects to a compatible AC outlet.

## Specifications

OVERVIEW	
UPC Code	037332253552
UPS Type	On-Line
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	24A
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 120V AC
Nominal Input Voltage Description	120V factory default
UPS Input Connection Type	L5-30P
UPS Input Cord Length (ft.)	8
UPS Input Cord Length (m)	2.4
Recommended Electrical Service	120V
Plug Type	L5-30P
Input Cord Length (ft.)	8
Input Cord Length (m)	2.44
Input Current	24A
Power Factor (Input)	0.99





Minimum Required Rack Depth (inches)	26.8
Optional Mounting Accessory Notes	2 post rail kit available, part # <a href="/tripplite.eaton.com/eaton-2-post-rack-mount-rail-kit-for-9px-ups~RK2PC">RK2PC</a>
Shipping Dimensions (hwd / in.)	9.45 x 22.84 x 30.71
Shipping Weight (lbs.)	77.83
Shipping Weight (kg)	35.30
UPS Housing Material	Metal
Unit Dimensions (hwd / in.)	3.410 x 17.330 x 23.820
Unit Weight (lbs.)	63.06
Unit Weight (kg)	28.60
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	With battery: 32° to 104°F (0° to 40°C); without battery: -13° to 131°F (-25° to 55°C)
Relative Humidity	0 to 96%, non-condensing
AC Mode Efficiency Rating (100% Load)	91.6
AC Economy Mode Efficiency Rating (100% Load)	97.2
Online Mode Heat Dissipation (BTU/Hr) @ Full Load	844
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	1462
Audible Noise	47 dB at 1m
Operating Elevation (m)	Up to 3000m
<b>COMMUNICATIONS</b>	
Network Management Cards	(1) <a href="/tripplite.eaton.com/Network-Card-Eaton-Tripp-Lite-Series-UPS-Systems~WEBCARDLXE">WEBCARDLXE</a>
Network Monitoring Port Description	WEBCARDLXE Supports detailed monitoring of UPS and site power conditions; DB9 port supports RS232 and contact closure communications; not compatible with WEBCARDLX
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	USB and RS232 cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management card included
Communications Interface	(1) Included network card; (1) RS-232; (1) USB
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	0ms

FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Expandable battery backup; Hot swappable batteries; On-Line/Double-Conversion; Pure sine wave output; Remote management; Surge/noise protection; Zero transfer time
Green Energy-Saving Features	High efficiency economy mode operation; Individually controllable load banks
APPLICATIONS	
UPS Applications	Mission Critical Applications
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	CE (Europe); ENERGY STAR Qualified; FCC (USA); REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>
Extended Service Plans	<b>ADVANCED DEPOT EXCHANGE</b> Service Part Number: TL9SW5Y-3000UCParts, electronics and UPS batteries coverageNext business day shippingTechnical support <b>5-year onsite plan: TLWFLN75XX-6009UC</b> Onsite parts and labor coverage for 5 yearsParts, electronics and UPS batteries coverage24x7 onsite labor coverage, next-day responseNext-day shippingTechnical support