


SmartRack 6U Wall Mount Mini Rack Enclosure, Low-Profile, Switch-Depth

MODEL NUMBER: SRW6U



6U wall mount rack secures and organizes network switches in closets, classrooms and other locations with limited floor space. Accommodates switches and patch panels up to 16.5 inches deep.

Description

Tripp Lite's SRW6U 6U network rack is designed to house EIA-standard 19-inch rack equipment in home and office network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, this wall mount switch rack has a maximum load capacity of 200 pounds (90.7 kilograms).

The side panels and front door lock securely to help prevent damage, tampering or theft. The front, top, bottom and removable side panels are vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right by rotating the cabinet 180° before mounting. Convenient top and bottom ports allow easy cable routing.

The SRW6U comes fully assembled and ready to mount to the wall, or use Tripp Lite's optional SRCASTER rolling caster kit to make it a mobile rack. Square and 12-24 threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments to accommodate equipment up to 16.5 inches deep, such as network switches and patch panels.

Features

Saves Valuable Workspace

Ideal for home and office network wiring closets, retail locations, classrooms and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Houses EIA-standard 19 in. rack equipment in 6U of space. Maximum load capacity of 200 lb. (90.7 kg)

Keeps Important Equipment Secure

Side panels and front door lock securely to help prevent damage, tampering or theft. Vented panels allow generous airflow that keeps equipment cool. Rotate cabinet 180° before mounting to open reversible front door left or right. Convenient ports with removable covers allow cable routing through top and bottom.

Easy Enclosure and Equipment Installation

Ships fully assembled for quick installation. Mounts to wall or rolls on floor with Tripp Lite's optional SRCASTER caster kit. Wall-mounting holes spaced 16 in. apart for standard wall stud placement. Vertical mounting rails adjust in 7/8 in. increments to accommodate equipment up to 16.5 in. deep, such as network switches and patch panels. Rails support square-hole or 12-24 threaded-hole mounting. Rack spaces numbered for easy reference.

Highlights

- Maximum load capacity of 200 lb. (90.7 kg)
- Locking steel cabinet vented at sides, front, top and bottom
- Flow-through ventilation keeps equipment cool
- Secures 6U of 19 in. rack equipment up to 16.5 in. deep
- Mounts to wall or rolls on floor (with optional SRCASTER)

Package Includes

- SRW6U SmartRack 6U Low-Profile Switch-Depth Wall-Mount Rack Enclosure
- (12) M6 screws
- (12) M6 cage nuts
- (12) M6 cup washers
- (12) 12-24 screws
- Removable mounting plate
- (3) Mounting plate screws
- (2) Keys
- Owner's manual



Meets Payment Card Industry Standards

Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332154651
Device Compatibility	Patch Panel; Network Switch; UPS
Rack Type	Small Enclosure
PHYSICAL	
Color	Black
Rack Height	6U
Rack Depth	Shallow
Maximum Device Depth (cm)	41.91
Maximum Device Depth (in.)	16.5
Maximum Device Depth (mm)	419
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Shipping Dimensions (hwd / in.)	17.50 x 20.60 x 26.40
Shipping Dimensions (hwd / cm)	44.45 x 52.32 x 67.06
Shipping Weight (lbs.)	34.00
Shipping Weight (kg)	15.42
Unit Dimensions (hwd / in.)	14.5 x 23.63 x 17.5
Unit Dimensions (hwd / cm)	36.83 x 60 x 44.45
Unit Weight (lbs.)	29
Unit Weight (kg)	13.15
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	2
FEATURES & SPECIFICATIONS	
Extra Wide	No



Grounding Lug	Front and Back door frames
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 60950-1
Product Compliance	RoHS; EIA/ECA-310-E; UKCA
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>