

208V 5000VA 5000W On-Line UPS, Unity Power Factor with Bypass PDU and 120V Transformer, Hardwire/L6-30P Input, 5U

MODEL NUMBER: SU5KRT3UTFMB



Double-conversion UPS with detachable PDU and maintenance bypass switch provides fulltime sine wave output for advanced network applications.

Features

Protects Mission-Critical Rack-Mounted Equipment against Damage, Downtime and Data Loss

Tripp Lite's SmartOnline® SU5KRT3UTFMB Unity Power Factor UPS system with Maintenance Bypass Switch and Detachable PDU protects connected equipment against damage, downtime and data loss due to power outages, voltage fluctuations and transient surges. Unity Power Factor design enables full 5000VA / 5000W output capacity when used with hardwire 208V input power (output de-rates to 4800W with included L6-30P cord option). In double-conversion mode, this UPS system maintains perfect output by continuously converting AC input to DC, then reconverting UPS output to fully regulated sine wave AC with $\pm 1\%$ voltage regulation and zero transfer time between online and battery modes. Featuring true on-line, double-conversion operation, Tripp Lite's SU5KRT3UTFMB provides the highest level of UPS power protection for critical server, network and telecom equipment.

High Availability Configuration Offers Reliable, Expandable Battery Backup Included Maintenance Bypass Switch is mounted on a detachable Bypass PDU that securely mounts to the rear-rails of a 4 post rack enclosure and remains safely in-place powering your equipment during UPS maintenance. The UPS connects to the Bypass PDU using a sophisticated blind-mate connector set with self-aligning guide-pins to ensure safe and reliable whole-UPS replacement with zero downtime for connected equipment. UPS battery backup keeps connected equipment operational through short power failures, and provides time to save data and perform an orderly system shutdown in case of a prolonged blackout. The internal battery set provides 14 minutes of support at half load and 5 minutes at full load. During normal operation, incoming utility power keeps the battery fully charged so backup power will be available when needed. Advanced temperature-controlled battery charge management system provides efficient recharge and enhanced battery lifespan. For mission critical applications demanding continuous uptime, the 5kVA UPS can provide expandable runtime with optional BP192V12RT3US external battery pack (sold separately). Battery-independent restart ensures automatic UPS power-up after lengthy power outages, even with expired batteries.

Economy Mode Helps the Environment and Your Cash Flow Operates with >98% full-load efficiency in optional economy mode significantly reducing BTU heat output and operating energy costs.

Intuitive Front-Panel Interface offers Convenient Monitoring Front-panel LEDs indicate line power, AC output, On-battery mode, and Fault conditions. The LCD readout with scroll controls supports visual

Highlights

- Unity (1.0) power factor equalizes VA and wattage to safely support more equipment
- Zero transfer time between on-line and battery modes for uninterrupted operation
- Detachable PDU with maintenance bypass switch allows convenient hot-swapping
- Pre-installed WEBCARDLXMINI network interface supports Auto Probe feature
- Step-down transformer converts 208V input into 120V output for low-voltage equipment

Applications

- Delivering perfectly regulated sine wave output to mission-critical equipment
- Protecting connected components from dangerous surges, spikes and line noise
- Keeping equipment operational through short power failures
- Allowing time to save data and safely shut down components in case of a prolonged blackout

Package Includes

- On-line double-conversion UPS
- Pre-installed WEBCARDLXMINI network management card
- Detachable bypass PDU
- Step-down transformer
- (2) Hardwire strain reliefs
- USB cable
- RS-232 cable
- L6-30P power cable
- Rack-mounting hardware
- Owner's manual

monitoring of a variety of control options to support advanced UPS settings and configurations. The panel rotates for comfortable viewing in rack-mount or tower configuration.

Pre-installed WEBCARDLXMINI Network Interface Offers 24/7 Access Pre-installed Java-free HTML5-based WEBCARDLXMINI interface enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Automated alerts help prevent accidental overloads, power loss and downtime. Advanced Communications Ports USB and DB9 ports with included cabling enable data-saving unattended shutdown of connected systems when used with Tripp Lite's free downloadable PowerAlert® software. Capabilities include detailed monitoring of load levels, self-test data and utility power conditions. DB9 ports also support basic contact-closure monitoring to report On-battery and Low-battery status for legacy systems.

Versatile Installation Options Hardware is included for mounting the complete 5kVA UPS system with internal batteries in 3U of space in an EIA-standard 19-inch 4-post rack. Use the optional 2POSTRMKITHD for 2-post rack mounting or the optional 2-9USTAND for mounting in an upright tower position.

2-Year Warranty, \$250K Ultimate Lifetime Insurance and Environmentally Responsible Design The SU5KRT3UTFMB comes with a 2-year warranty and \$250,000 of Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only). It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Specifications

OVERVIEW	
UPC Code	037332237965
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	Hardwire AC input: 25.6A (208V) maximum; With included NEMA L6-30P input: 24A (208V) maximum; Max inrush current: 100A
Nominal Input Voltage(s) Supported	208V AC
Nominal Input Voltage Description	208V factory default
UPS Input Connection Type	Hardwire; L6-30P
UPS Input Connection Description	Hardwire input supports 3 wire L1, L2/N, PE(GND) input configurations; Includes optional L6-30P input cable
Input Phase	Single-Phase
Input Frequency	60 Hz
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Power Factor (Input)	0.98 minimum (full load, nominal input voltage)
THDi	<8% full load; <10% half load
OUTPUT	
Output Capacity (VA)	5000

Output Capacity (kVA)	5
Output Capacity (Watts)	5000
Output Capacity (kW)	5
Output Capacity Details	Supports 5000VA / 5000W with hardwire AC input; Maximum output capacity de-rates to 4800W (208V) when used with included L6-30P AC input cord; Inverter supports up to 104% load continuously, Up to 125% / 150% for 1.0 / 0.5 min. before bypass transfer (when available) or shutdown; Loads greater than 150% trigger immediate shutdown; AC TRANSIENT RESPONSE: $\pm 1.5\%$ RMS of initial value (between 10% & 90% load step)
Power Factor	1.0
Crest Factor	3:1 maximum
Nominal Voltage Details	Nominal output voltage selection is available via front panel LCD interface; 208V 60Hz output settings required for transformer compatibility
Frequency Compatibility	60 Hz
Frequency Compatibility Details	MAX-QUALITY/MAX-EFFICIENCY/AUTO-ADAPTIVE MODES: Output frequency matches 60Hz input nominal on startup and tracks input frequency up to $\pm 3\text{Hz}$ of nominal; When input frequency is greater than $\pm 3\text{Hz}$ of nominal, output frequency is inverter regulated to $\pm 0.5\text{Hz}$ of nominal; BATTERY MODE: Output frequency is inverter regulated to $\pm 0.5\text{Hz}$ of the configured nominal output frequency; FREQUENCY REGULATION MODE: Enables 60Hz frequency correction to $\pm 0.5\text{Hz}$ (no de-rating, bypass is available when input frequency is within $\pm 0.5\text{Hz}$ of output)
Load Management Receptacles	Two built-in switchable output load banks; BANK 1 (Set of 2 L6-30R outlets); BANK 2 (Set of 2 L6-20R outlets)
Output Circuit Breakers	Output Circuit Breakers 30A double-pole breaker protects 2 L6-30R outlets; 20A double-pole breaker protects 2 L6-20R outlets; Set of 4 single-pole breakers protect 3 5-15R outlets each
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120V; 208V
Output Receptacles	(12) 5-20R; Hardwire; (2) L6-20R; (2) L6-30R
Output Voltage Regulation	$\pm 1\%$ Inverter output; $\pm 10\%$ Economy mode; $\pm 15\%$ Bypass mode (configurable from $\pm 5\%$ to $\pm 20\%$); Output voltage THD $< 2\%$ (full load) / $< 3\%$ (half load)
Individually Controllable Load Banks	Yes
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	5 min. (5000W)
Runtime Half Load (min.)	14 min. (2500W)
Expandable Runtime	Yes
Expandable Runtime Description	Up to 4 external battery packs with sensor cabling are automatically sensed and configured for advanced temperature controlled charging and accurate runtime reporting; Configurations using 5-10 external battery packs are supported, but may require the use of Tripp Lite's EXTERNAL BATTERY CONFIGURATION software for full integration
External Battery Pack Compatibility	 BP192V12RT3US
DC System Voltage (VDC)	192
Battery Recharge Rate (Included Batteries)	3 hours from 10% to 90% (typical, internal batteries with full load discharge); Charge settings: 1.5A (internal batteries) / 2A (with external battery packs) configures automatically; Supports temperature compensated battery charging

Primary UPS Width (mm)	445
Shipping Dimensions (hwd / in.)	33.75 x 33.40 x 24.00
Shipping Weight (kg)	111.58
Bypass PDU Dimensions (hwd / cm)	13.03 x 29.46 x 25.4
Bypass PDU Dimensions (hwd / in.)	5.13 x 11.6 x 10
Stepdown Transformer Dimensions (hwd / cm)	8.89 x 44.45 x 52.70
Stepdown Transformer Dimensions (hwd / in.)	3.5 x 17.5 x 20.75
Stepdown Transformer Height (mm)	89
Stepdown Transformer Width (mm)	445
Stepdown Transformer Depth (mm)	527
Stepdown Transformer Weight (kg)	28.80
Stepdown Transformer Weight (lbs.)	63.5
Unit Dimension Details	Minimum required rack depth assumes 127mm / 5 in. additional depth for AC input/output cabling; See submittal drawing for additional dimension detail
UPS Housing Material	Sheet metal
UPS Power Module Dimensions (hwd, in.)	8.75 x 17.5 x 35.5
UPS Power Module Weight (kg)	52.34
UPS Power Module Weight (lbs.)	115.4
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	5 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	1050
AC Mode Efficiency Rating (100% Load)	>94%
AC Economy Mode Efficiency Rating (100% Load)	>98%
Operating Elevation (ft.)	Up to 6562 ft.
Audible Noise	67.1dB (full load) / 53dB (no load) front side 1m
Operating Elevation (m)	Up to 2000m
COMMUNICATIONS	
Network Management Cards	 WEBCARDLXMINI
Network Monitoring Port Description	Includes Pre-installed WEBCARDLXMINI network management card; DB9 port supports RS-232 and Contact-closure signaling

PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at https://www.tripplite.com/poweralert
Communications Cable	USB, DB9 serial and EPO cables included
WatchDog Compatibility	Yes
Network Management Card Description	Network management card included
Communications Interface	Contact closure; DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	Online to Battery mode: 0 ms. (Zero transfer time)
Transfer Time (Economy Mode)	Online to Eco mode: 2 milliseconds / Eco to Battery mode: 8 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	156V (full load) / 100V (50% load or less, derates linearly)
High Voltage Transfer to Battery Power (Setpoint)	275V
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLXMINI); Automatic inverter bypass; Hot swappable UPS power module; Hot swappable batteries; Manual bypass switch; On-Line/Double-Conversion; Surge/noise protection; Zero transfer time
Green Energy-Saving Features	High efficiency economy mode operation; Individually controllable load banks; Schedulable daily hours of economy mode operation; Support for daily startup and shutoff
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; ENERGY STAR Qualified; FCC Part 15 Class A (USA); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance