

## SmartOnline 120V 1.5kVA 1.2kW Double-Conversion UPS, 2U Rack/Tower, Extended Run, Network Card Options, USB, DB9 Serial

MODEL NUMBER: SU1500RTXL2UA



### Description

Requiring only two rack spaces (2U) in a standard rack enclosure, Tripp Lite's SU1500RTXL2Ua SmartOnline UPS System protects connected equipment against data loss, downtime and equipment damage due to power outages, voltage fluctuations and transient surges. Featuring true on-line operation with pure sine wave output and zero transfer time to battery, it provides the highest level of power protection for mission-critical equipment. Internal batteries support connected equipment during blackouts, and runtime is expandable with optional external battery packs. The SU1500RTXL2Ua has six outlets arranged in two individually controllable load banks that can be used to reboot select equipment on demand or maximize battery runtime for mission-critical equipment. USB and DB9 communication ports support messaging of detailed UPS operational parameters and line power status. Included PowerAlert UPS monitoring and unattended shutdown software provides management support for an unlimited number of network UPS systems.

### Features

- SmartOnline high-performance UPS system is ideal for critical voice, data, medical and industrial network applications
- True on-line, double-conversion UPS provides perfectly regulated sine wave output within 2% of 120V under all usage conditions
- Maintains continuous operation through blackouts, voltage fluctuations and surges with zero transfer time
- Highly efficient operation in optional economy mode setting, saving BTU heat output and energy costs
- Removes harmonic distortion, fast electrical impulses, frequency variations and other hard to solve power problems not addressed by other UPS types
- Corrects line voltage conditions as low as 65V and as high as 150V back to 120V (+/-2%) values
- Standard internal battery set offers 14 min. runtime at half load (600W) and 5 min. at full load (1200W)
- Extended runtime available with optional BP48V24-2U (limit 1), BP48V60RT-3U (multi-pack compatible) and BP48V27-2US (multi-pack compatible) external battery packs
- Some external battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Intelligent battery management system extends battery life
- Compact rackmount form factor installs using only 2 rack spaces (2U) with a maximum installed depth

### Highlights

- 1500VA / 1.5kVA / 1200 watt on-line double-conversion 2U rack/tower UPS
- 120V +/-2% output at 50/60Hz, high efficiency economy mode option
- Expandable runtime, Hot-swap batteries; 19 in / 48.3cm installed depth
- USB, RS232 & EPO ports; support for network card options
- Front panel status LEDs with detailed load and battery metering
- 2 independently switchable output load banks
- NEMA 5-15P input; 5-15R outlets
- To use the Auto Probe feature, this product requires a WEBCARDLX network interface (sold separately) running LX firmware update 15.5.2 or later

### Package Includes

- SU1500RTXL2Ua UPS System
- 1 x 6-ft. USB Cable
- 1 x 6-ft. DB9 Cable
- 4-Post Rackmounting Hardware
- Owner's Manual

of only 19 in.

- Ships with all mounting accessories for 4-post rackmount installation
- Optional 2POSTRMKITWM enables 2-post rackmount or wallmount installation
- Optional 2-9USTAND accessory enables small-footprint upright tower placement
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Network interfaces support simultaneous communications via built-in USB, DB9 serial / contact-closure and slot for network management card options
- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX, SNMPWEBCARD, MODBUSCARD and RELAYIOCARD
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Included PowerAlert UPS monitoring software supports safe unattended shutdown, monitoring and control via local connected servers, plus any number of additional servers over IP
- UPS interface supports on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery capacity, AC line frequency, timed inverter shutoff, activate self-test, load bank output power control and remote reboot, UPS nominal voltage adjustment and UPS line to battery power voltage setpoints
- Built-in Emergency Power Off (EPO) interface with cable
- NEMA 5-15P input plug; NEMA 5-15R output receptacles
- Integrated 2-bank switched PDU enables remote outlet management for load shedding or remote reboot of individual load banks (bank one has 2 outlets, bank two has 4 outlets)
- Front panel LEDs offer current monitoring and battery charge level information
- UPS ships fully assembled in full compliance with DOT regulations; no time-consuming connection of internal batteries by user required
- Single-line tel/DSL or network Ethernet surge suppression
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332125972
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	20A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
Input Frequency	50/60Hz +/-5%

<b>OUTPUT</b>	
Output Capacity (VA)	1500
Output Capacity (kVA)	1.5
Output Capacity (Watts)	1200
Output Capacity (kW)	1.2
Output Capacity Details	OVERLOAD CAPACITY: Supports inverter operation up to 105% load continuously, 125% load for 3 minutes; 150% load for 30 seconds and >150% load for 0.5 seconds before switching to BYPASS (when bypass input voltage and frequency are WITHIN bypass limits) or SHUTDOWN (when bypass input voltage or frequency are OUTSIDE bypass limits)
Power Factor	0.8
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Output frequency matches input nominal on startup, defaults to 60 Hz on cold-start
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Economy Line Mode)	+/- 10%
Output Voltage Regulation (Battery Mode)	+/- 2%
Load Management Receptacles	Two switchable 5-15R load banks (bank 1 - two outlets, bank 2 - four outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	Yes
<b>BATTERY</b>	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	5 min. (1200W)
Runtime Half Load (min.)	14 min. (600W)
Expandable Runtime	Yes
External Battery Pack Compatibility	&nbsp;<a class="productLink" href="//tripplite.eaton.com/External-48V-2U-Rack-Tower-Battery-Pack-Enclosure-DC-Cabling-select-UPS-Systems~BP48V24-2U">BP48V24-2U</a>&nbsp; (limit 1); &nbsp;<a class="productLink" href="//tripplite.eaton.com/External-48V-3U-Rack-Tower-Battery-Pack-Enclosure-DC-Cabling-select-UPS-Systems~BP48V60RT-3U">BP48V60RT-3U</a>&nbsp; (multi-pack compatible); &nbsp;<a class="productLink" href="//tripplite.eaton.com/External-48V-2U-Rack-Tower-Battery-Pack-for-UPS-Systems~BP48V27-2US">BP48V27-2US</a>&nbsp; (multi-pack compatible)
DC System Voltage (VDC)	48
Battery Recharge Rate (Included Batteries)	Less than 6 hours from 10% to 80% (typical, full load discharge)

Battery Access	Front panel battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//tripplite.eaton.com/2U-UPS-Replacement-48VDC-Battery-Cartridge-1-set-4-select-Tripp-Lite-SmartPro-UPS~RBC94-2U">RBC94-2U</a>&nbsp;</td>
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	2% output voltage regulation during overvoltages to 150
Undervoltage Correction	2% output voltage regulation during undervoltages to 80
Severe Undervoltage Correction	2% output voltage regulation during undervoltages to 65 (under 70% load only)
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
LED Indicators	14 LEDs indicate line power, online mode, economy/bypass mode, on-battery, overload, battery low, replace battery and fault status information; 4-LED meter displays load and battery charge levels; LED panel rotates for viewing in rack/tower formats
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	600
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount
Rack Height	2U
Cooling Method	Fan
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (&nbsp;<a class="productLink" href="//tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a>&nbsp;</td>
Minimum Required Rack Depth (cm)	55.88

Minimum Required Rack Depth (inches)	22
Minimum Required Rack Depth with External Battery Pack (cm)	66
Minimum Required Rack Depth with External Battery Pack (in.)	26
Minimum Required Rack Depth without External Battery Pack (cm)	56
Minimum Required Rack Depth without External Battery Pack (in.)	22
Optional Mounting Accessory Notes	Optional <a href="//tripplite.eaton.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> enables upright tower UPS placement; <a href="//tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> enables wall-mount and 2-post rackmount installation; <a href="//tripplite.eaton.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4POSTRAILKITWM</a> enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); <a href="//tripplite.eaton.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT">UPSHDEARKIT</a> enables installation in 2 or 4-post racks using front vertical rails only, without rear support
Primary UPS Depth (mm)	483
Primary UPS Height (mm)	89
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / in.)	9.20 x 23.40 x 19.50
Shipping Dimensions (hwd / cm)	23.37 x 59.44 x 49.53
Shipping Weight (lbs.)	61.60
Shipping Weight (kg)	27.94
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.89 x 44.45 x 48.26
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.5 x 19
UPS Power Module Weight (kg)	20.00
UPS Power Module Weight (lbs.)	44.1
Unit Weight (lbs.)	44.0000
Unit Weight (kg)	19.96
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	612
AC Economy Mode BTU / Hr. (Full Load)	216
Battery Mode BTU / Hr. (Full Load)	667

AC Economy Mode Efficiency Rating (100% Load)	95%
<b>COMMUNICATIONS</b>	
Network Management Cards	SNMPWEBCARD; &nbsp;<a class="productLink" href="//tripplite.eaton.com/Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems-TLNETCARD">TLNETCARD</a>&nbsp;; &nbsp;<a class="productLink" href="//tripplite.eaton.com/Web-Management-Accessory-Card-WEBCARDLX">WEBCARDLX</a>&nbsp;; &nbsp;<a class="productLink" href="//tripplite.eaton.com/MODBUS-Management-Accessory-Card-UPS-Remote-Monitoring-Control-MODBUSCARD">MODBUSCARD</a>&nbsp;; &nbsp;<a class="productLink" href="//tripplite.eaton.com/Programmable-Relay-I-O-Card-RELAYIOCARD">RELAYIOCARD</a>&nbsp;;
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; DB9 port supports RS232 and contact closure communications; Economy-mode setting option is available using PowerAlert software and DB9 Serial cable connection OR via select Network Management Card options
PowerAlert Software	For local monitoring via the UPS's built-in communication ports , download PowerAlert Local software at <a href="https://www.tripplite.com/poweralert">https://www.tripplite.com/poweralert</a>
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management card optional
Communications Interface	Contact closure; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	80V (100% load), 65V ( <70% load)
High Voltage Transfer to Battery Power (Setpoint)	150
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic inverter bypass; Hot swappable batteries; Remote management; Surge/noise protection; Zero transfer time
Green Energy-Saving Features	High efficiency economy mode operation; Individually controllable load banks; Schedulable daily hours of economy mode operation
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; FCC Part 15 Class A (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000&nbsp;<a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;;



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.