



SmartOnline 120V 750VA 600W Double-Conversion UPS, 2U Rack/Tower, Extended Run, Pre-installed WEBCARDLX Network Interface, USB, DB9 Serial

MODEL NUMBER: SU750RTXL2UN





Description

750VA online, double-conversion UPS system for critical server, network and telecommunications equipment. 2U rackmount form factor with an installed depth of only 13.5 inches. Extended runtime available with optional BP24V15RT2U (limit 1), BP24V28-2U (limit 1), BP24V70-3U (multi-pack compatible) and BP24V36-2US (multi-pack compatible) external battery packs. Full-time sine wave 120V output with +/-2% voltage regulation. Online, double-conversion Uninterruptible Power Supply (UPS) actively converts raw incoming AC power to DC, then re-converts output back to completely regulated, filtered AC output. Operates continuously without using battery power during brownouts to 65V and overvoltages to 150. NEMA 5-15P input plug; NEMA 5-15R output receptacles. Network-grade AC surge and noise suppression. Zero transfer time between AC and battery operation. Network management interfaces support simultaneous communications via USB port, DB9 serial port and pre-installed WEBCARDLX Network Interface. Built-in DB9 port offers both enhanced RS-232 enabled monitoring data, plus contact closure monitoring ability. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces. PowerAlert monitoring software is available via free download. Emergency Power Off (EPO) interface. Integrated two-bank PDU switching supports load shedding and remote reboot of connected equipment. 3-stage metered current monitoring and battery charge status LEDs. LED display panel easily rotates for viewing in rackmount or tower configurations. Dataline surge suppression for dialup, DSL or network Ethernet connection. Utility power and voltage regulation LEDs. Audible alarm. Self-test. Fault-tolerant auto-bypass mode. 4-post rackmount accessories included; 2-9USTAND tower kit and 2POSTRMKITWM 2-post rack & wallmount accessories available. Field-replaceable, hot-swappable internal batteries and external battery packs. \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- SmartOnline high-performance UPS system is ideal for critical voice, data, medical and industrial network applications
- True online, double-conversion UPS provides perfectly regulated sine wave output within 2% of 120V under all usage conditions
- Maintains continuous operation through blackouts, voltage fluctuations and surges with zero transfer time
- Removes harmonic distortion, fast electrical impulses, frequency variations and other hard-to-solve power problems not addressed by other UPS types

Highlights

- 750VA / .75kVA / 600 watt online double-conversion 2U rack/tower UPS
- 120V +/-2% output at 50/60Hz, high efficiency economy mode option
- Expandable runtime, Hot-swap batteries; 13.5 in / 34.3cm installed depth
- USB, RS232 & EPO ports; Preinstalled WEBCARDLX Network Interface
- Front panel status LEDs with detailed load and battery metering
- 2 independently switchable output load banks
- NEMA 5-15P input; 5-15R outlets
- To enable the Auto Probe feature, this product requires LX firmware update 15.5.2 or later to be installed

Package Includes

- SU750RTXL2U with preinstalled WEBCARDLX network interface
- USB, DB9 and EPO cabling
- Mounting hardware for 4-post rack enclosures
- Instruction manual





- Corrects line voltage conditions as low as 65V and as high as 150V back to 120V (+/-2%) values
- Standard internal battery set offers 11 min. runtime at half load (300W) and 6 min. at full load (600W)
- Extended runtime available with optional BP24V15RT2U (limit 1), BP24V28-2U (limit 1), BP24V70-3U (multi-pack compatible) and BP24V36-2US (multi-pack compatible) external battery packs
- Intelligent battery management system extends battery life
- Some external battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Compact rackmount form factor installs using only 2 rack spaces (2U) with a maximum installed depth of only 13.5 inches
- Ships with all mounting accessories for 4-post rackmount installation
- Optional 2POSTRMKITWM enables 2-post rackmount or wallmount installation
- Optional 2-9USTAND accessory enables small-footprint upright tower placement
- · Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Network interfaces support simultaneous communications via built-in USB, DB9 serial / contact-closure and pre-installed WEBCARDLX network interface
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from <u>tripplite.eaton.com/products/power-alert</u>
- Built-in Emergency Power Off (EPO) interface with cable
- NEMA 5-15P input plug/NEMA 5-15R output receptacles
- Integrated 2-bank switched PDU enables remote outlet management for load shedding or remote reboot
 of individual devices (each load bank consists of a single outlet)
- Front panel LEDs offer current monitoring and battery charge level information
- Single-line tel/DSL or network Ethernet line surge suppression
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW		
UPC Code	037332190758	
UPS Type	On-Line	
INPUT		
Input Phase	Single-Phase	
Rated input current (Maximum Load)	8.6A	
Nominal Input Voltage(s) Supported	120V AC	
UPS Input Connection Type	5-15P	
Input Circuit Breakers	15A	
UPS Input Cord Length (ft.)	6	
UPS Input Cord Length (m)	1.8	
Recommended Electrical Service	15A 120V	
OUTPUT		





Output Capacity (VA)	750
Output Capacity (kVA)	0.75
Output Capacity (Watts)	600
Output Capacity (kW)	0.6
Output Capacity Details	OVERLOAD CAPACITY: Supports inverter operation up to 105% load continuously, 125% load for 3 minutes; 150% load for 30 seconds and >150% load for 0.5 seconds before switching to BYPASS (when bypass input voltage and frequency are WITHIN bypass limits) or SHUTDOWN (when bypass input voltage or frequency are OUTSIDE bypass limits)
Power Factor	0.8
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Output frequency matches input nominal on startup, defaults to 60 Hz on cold-start
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Battery Mode)	+/- 2%
Load Management Receptacles	Two switchable single-outlet 5-15R load banks
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	Yes
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	4 min. (600W)
Runtime Half Load (min.)	11 min. (300W)
Expandable Runtime	Yes
External Battery Pack Compatibility	<a class="productLink" href="//tripplite.eaton.com/External-24V-2U-Rack-Tower-Battery-Pack-for-select-
Tripp-Lite-UPS-Systems~BP24V15RT2U">BP24V15RT2U &hbsp (limit 1); &hbsp <a <br="" class="productLink">href="//tripplite.eaton.com/External-24V-2U-Rack-Tower-Battery-Pack-select-Tripp-Lite-UPS-Systems~BP24V28- 2U">BP24V28-2U &hbsp (limit 1); &hbsp <a class="productLink" href="/tripplite.eaton.com/External-24V-3U-
Rack-Tower-Battery-Pack-select-Tripp-Lite-UPS-Systems~BP24V70-3U">BP24V70-3U Rack-Tower-Battery-Pack-select-Tripp-Lite-UPS-Systems~BP24V70-3U">BP24V70-3U compatible); &hbsp <a class="productLink" href="/tripplite.eaton.com/External-24V-3U-
rack-Tower-Battery-Pack-select-Tripp-Lite-UPS-Systems~BP24V70-3U">BP24V70-3U compatible); &hbsp <a class="productLink" href="/tripplite.eaton.com/external-24V-2u-rack-mount-battery-pack-for-
tripp-lite-ups-systems-SMART750-SU750-SU1000-SUINT1000-and-more~BP24V36-2US">BP24V36- 2US &hbsp (multi-pack compatible)
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 6 hours from 10% to 80% (typical, full load discharge)
Battery Access	Front panel battery access door
Internal UPS Replacement Battery Cartridge	<a class="productLink" href="//tripplite.eaton.com/2U-UPS-Replacement-24VDC-Battery-Cartridge-1-set-2-
select-Tripp-Lite-SmartPro-UPS~RBC92-2U">RBC92-2U





VOLTAGE REGULATION		
Voltage Regulation Description	Online, double-conversion power conditioning	
Overvoltage Correction	2% output voltage regulation during overvoltages to 150	
Undervoltage Correction	2% output voltage regulation during undervoltages to 80	
Severe Undervoltage Correction	2% output voltage regulation during undervoltages to 65 (under 70% load only)	
USER INTERFACE, ALERTS & CON	TROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation	
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch	
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions	
LED Indicators	14 LEDs indicate line power, online mode, bypass mode, on-battery, overload, battery low, replace battery and fault status information; 4-LED meter displays load and battery charge levels; LED panel rotates for viewing in rack/tower formats	
SURGE / NOISE SUPPRESSION		
UPS AC Suppression Joule Rating	480	
UPS AC Suppression Response Time	Instantaneous	
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet	
EMI / RFI AC Noise Suppression	Yes	
PHYSICAL		
Primary Form Factor	Rackmount	
Rack Height	2U	
Cooling Method	Fan	
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount	
Installation Form Factors Supported with Optional Accessories	2 post rackmount (<a class="productLink" href="//tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-
Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM); 2-4 post front rail rackmount (<a class="productLink" href="//tripplite.eaton.com/Heavy-Duty-2-post-Front-Mounting-Ear-
Kit~UPSHDEARKIT">UPSHDEARKIT); 4 post rackmount short-depth (<a <br="" class="productLink">href="//tripplite.eaton.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount- Racks~4POSTRAILKITWM">4POSTRAILKITWM); Tower (<a <br="" class="productLink">href="//tripplite.eaton.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2- 9USTAND); Wallmount (





Optional <a class="productLink" href="//tripplite.eaton.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-
Systems~2-9USTAND">2-9USTAND enables upright tower UPS placement; 2POSTRMKITWM enables wall-mount and 2-post rackmount installation; <a class="productLink" href="/tripplite.eaton.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-
Wall-Mount-Racks~4POSTRAILKITWM">4POSTRAILKITWM enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); <a class="productLink" href="/tripplite.eaton.com/Heavy-
Duty-2-post-Front-Mounting-Ear-Kit-UPSHDEARKIT">UPSHDEARKIT enables installation in 2 or 4-post racks using front vertical rails only, without rear support</a
343
89
445
9.10 x 23.30 x 19.60
23.11 x 59.18 x 49.78
40.00
18.14
Steel
8.89 x 44.45 x 34.29
3.5 x 17.5 x 13.5
13.15
29
+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
0 to 95%, non-condensing
306
87%
97%
333
WEBCARDLX
Includes pre-installed WEBCARDLX; DB9 port supports RS232 and contact closure communications; Economy- mode setting option is available using PowerAlert software and DB9 Serial cable connection OR installed Network Management Card
For local monitoring via the UPS's built-in communication ports, download PowerAlert software at https://tripplite.eaton.com/products/power-alert





Network Management Card Description	Network management card included
Communications Interface	Contact closure; DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	80V (100% load), 65V (<70% load)
High Voltage Transfer to Battery Power (Setpoint)	150
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (included); Automatic inverter bypass; Expandable battery backup; Hot swappable batteries; On-Line/Double-Conversion; Remote management; Sine wave output; Surge/noise protection; Zero transfer time
APPLICATIONS	
UPS Applications	Mission Critical Applications
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance :

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.