

SmartOnline 277/480V 3-Phase Wye 80kVA Modular 3-Phase UPS System, On-line Double- Conversion UPS for North America

MODEL NUMBER: **SU80KTV**



Description

Tripp Lite's SU80KTV (80kVA) SmartOnline Modular 3-Phase Intelligent, True On-Line UPS System provides 100% system availability with N+1 modular architecture and 1+1 parallel capability. In an N+1 configuration, the SU80KTV features four self-contained, redundant 20kVA power modules that can be hot-swapped (with the load powered) if maintenance is required. Connect two SU80KTV models in parallel (1+1 configuration) to provide fail-safe redundancy (two 80kVA models supporting a 80kVA load) or to increase capacity (two 80kVA models supporting a 160kVA load).

The SU80KTV provides mission-critical equipment with the highest level of power protection available. Large capacity 80,000VA/64,000W UPS continually converts incoming AC power into filtered DC power, and then resynthesizes it back into AC power with a pure sine wave. Perfectly regulated, continuous sine wave output with zero transfer time offers compatibility with all equipment types. The SU80KTV's high input power factor, advanced IGBT inverter technology and Digital Signal Processor (DSP) technology create less than 3% input Total Harmonic Distortion (THDi). With SU80KTV's low THDi, generators run cooler and last longer, allowing managers to save installation costs by installing a generator with a capacity equal to their equipment load (a 1:1 ratio). Extremely efficient operation (up to 96%) saves money by lowering electricity consumption. Hardwire input and output connections. The SU80KTV features 277/480VAC, 3-phase, 4-wire (plus ground), wye input and output. It also features a wide input voltage correction range (218-348/378-603VAC at full load). Frequency is 50 or 60 Hz (auto-selectable). The SU80KTV features a single small-footprint tower power module. A stand-alone hardwired external battery module (Model or BP480V40C with matching battery cabinets, available separately) is required for operation and to provide battery backup support. Additional external BP480V40C battery modules can be connected for extended runtime. Other battery cabinets for extended runtime solutions also available; contact Tripp Lite for more information. A manual bypass breaker as well as an automatic bypass function ensure 100% availability of connected equipment by safely passing through AC power if the UPS requires

Highlights

- 80,000 VA (80kVA) tower UPS with 4 hot-swappable power modules
- N+1 redundant modular architecture helps ensure 100% availability
- 1+1 parallel capability allows for system redundancy or increased capacity
- Low THDi saves installation costs by allowing 1:1 generator sizing
- 3-phase hardwire (277/480VAC) input/output. Wide input voltage correction range (218-348/378-603VAC at full load)
- On-line, double-conversion operation with zero transfer time; IGBT technology; extremely efficient operation (up to 96%)
- Runtime is expandable via external battery cabinet options

Package Includes

- SU80KTV UPS System
- Serial cable
- Parallel cable (for 1+1 operation)
- Instruction manual and startup checklist
- Warranty information

maintenance. A built-in RS-232 communication port works with PowerAlert Software, available via free download, to provide shutdown commands and condition reporting. Compatible with Tripp Lite UPS management card options. Front panel combination LCD/LED display alerts users to a variety of UPS operational modes and conditions. The LCD display includes a real-time event log screen with up to 500 events listed. A dynamic battery management screen optimizes battery function to lengthen service life and allows cold restart of UPS during a prolonged blackout to utilize its batteries for periodic system access or data retrieval. An Emergency Power Off button turns UPS output OFF and disables Bypass output. Built-in Emergency Power Off (EPO) dry-contact interface supports remote emergency shutdown in large facilities. A start-up service program is recommended to enhance the reliability of the installation.

Features

- N+1 configuration: four self-contained, redundant 20kVA power modules can be hot-swapped (with the load powered) if maintenance is required
- 1+1 configuration: connect two SU80KTV models in parallel to provide fail-safe redundancy or to increase capacity
- High input power factor, advanced IGBT inverter technology and Digital Signal Processor (DSP) technology create low input Total Harmonic Distortion (THDi)
- Extremely efficient operation (up to 96%) saves money by lowering electricity consumption
- True on-line, double conversion UPS with IGBT technology provides pure, sine wave AC output at all times
- Maintains continuous operation through blackouts, voltage fluctuations and surges with zero transfer time
- Removes harmonic distortion, electrical impulses, frequency variations and other hard-to-solve power problems
- 80,000VA/64,000W power capacity with 3-phase, hardwire 277/480VAC input/output connections
- Features a wide input voltage correction range (218-348/378-603VAC at full load)
- Precision +/-1% output voltage regulation
- A stand-alone hardwired external battery module (Model BP480V40C, available separately from Tripp Lite) is required for operation and to provide battery backup support. Additional external battery modules can be connected for extended runtime.
- Front panel combination LCD/LED display includes a real-time event log screen with up to 500 events listed
- Dynamic battery management screen optimizes battery function to lengthen service life and allows cold restart of UPS
- Serial port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX, SNMPWEBCARD, MODBUSCARD and RELAYIOCARD
- Emergency Power Off button turns UPS output OFF and disables Bypass output
- Built-in Emergency Power Off (EPO) dry-contact interface supports remote emergency shutdown in



large facilities

- Start-up service program is recommended to enhance the reliability of the installation

Specifications

| OVERVIEW | |
|--|---------------------------------|
| UPC Code | 037332142405 |
| UPS Type | On-Line |
| INPUT | |
| Rated input current (Maximum Load) | 97A (per phase, online) |
| Nominal Input Voltage(s) Supported | 277/480V 3-PH Wye |
| UPS Input Connection Type | Hardwire |
| UPS Input Connection Description | 277/480V (3-Phase, 4 Wire, wye) |
| Input Phase | 3-Phase |
| OUTPUT | |
| Output Volt Amp Capacity (VA) | 80000 |
| Output kVA Capacity (kVA) | 80 |
| Output Watt Capacity (Watts) | 64000 |
| Output kW Capacity (kW) | 64 |
| Power Factor | 0.8 |
| Crest Factor | 3:1 |
| Frequency Compatibility | 50 / 60 Hz |
| Output Voltage Regulation (Line Mode) | +/-1% |
| Output Voltage Regulation (Battery Mode) | +/-1% |
| Output AC Waveform (AC Mode) | Sine wave |
| Output AC Waveform (Battery Mode) | Pure Sine wave |
| Nominal Output Voltage(s) Supported | 277/480V 3-PH Wye |
| Output Receptacles | Hardwire |
| Individually Controllable Load Banks | No |
| BATTERY | |
| Expandable Battery Runtime | Battery set sold separate |



| | |
|---|--|
| External Battery Pack Compatibility | BP480V200 & BP480V300 & BP480V400 & BP480V500 |
| Expandable Runtime Description | External battery pack wiring is contractor supplied |
| DC System Voltage (VDC) | +/- 240VDC |
| Battery Recharge Rate (Included Batteries) | 2 - 4 hours from 10% to 90% |
| Battery Replacement Description | Hot-swappable, replaceable batteries |
| Expandable Runtime | Yes |
| POWER | |
| LED Indicators | 4-LED Display: Displays normal AC input, on battery power, bypass input and fault conditions |
| VOLTAGE REGULATION | |
| Voltage Regulation Description | Online, double-conversion power conditioning |
| Overvoltage Correction | Maintains continuous operation without using battery power during overvoltages to 348/603 (3-Phase, 4-Wire, wye) |
| Undervoltage Correction | Maintains continuous operation without using battery power during brownout / undervoltage conditions to 218/378 (3-Phase, 4-Wire, wye) |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | ON button turns UPS's inverter ON. OFF button turns UPS's inverter OFF. LCD Display Control Buttons browses through and selects items displayed on LCD screen. Emergency Power Off button turns UPS output OFF and disables Bypass output. Manual Bypass breaker bypasses the UPS's inverter during maintenance. |
| Alarm Cancel Operation | Power-fail alarm can be silenced using alarm-cancel switch |
| Audible Alarm | Alarms warn against a variety of operational conditions: low-battery, overload, shutdown, bypass and more |
| SURGE / NOISE SUPPRESSION | |
| EMI / RFI AC Noise Suppression | Yes |
| AC Suppression Joule Rating | 4675 |
| AC Suppression Response Time | Instantaneous |
| PHYSICAL | |
| Cooling Method | Fans |
| Installation Form Factors Supported with Included Accessories | Tower |
| Primary Form Factor | Tower |
| Primary UPS Depth (mm) | 1,041 |
| Primary UPS Height (mm) | 1,699 |
| Primary UPS Width (mm) | 521 |



| | |
|---|--|
| Shipping Dimensions (hwd / cm) | 193.68 x 72.39 x 115.57 |
| Shipping Dimensions (hwd / in.) | 76.25 x 28.50 x 45.50 |
| Shipping Weight (kg) | 583.32 |
| Shipping Weight (lbs.) | 1286.00 |
| UPS Housing Material | Steel |
| UPS Power Module Dimensions (hwd, cm) | 169.93 x 52.07 x 104.14 |
| UPS Power Module Dimensions (hwd, in.) | 66.9 x 20.5 x 41 |
| UPS Power Module Weight (kg) | 501.22 |
| UPS Power Module Weight (lbs.) | 1105 |
| ENVIRONMENTAL | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius |
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius |
| Relative Humidity | 0 to 90%, non-condensing |
| AC Mode BTU / Hr. (Full Load) | 18665 |
| Battery Mode BTU / Hr. (Full Load) | 19005 |
| COMMUNICATIONS | |
| Network Management Cards | SNMPWEBCARD TLNETCARD WEBCARDLX MODBUSCARD RELAYIOCARD |
| PowerAlert Software | For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert |
| Communications Cable | DB9 cabling included |
| Communications Interface | DB9 Serial; Slot for SNMP/Web interface |
| LINE / BATTERY TRANSFER | |
| Transfer Time | No transfer time (0 ms.) in online, double-conversion mode |
| SPECIAL FEATURES | |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported |
| High Availability UPS Features | Automatic inverter bypass; Hot swappable batteries; Auto Probe Monitoring (requires WEBCARDLX); Zero transfer time; On-Line/Double-Conversion |
| Green Energy-Saving Features | High efficiency economy mode operation; Schedulable daily hours of economy mode operation |
| STANDARDS & COMPLIANCE | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|---|--|
| UPS Certifications | Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances) |
| WARRANTY | |
| Product Warranty Period (U.S. & Canada) | 1-year limited warranty |
| Product Warranty Period (International) | 2-year limited warranty |
| Product Warranty Period (Mexico) | 1-year limited warranty |
| Product Warranty Period (Puerto Rico) | 2-year limited warranty |
| 3-Phase Warranty Statement | <u>Tripp Lite 3-Phase UPS Factory Warranty</u> |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>