

3-Breaker Parallel Tie Cabinet with Maintenance Bypass Switch (for 2x SU80KX 3-Phase UPS)

MODEL NUMBER: **SUPC2MBP80KX**



Highlights

- 3 breaker parallel tie cabinet accessory for two Tripp Lite 80kVA 3 phase UPS systems
- Links the output of two UPS systems for 160kVA non-redundant operation
- Integral Maintenance Bypass switch enables UPS maintenance or replacement
- 3 built-in circuit breakers, heavy duty copper buswork
- Compatible Tripp Lite SU80KX 3 phase UPS systems

Description

Tripp Lite's parallel tie cabinet provides a means for safely paralleling two UPS systems for non-redundant combined mode operation. Non-redundant configuration combines the output of two UPS systems to support twice the output current. Built-in Maintenance Bypass Switch enables UPS maintenance and repair of with no disruption in power to connected equipment. Two input breakers receive incoming power from the UPS and are connected to heavy duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined. See owners manual and [Tripp Lite Parallel Tie Cabinet with Bypass Panel](#) download for detailed specifications, dimensional drawings, operational flow charts and technical descriptions.

Compatible with two Tripp Lite SU80KX UPS systems.

Features

- Provides a means for safely paralleling two UPS systems for non-redundant combined mode operation
- Non-redundant configuration combines the output of two UPS systems to support twice the output current
- Built-in Maintenance Bypass Switch enables UPS maintenance and repair of with no disruption in power to connected equipment
- Two input breakers receive incoming power from the UPS and are connected to heavy duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined
- Compatible with two Tripp Lite SU80KX UPS systems

Specifications

OVERVIEW	
UPC Code	037332167200
Accessory Type	Parallel Tie Cabinet
Accessory Class	UPS Accessories

INPUT	
Nominal Input Voltage(s) Supported	380V AC; 400V AC; 415V AC
Voltage Compatibility (VAC)	380; 400; 415
PHYSICAL	
Form Factors Supported	Wallmount
Shipping Dimensions (hwd / in.)	13.00 x 37.00 x 62.00
Shipping Dimensions (hwd / cm)	33.02 x 93.98 x 157.48
Shipping Weight (lbs.)	375.00
Shipping Weight (kg)	170.10
Unit Dimensions (hwd / in.)	61.250 x 36.130 x 11.800
Unit Dimensions (hwd / cm)	155.6 x 91.7 x 29.85
Unit Weight (lbs.)	370
Unit Weight (kg)	167.83
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty