

# UPS Maintenance Bypass Panel for SUTX40K - 3 Breakers

MODEL NUMBER: **SUT40KMBPX**



UPS bypass panel reroutes power to keep essential equipment operational while the UPS is inoperative or under maintenance.

## Features

**UPS Maintenance Bypass Panel Keeps Equipment Powered During UPS Maintenance** This wall-mount three-breaker maintenance bypass panel is compatible with Tripp Lite's SUTX40K 3-phase UPS system. It allows you to reroute power around the UPS, providing an alternate path for electricity that keeps the connected load operational while the UPS is offline for maintenance or repairs.

**Features 3 Built-In Circuit Breakers to Isolate Loads** Three 4-pole circuit breakers – an AC input breaker, a maintenance bypass breaker and a maintenance isolation breaker – are connected to heavy-duty buswork and isolate the UPS system from its connected load with no loss of network availability. This allows the load to remain continuously powered without costly downtime. A Kirk-key interlock system enhances safety and security. Removable handles allow the panel's trim cover to be removed for internal access. The 125A unit has a kAIC rating of 10K.

**Switching Between Normal and Bypass Modes Is Easy** When a UPS needs maintenance, this UPS bypass panel keeps power supplied to components via its mechanical interlock system by switching power to the external bypass breaker. Simply unscrew the interlock switch, rotate the switch from the UPS AC input breaker (SW1) to the bypass breaker (SW2), then turn on the bypass breaker and turn off the UPS and isolation breaker (SW3) to perform UPS maintenance without service interruption.

**Convenient Wall-Mount Installation** Made of galvanized steel, the service bypass panel has rear mounting holes for installation on a smooth, solid wall (mounting hardware not included).

## Specifications

| OVERVIEW        |                 |
|-----------------|-----------------|
| UPC Code        | 037332241108    |
| Accessory Type  | Bypass Panel    |
| Accessory Class | UPS Accessories |

## Highlights

- Isolates UPS from connected loads for maintenance without losing network availability
- Maintenance bypass panel mounts to wall next to UPS for convenient access
- 125A 10 kAIC unit has three 4-pole built-in circuit breakers connected to heavy-duty buswork
- Secure Kirk-key interlock system prevents unauthorized access to power
- Compatible with Tripp Lite's SUTX40K 3-phase UPS system

## Applications

- Bypass a compatible offline 3-phase UPS system to continue powering mission-critical equipment without interruption

## System Requirements

- Tripp Lite SUTX40K 3-phase UPS system

## Package Includes

- SUT40KMBPX UPS Maintenance Bypass Panel for SUTX40K - 3 Breakers
- Installation and Operation Manual



Powering Business Worldwide



| INPUT                               |                                       |
|-------------------------------------|---------------------------------------|
| Nominal Input Voltage Description   | 400Y/230 VAC 3 phase, 4 wire (3P+N+E) |
| OUTPUT                              |                                       |
| Output Capacity Details             | 125A maximum                          |
| PHYSICAL                            |                                       |
| Form Factors Supported              | Wallmount                             |
| Shipping Dimensions (hwd / in.)     | 22.00 x 25.00 x 10.00                 |
| Shipping Weight (kg)                | 13.61                                 |
| Unit Dimensions (hwd / in.)         | 17.500 x 20.000 x 4.600               |
| Unit Dimensions (hwd / cm)          | 44.45 x 50.8 x 11.68                  |
| Unit Weight (lbs.)                  | 20                                    |
| Unit Weight (kg)                    | 9.07                                  |
| WARRANTY & SUPPORT                  |                                       |
| Product Warranty Period (Worldwide) | 1-year limited warranty               |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.