

SmartOnline 240 & 120V 20kVA 18kW Double-Conversion UPS in 25U enclosure, Pre-installed Network Card, USB, DB9, Bypass, Hardwire

MODEL NUMBER: SU20KRTHWTFASSM



Description

Tripp Lite SU20KRTHWTFASSM 20,000VA / 20kVA / 18,000 watt online, double-conversion UPS system offers complete power protection for critical server, network and telecommunications equipment in a 16U rack/tower configuration pre-assembled into a Tripp Lite 25U rack enclosure. This system delivers complete N+1 redundancy when used at loads up to 50%, and non-redundant operation at loads between 50 and 100%. Fault-tolerant auto-bypass prevents unexpected service interruptions during UPS overload or internal fault conditions. Included parallel PDU with manual bypass switching enables hot-swappable replacement of all major UPS system components in both N+1 and combined operating modes. Enhanced availability, fault tolerance and simple hot-swap replacement options make this UPS ideal for advanced networking applications in data centers, computer rooms, network closets and rugged industrial locations.

Features

- Tripp Lite SU20KRTHWTFASSM 20kVA, 20,000VA / 18,000 watt on-line, double-conversion UPS system in a 16U total rack/tower configuration (max output de-rates to 18kVA / 16kW when operated at 208V nominal input voltage)
- Pre-built into a 25U SmartRack enclosure with 6U of open rack space able to accommodate two optional additional BP240V10RT3U external battery packs
- Offers enhanced fault-tolerance and reliability with N+1 configuration support and hot-swappable whole UPS replacement options
- Unique configuration ties input, output and data connections of two standard 10kVA UPS systems via detachable parallel PDU to offer 20kVA non-redundant operation and automatic N+1 redundancy at load levels of 50% and lower
- Included Parallel PDU with manual bypass switching enables hot-swappable replacement of either

Highlights

- 20kVA / 20,000VA / 18,000W on-line double-conversion UPS; 0.9 power factor; Extended runtime
- 16U configuration built into a 25U rack enclosure; 9 open rack-spaces for battery packs or other network items
- Hot-swappable power and battery modules; Maintenance bypass switch; N+1 fault tolerance is available at loads up to 50%
- USB, RS232 & EPO ports; Pre-installed network management card interface
- Hardwire 240V 60Hz (3 wire) input; 240 & 120V 60Hz hardwire output

Package Includes

- Two SU10000RT3UPM UPS power modules
- Two BP240V10RT3U battery packs
- One SU20KXFMRT4U 120V transformer
- SUPDMB20KHW parallel PDU with Bypass switch
- Pre-installed in a Tripp Lite 25U rack enclosure
- USB, DB9 and EPO cables

power module at any supported load level, with no interruption to connected equipment

- Hardwire input and output connections
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Full-time active power conditioning provides clean, continuous dual-conversion AC output free of voltage fluctuations, power interruptions and line noise
- Double-conversion operation converts raw input from AC to DC, then resynthesizes output power back to perfect sine wave AC with enhanced protection from harmonic distortion, fast electrical impulses and other hard-to-solve power problems not addressed by other UPS types
- Maintains full-time sine wave output within 2% of 240/120V nominal at 60Hz during brownouts as low as 100V and overvoltages as high as 300V
- Expandable runtime is supported with optional BP240V10RT3U; BP240V787C-1PH external battery packs
- Some external battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Intelligent battery management system with temperature-compensated charging extends battery life
- Battery independent restart ensures automatic UPS power-up without user interaction after lengthy power outages, even when batteries are expired and require replacement
- Rack / tower configuration installs in 16 total rack spaces (16U)
- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Pre-installed Network Management Card (one per 10kVA power module) offers communications and control via secure remote web and network interfaces
- Supports Emergency Power Off (EPO) via built-in interface
- Front panel LEDs and LCD readout with scroll controls and password option supports visual monitoring of all major UPS functions and advanced UPS settings for charge level, nominal voltage selection, frequency conversion and other operational parameters
- LED / LCD display panel rotates for viewing in rackmount or tower configurations
- Network-grade AC surge and noise suppression
- Industrial mode option (factory preset) enables supports high current startup loads by momentarily switching to bypass mode in response to short duration overload conditions
- External battery packs are field replaceable and hot swappable
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW



UPC Code	037332180896
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	98A
Nominal Input Voltage(s) Supported	208V AC; 240V AC
UPS Input Connection Type	Hardwire
UPS Input Connection Description	3 wire single phase input (L1, L2, G)
Recommended Electrical Service	120A @ 200V-240V (L, N, PE), or 125A @ 200V, 208V, or 240V (L1, L2, G)
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	20000
Output kVA Capacity (kVA)	20
Output Watt Capacity (Watts)	18000
Output kW Capacity (kW)	18
Output Capacity Details	Output de-rates to 18kVA / 16kW with 208V nominal input voltage; Supports up to 105% load continuously in double conversion mode, 106 to 125% for 1 minute, 126% to 150% for 30 seconds; Loads over 150% trigger immediate bypass mode operation to support loads directly from mains power; Double conversion mode is automatically restored as load levels are reduced to 95% or less
Power Factor	0.9
Crest Factor	3:1
Nominal Voltage Details	Included step-down transformer supports 120V output
Frequency Compatibility	60 Hz
Frequency Compatibility Details	Output frequency regulation +/- 0.05Hz (free running)
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Battery Mode)	+/- 2%
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120V; 240V
Output Receptacles	Hardwire
Individually Controllable Load Banks	No
BATTERY	
Full Load Runtime (min.)	4.3 minutes (18,000 watts)
Half Load Runtime (min.)	12.5 minutes (9000 watts)



Maximum Device Depth (in.)	32.5
Maximum Device Depth (mm)	826
Primary Form Factor	Rackmount
Primary UPS Depth (mm)	656
Primary UPS Height (mm)	131
Primary UPS Width (mm)	445
Rack Height	14U
Shipping Dimensions (hwd / cm)	132.08 x 68.58 x 127.00
Shipping Dimensions (hwd / in.)	52.00 x 27.00 x 50.00
Shipping Weight (kg)	416.40
Shipping Weight (lbs.)	918.00
Stepdown Transformer Depth (mm)	744
Stepdown Transformer Dimensions (hwd / cm)	17.78 x 44.45 x 74.42
Stepdown Transformer Dimensions (hwd / in.)	7 x 17.5 x 29.3
Stepdown Transformer Height (mm)	178
Stepdown Transformer Weight (kg)	127.50
Stepdown Transformer Weight (lbs.)	281.1
Stepdown Transformer Width (mm)	445
Unit Dimension Details	Includes 2 SU10000RT3UPM UPS/Power modules, 2 BP240V10RT3U Battery packs, 1 SU20KXFMRT4U transformer and SUPDMB20KHW parallel bypass PDU; Listed weights and dimensions for UPS/Power module, battery pack and transformer each refer to a single unit; MAXIMUM DEVICE DEPTH specification refers to the whole UPS installed depth with parallel bypass PDU installed
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	13.06 x 44.45 x 65.58
UPS Power Module Dimensions (hwd, in.)	5.14 x 17.5 x 25.82
UPS Power Module Weight (kg)	20.00
UPS Power Module Weight (lbs.)	44.1
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	6830
Battery Mode BTU / Hr. (Full Load)	9185
AC Mode Efficiency Rating (100% Load)	87%



Operating Elevation (ft.)	0-3000m (0 to 10,000 ft.)
Audible Noise	60 dBA at front side 1 meter
Operating Elevation (m)	0-3000 m
COMMUNICATIONS	
Network Monitoring Port Description	Additional contact closure support with optional RELAYIOMINI interface cards; RELAYIOMINI installation requires removal of panel containing USB ports
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	USB, DB9 serial and EPO cables included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	100V
High Voltage Transfer to Battery Power (Setpoint)	300V
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable UPS power module; Hot swappable batteries; Manual bypass switch; Auto Probe Monitoring (included); Zero transfer time; On-Line/Double-Conversion
Green Energy-Saving Features	Support for daily startup and shutoff
STANDARDS & COMPLIANCE	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances)
Certification Details	IEC 61000-4-5 1995 B Surge Immunity
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>