

SmartOnline 20kVA 16kW Modular 3-Phase UPS System, Double-Conversion UPS, Network Card Slot, DB9 Serial

MODEL NUMBER: **SU20KX**



Description

Tripp Lite's SU20KX (20kVA) SmartOnline Modular 3-Phase Intelligent, True On-Line UPS System provides 100% system availability with 1+1 parallel capability. In 1+1 configuration, two SU20KX models connected in parallel can provide fail-safe redundancy (two 20kVA models supporting a 20kVA load) or increased capacity (two 20kVA models supporting a 40kVA load). The SU20KX provides mission-critical equipment with the highest level of power protection available. Large capacity 20,000VA/16,000W UPS continually converts incoming AC power into filtered DC power, and then resynthesizes it back into AC power with a pure sine wave. Perfectly regulated, continuous sine wave output with zero transfer time assures compatibility with all equipment types. High input power factor, advanced IGBT inverter technology and Digital Signal Processor (DSP) technology produce less than 3% input total harmonic distortion (THDi). With low THDi, generators run cooler and last longer, allowing managers to save installation costs by installing a generator with a capacity equal to the equipment load (1:1 ratio). Extremely efficient operation (up to 97%) saves money by lowering electricity consumption. Hardwire input and output connections. The SU20KX features 50 or 60 Hz (auto-selectable) frequency. The SU20KX combines internal power and battery modules in a single small-footprint tower compartment. Typical half-load/full-load runtimes are 13 min./5.5 min. Battery runtime can be extended with optional stand-alone hardwired external battery modules (Models BP480V26B and BP480V40C, available separately). A manual bypass breaker and an automatic bypass function ensure 100% availability of connected equipment by safely passing through AC power if the UPS requires maintenance.

Features

- 1+1 configuration: Two SU20KX can be connected in parallel to provide either fail-safe redundancy or increased capacity
- Low THDi (less than 3%) reduces installation costs by allowing 1:1 generator sizing
- Extremely efficient operation (up to 97%) saves money by reducing electricity consumption

Highlights

- 20,000 VA (20kVA) 3-phase tower UPS
- 1+1 parallel capability allows for system redundancy or increased capacity
- Low THDi reduces installation costs by permitting 1:1 generator sizing
- 3-phase hardwire (220/380V, 230/400V or 240/415V AC, 3-phase, 4-wire + ground, wye) input/output
- IGBT technology and zero transfer time, on-line, double-conversion operation
- Runtime is expandable with the addition of two SURBC2030 internal battery packs or via external battery cabinet options

Package Includes

- SU20KX UPS System
- DB9 cable
- Instruction manual
- Warranty information



- True on-line, double-conversion UPS with IGBT technology provides pure sine wave AC output at all times
- Maintains continuous operation with zero transfer time through blackouts, voltage fluctuations and surges
- Removes harmonic distortion, electrical impulses, frequency variations and other hard-to-solve power problems
- 20,000VA/16,000W power capacity with 3-phase, hardwire input/output connections
- Wide input voltage correction range: 173-276V/300-477V AC
- Precision +/-1% output voltage regulation
- Internal power and battery modules are combined in a single small-footprint tower compartment. Typical half-load/full-load runtimes are 13 min./5.5 min. Battery runtime can be extended with optional stand-alone hardwired external battery modules (Models BP480V26B and BP480V40C, available separately)
- Front panel combination LCD/LED display includes a real-time event log screen with up to 500 events listed
- Dynamic battery management screen optimizes battery function to lengthen service life and allow cold restart of the UPS
- Serial port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX, SNMPWEBCARD, MODBUSCARD and RELAYIOCARD
- Emergency Power Off button turns UPS output OFF and disables Bypass output
- Built-in Emergency Power Off (EPO) dry-contact interface supports remote emergency shutdown in large facilities

Specifications

OVERVIEW	
UPC Code	037332141354
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	28A / 29A / 30A
Nominal Input Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Nominal Input Voltage Description	3-Phase Wye, 4 wire (L1, L2, L3, N, G)
UPS Input Connection Type	Hardwire
Input Phase	3-Phase
OUTPUT	



Output Volt Amp Capacity (VA)	20000
Output kVA Capacity (kVA)	20
Output Watt Capacity (Watts)	16000
Output kW Capacity (kW)	16
Power Factor	0.8
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Line Mode)	+/-1%
Output Voltage Regulation (Battery Mode)	+/-1%
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Output Receptacles	Hardwire
Individually Controllable Load Banks	No
BATTERY	
Full Load Runtime (min.)	5.5 min. (16kw)
Half Load Runtime (min.)	13 min. (8kw)
Expandable Battery Runtime	Supports extended runtime with optional external battery packs
External Battery Pack Compatibility	 BP480V200 BP480V26B BP480V300 BP480V400 BP480V40C BP480V500
Expandable Runtime Description	External battery pack wiring is contractor supplied
DC System Voltage (VDC)	+/- 240VDC
Internal UPS Replacement Battery Cartridge	 SURBC2030
Battery Replacement Description	Hot-swappable, replaceable batteries
Expandable Runtime	Yes
POWER	
LED Indicators	4-LED Display: Displays normal AC input, on battery power, bypass input and fault conditions



VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	Maintains continuous operation without using battery power during overvoltages to 276-477 (3-phase, 4-wire, wye), reducing output within 1% of nominal
Undervoltage Correction	Maintains continuous operation without using battery power during brownout/undervoltage conditions to 173-300 (3-phase, 4-wire, wye)
USER INTERFACE, ALERTS & CONTROLS	
Switches	ON button turns UPS inverter on. OFF button turns UPS inverter off. LCD Display Control Buttons browse through and select items displayed on LCD screen. EPO (Emergency Power Off) button turns UPS output off and disables Bypass output
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Alarms signal a variety of operational conditions: low-battery, overload, shutdown, bypass and more
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	5950
AC Suppression Response Time	Instantaneous
PHYSICAL	
Cooling Method	Fans
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
Primary UPS Depth (mm)	856
Primary UPS Height (mm)	1,168
Primary UPS Width (mm)	521
Shipping Dimensions (hwd / cm)	139.70 x 72.39 x 107.95
Shipping Dimensions (hwd / in.)	55.00 x 28.50 x 42.50
Shipping Weight (kg)	334.98
Shipping Weight (lbs.)	738.50
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	116.84 x 52.07 x 85.60
UPS Power Module Dimensions (hwd, in.)	46 x 20.5 x 33.7
UPS Power Module Weight (kg)	266.98
UPS Power Module Weight (lbs.)	588.6
ENVIRONMENTAL	



Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	3053
Battery Mode BTU / Hr. (Full Load)	3488
COMMUNICATIONS	
Network Management Cards	SNMPWEBCARD TLNETCARD WEBCARDLX MODBUSCARD RELAYIOCARD
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	DB9 cabling included
Communications Interface	DB9 Serial; Slot for SNMP/Web interface
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during brownout/undervoltage conditions to 173-300V AC (3-phase, 4-wire, wye). Below this point, output is maintained utilizing reserve battery power
High Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during overvoltages to 276-477V AC (3-phase, 4-wire, wye), reducing output within 1% of nominal. Above this point, output is maintained utilizing reserve battery power
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries; Auto Probe Monitoring (requires WEBCARDLX); Zero transfer time; On-Line/Double-Conversion
Green Energy-Saving Features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
STANDARDS & COMPLIANCE	
UPS Certifications	CE
WARRANTY	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty
3-Phase Warranty Statement	Tripp Lite 3-Phase UPS Factory Warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>