

# SmartOnline SV Series 80kVA Medium-Frame Modular Scalable 3-Phase On-Line Double-Conversion 208/120V 50/60Hz UPS System, No SVBM Battery Modules

MODEL NUMBER: **SV80KM4P0B**



3-phase 80kVA UPS system offers network-grade power protection in a highly configurable, modular and scalable medium-chassis rack-width frame. No internal battery modules. Requires external batteries for extended runtimes.

## Description

The SV80KM4P0B SmartOnline® SV Series 80kVA 3-Phase On-Line Double-Conversion UPS System delivers true scalability and offers the highest level of secure, uninterrupted power protection. Featuring a modular, scalable design with high-efficiency voltage and frequency independent (VFI) operation, this on-line UPS system is ideal for protecting a variety of critical IT systems.

The SV80KM4P0B includes pre-installed input, bypass and output breakers, as well as a static transfer switch (STS) and four 20kVA SV20PM power modules. It comes fully configured for 80kVA total capacity or 60kVA with enhanced N+1 protection. External  $\pm 120$ VDC battery options, such as BP240V370 or EBP240VXXX series battery cabinets, are available from Tripp Lite for extended runtimes.

The Java-free HTML5-based WEBCARDLX interface enables full remote access for site power and UPS status monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network.

With up to 92% efficiency in standard mode and up to 99% efficiency in optional economy mode, this 80kVA UPS system helps you reduce operating and cooling costs. Automatic and manual bypass options keep connected equipment operational during routine maintenance or critical power module failure. Front-panel display offers full UPS condition and status reporting.

## Features

**80kVA 72kW 3-Phase Medium-Chassis UPS System** Supports 208/120V or 220/127V AC 50/60Hz Wye 4-wire plus Earth hardwire input and output wiring  
 Dual hardwire input design enables operation from up to 2 power sources  
 Network-grade sine-wave AC output with 1% output voltage regulation and less than 1% output total harmonic distortion  
 Tested to UL 1778 (U.S.), CSA (Canada) and NOM (Mexico) standards  
 High 0.9 power factor for maximum power to the connected load

**Pre-Installed WEBCARDLX Network Interface** Allows full remote access for power monitoring, configuration, control and email notifications via secure web browser, SNMP, telnet or SSH  
 Supports 10/100 Mbps auto-sensing for communication with an Ethernet network  
 Optional EnviroSense2 sensors

## Highlights

- Fully configured for 80kVA capacity or 60kVA w/N+1 fault tolerance
- Economy mode option helps reduce operating and cooling costs
- Pre-installed WEBCARDLX network interface for 24/7 remote access
- DSP/IGBT technology and 1% output voltage regulation
- No internal battery modules, and requires external batteries to operate

## Package Includes

- SV80KM4P0B SmartOnline SV Series 80kVA 3-Phase On-Line Double-Conversion UPS System
- Pre-installed WEBCARDLX network interface
- (4) SV20PM 20kVA power modules (shipped separately)
- Owner's manual



(sold separately) enable site monitoring of temperature, humidity and contact-closure status  
 No Java required

**Modular, Scalable Design for Maximum Flexibility** Modular configuration with hot-swappable power modules, and fast maintenance with zero downtime Comes fully configured for 80kVA total capacity or 60kVA with N+1 fault tolerance Supports external  $\pm 120$ VDC battery options for extended runtimes

**Optional Economy Mode** Up to 99% efficient in optional economy mode to lower operating and cooling costs

**Wide Input/Narrow Output Voltage Operating Range** Enables full continuous online operation during brownouts as low as 121V and overvoltages up to 253V Regulates output voltage within 1% of the selected nominal output voltage in on-line double-conversion mode

**Advanced IGBT Inverter with Digital Signal Processor (DSP) Technology** Provides for less than 2% input total harmonic distortion (THDi) to support 1:1 generator sizing and prevent the need to oversize generator systems relative to UPS capacity

**Automatic and Manual Bypass Options** Keep connected equipment operational during routine maintenance or critical power module failure

## Specifications

OVERVIEW	
UPC Code	037332237484
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	SV80KM4P0B 80kVA Maximum Configuration: 240A; 305A maximum inrush current
Nominal Input Voltage(s) Supported	120/208V 3-PH Wye; 127/220V 3-PH Wye
Nominal Input Voltage Description	Set of two hardwire input connections enables 3-Phase Wye, 4 wire (3P, N, G) inputs from two separate power sources
UPS Input Connection Type	Hardwire
Input Circuit Breakers	MAIN and ALTERNATE AC inputs are each protected by 300A 3 pole magnetic breakers
Input Phase	3-Phase
Input Frequency	40 to 70Hz (online mode); 50/60Hz Auto-selectable
Power Factor (Input)	Greater than 0.99 (full load)
THDi	Less than 2% (full linear load)
OUTPUT	
Output Volt Amp Capacity (VA)	80000
Output kVA Capacity (kVA)	80
Output Watt Capacity (Watts)	72000
Output kW Capacity (kW)	72
Output Capacity Details	OVERLOAD CAPABILITY: Supports 105-110% load for 1 hour, 111-125% load for 10 minutes, 126-150% for 1 minute and Over 150% for 200ms before switching to Bypass; Online operation resumes when load is reduced to 100% or less
Power Factor	0.9
Crest Factor	3:1



Nominal Voltage Details	Output THD full resistive load: <1.5%; Output THD non-linear load: <4%; Max DC offset: $\pm 50\text{mV}$ ; Max Phase angle deviation: $2^\circ$ ; Max Voltage unbalance deviation: 1%; Output short-circuit protection included
Frequency Compatibility	50 / 60 Hz; Supports 50 to 60 Hz and 60 to 50 Hz conversion
Frequency Compatibility Details	Auto-selectable, user adjustable
Output Receptacle Details	Output wiring: 3P, N, E
Output Circuit Breakers	300A 3 pole magnetic breaker
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120/208V 3-PH Wye; 127/220V 3-PH Wye
Output Receptacles	Hardwire
Output Voltage Regulation	ONLINE, FREQUENCY CONVERSION, BATTERY MODE: 208/120, 220/127 $\pm 1\%$ typical (balanced load); $\pm 2\%$ typical (unbalanced load); ECONOMY MODE: 208/120, 220/127 $\pm 15\text{V}$ ; BYPASS MODE: +15% (default, adjustable to +10%, +15% or +20%), -20% (default, adjustable to -10%, -20%, -30%)
Output Frequency Regulation	ONLINE MODE: Output frequency is $\pm 0.05\text{Hz}$ of input frequency when input is within $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting; Output frequency is $\pm 0.05\text{Hz}$ the configured 50/60Hz output setting when input is outside $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting; BATTERY MODE: Output frequency is $\pm 0.1\text{Hz}$ of the configured 50/60Hz output setting; FREQUENCY CONVERTER MODE: Output frequency is $\pm 0.1\text{Hz}$ of the configured 50/60Hz output setting; ECONOMY MODE: Output frequency equals input frequency up to $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting (UPS switches to Online mode if frequency goes outside of this range); BYPASS MODE: Output frequency equals input frequency up to $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting (switches to STANDBY mode if frequency goes outside of this range). *The TRACKING RANGE is factory set to $\pm 4\text{Hz}$ and is user adjustable to $\pm 1\text{Hz}$ , $\pm 2\text{Hz}$ or $\pm 4\text{Hz}$ ; The selected TRACKING RANGE setting controls frequency output tolerances as described above in Online, Economy and Bypass modes
Output Amp Capacity	Output Amp Capacity 222A (208/120V); 210A (220/127V)
Individually Controllable Load Banks	No
Modular Upgrade Options	Includes 4 SV20PM 20kVA power modules; This is the maximum configuration for the SV medium-chassis series, no additional power modules can be added
<b>BATTERY</b>	
Full Load Runtime (min.)	No internal batteries and external batteries are required to operate
Half Load Runtime (min.)	No internal batteries and external batteries are required to operate
Expandable Battery Runtime	Extended runtimes available with $\pm 120\text{VDC}$ external battery packs (sold separately); Recommended 3 pole, 400A, 250VDC breaker rating for external battery system
Expandable Runtime	Yes
Expandable Runtime Description	External battery pack wiring is contractor supplied.







