

## SmartOnline 2000VA 1800W 120V Double-Conversion Sine Wave UPS - 7 Outlets, Extended Run, Network Card Option, LCD, USB, DB9, 2U Rack/Tower, TAA

MODEL NUMBER: SU2200RTXLCD2UTAA



Provides battery backup, power protection and sine wave output for mission-critical IT installations, edge networks and other network applications requiring TAA compliance.

### Features

#### 2kVA 1.8kW 120V Battery Backup Protects Equipment Against Damage, Downtime and Data Loss

This on-line double-conversion UPS system maintains perfect output by converting AC input to DC, then reconverting UPS output to fully regulated sine wave AC. Constant on-line operation completely isolates sensitive equipment from every power problem on the AC line. The SmartOnline® SU2200RTXLCD2UTAA provides the highest level of power protection and battery backup for education, healthcare, military, government and other mission-critical IT applications where space is limited, but premium power reliability is essential.

#### Reliable, Expandable Battery Backup Keeps You Operational Through Power Outages

The field-replaceable, hot-swappable VRLA battery modules allow you to work through short power failures and give you enough time to safely save files and shut down your system in the case of a prolonged blackout. Zero transfer time between on-line and battery modes maintains continuous operation of connected equipment without interruption or rebooting. Extra runtime is available by connecting up to four optional extended battery modules (BP72RT2UTAA, sold separately).

#### Optional Network Management Card Allows 24/7 Remote Access

The WEBCARDLXE network interface (sold separately) enables full remote configuration and management, including load shedding, reboots of connected equipment and safe shutdowns. The IP-based Auto Probe feature ensures continuous network uptime by communicating with other network devices, detecting lost connectivity and automatically rebooting IT equipment. Optional EnviroSense2 modules (E2MT, E2MTDO and E2MTHDI, all sold separately) provide a variety of environmental monitoring and control options. **Note:** The SU2200RTXLCD2UTAA is not compatible with WEBCARDLX.

#### NEMA Outlets Protect Your Connected Components

One L5-20R and six 5-20R managed outlets provide connected equipment with pure sine wave AC output and allow you to manage power consumption down to the outlet group level. Power provided by these outlets is filtered to protect connected equipment against damaging surges and line noise. Four 5-20R outlets are split evenly into two switchable load banks that let you reboot select components or shed non-critical loads in order to extend runtime for critical loads during an outage. A cooling fan helps protect equipment from overheating.

### Highlights

- Offers network-grade protection against power failures and voltage fluctuations
- Zero transfer time between on-line and battery modes for uninterrupted operation
- Keeps equipment running during outages to allow time for file saves and safe shutdown
- Optional WEBCARDLXE network interface enables 24/7 complete and remote control
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- 2000VA 1800W 120V Double-Conversion UPS
- USB cable
- DB9 cable
- Rack-mounting hardware
- Tower support stands
- Safety instructions
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE  
SERIES

**Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better**

This UPS system filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

**Intuitive Front-Panel Interface for Convenient UPS Operation and Monitoring**

The two-line front-panel LCD features 10 selectable screens that allow quick access to a wide range of detailed UPS and site power information. LEDs show UPS status: a green light means utility power is on, an orange light means the UPS is in battery or bypass mode and a red light indicates an active alarm or fault. The control panel rotates to accommodate both rack-mount and tower configurations.

**Advanced Communications Ports Allow for Automatic Saves and Shutdowns**

RS-232 and USB ports connect to a device for a variety of communication options (cables are included). A dry-contact relay port can be programmed through the LCD to provide reliable communications to automation and industrial components. The RPO/ROO port permits emergency shutdown or remote restart of all connected equipment.

**Automatically Turns Back On After Power Is Restored**

Battery-independent restart ensures automatic UPS power-up without user interaction after lengthy power outages, even after a complete battery discharge. This can save you a costly site visit.

**Versatile Installation Options**

Hardware is included for mounting the UPS system in 2U of space in an EIA-standard 19-inch 4-post rack. You can also adapt it for 2-post rack mounting with the optional RK2PC (sold separately) or tower installation using the included support stands. The eight-foot power cord with NEMA 5-20P plug connects to any compatible AC outlet.

**TAA-Compliant for GSA Schedule Purchases**

The SU2200RTXLCD2UTAA is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

## Specifications

OVERVIEW	
UPC Code	786689875770
UPS Type	On-Line
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	16A
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 120V AC
Nominal Input Voltage Description	120V factory default
UPS Input Connection Type	5-20P
UPS Input Cord Length (ft.)	8
UPS Input Cord Length (m)	2.4
Recommended Electrical Service	120V
Input Plug Type	NEMA 5-20P
Input Cord Length (ft.)	8
Input Cord Length (m)	2.44



Powering Business Worldwide

TRIPP LITE  
SERIES

Input Current	16A
Power Factor (Input)	0.99
<b>OUTPUT</b>	
Output Capacity (VA)	2000
Output Capacity (kVA)	2
Output Capacity (Watts)	1800
Output Capacity (kW)	1.8
Power Factor	0.9
Crest Factor	3:1
Nominal Voltage Details	120V factory-default nominal voltage
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Online Mode: Sync with line $\pm 5\%$ of nominal line frequency (outside this range: $\pm 0.5\%$ of auto-selected nominal frequency). Battery Mode: $\pm 0.5\%$ of auto-selected nominal frequency
Output Voltage Regulation (Line Mode)	+/- 1%
Output Voltage Regulation (Economy Line Mode)	+/- 1%
Output Voltage Regulation (Battery Mode)	+/- 2%
Load Management Receptacles	Two switchable two-outlet load banks
Output AC Waveform (AC Mode)	Pure Sine wave
Output (Watts)	1800
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	100V; 110V; 115V; 120V; 127V
Output Receptacles	(6) 5-20R; (1) L5-20R
Individually Controllable Load Banks	Yes
<b>BATTERY</b>	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	7.7 min. (1800W)
Runtime Half Load (min.)	20.2 min. (900W)
Expandable Runtime	Yes
Expandable Runtime Description	Add up to 4 extended battery modules (EBM). Part number <a href="https://tripplite.eaton.com/External-72V-Battery-Module-for-select-Tripp-Lite-series-UPS-2U-TAA~BP72RT2UTAA">BP72RT2UTAA</a>
External Battery Pack Compatibility	<a href="https://tripplite.eaton.com/External-72V-Battery-Module-for-select-Tripp-Lite-series-UPS-2U-TAA~BP72RT2UTAA">BP72RT2UTAA</a>
DC System Voltage (VDC)	72

Battery Recharge Rate (Included Batteries)	3 hours recharge to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//tripplite.eaton.com/replacement-battery-for-eaton-9px-ups-and-ebm-744-A3121">744-A3121</a>&nbsp;
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Online, double-conversion power conditioning
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, frequency, operating mode, alarm function and a variety of additional options
Switches	RPO / ROO
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
LED Indicators	4 status-indicating LEDs
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	190
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	190
AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount
Rack Height	2U
Cooling Method	Fan
Included Mounting Accessory Description	Includes 4 post rackmount installation accessories
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (&nbsp;<a class="productLink" href="//tripplite.eaton.com/eaton-2-post-rack-mount-rail-kit-for-9px-ups-RK2PC">RK2PC</a>&nbsp;)
Minimum Required Rack Depth (cm)	68.07
Minimum Required Rack Depth (inches)	26.8
Optional Mounting Accessory Notes	2 post rail kit available, part # &nbsp;<a class="productLink" href="//tripplite.eaton.com/eaton-2-post-rack-mount-rail-kit-for-9px-ups-RK2PC">RK2PC</a>&nbsp;
Shipping Dimensions (hwd / in.)	9.45 x 22.84 x 30.71



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Weight (lbs.)	76.28
Shipping Weight (kg)	34.60
UPS Housing Material	Metal
Unit Dimensions (hwd / in.)	3.410 x 17.330 x 23.820
Unit Weight (lbs.)	61.51
Unit Weight (kg)	27.90
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	With battery: 32° to 104°F (0° to 40°C); without battery: -13° to 131°F (-25° to 55°C)
Relative Humidity	0 to 96%, non-condensing
AC Mode Efficiency Rating (100% Load)	91.4
AC Economy Mode Efficiency Rating (100% Load)	96.8
Online Mode Heat Dissipation (BTU/Hr) @ Full Load	578
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	974
Operating Elevation	0-10000 ft. (0-3000 m)
Audible Noise	47 dB at 1m
<b>COMMUNICATIONS</b>	
Network Management Cards	(1) <a href="https://tripplite.eaton.com/Network-Card-Eaton-Tripp-Lite-Series-UPS-Systems-WEBCARDLXE">WEBCARDLXE</a>
Network Monitoring Port Description	WEBCARDLXE Supports detailed monitoring of UPS and site power conditions; DB9 port supports RS232 and contact closure communications; not compatible with WEBCARDLX
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	USB and RS232 cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management card optional
Communications Interface	(1) Contact closure; (1) RS-232; (1) Slot for SNMP/Web interface; (1) USB
Emergency Power Off (EPO)/Remote On-Off (ROO)	Yes
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	0ms
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported



Powering Business Worldwide

TRIPP LITE  
SERIES

High Availability UPS Features	Expandable battery backup; Hot swappable batteries; On-Line/Double-Conversion; Pure sine wave output; Remote management; Surge/noise protection; Zero transfer time
Green Energy-Saving Features	High efficiency economy mode operation; Individually controllable load banks
<b>APPLICATIONS</b>	
UPS Applications	Mission Critical Applications
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 1778; cTUVus
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 & <a href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>
Extended Service Plans	<b>ADVANCED DEPOT EXCHANGE</b> Service Part Number: TL9SW5Y-2200UC Parts, electronics and UPS batteries coverage Next business day shipping Technical support <b>5-year onsite plan: TLWFLN75XX-2509UC</b> Onsite parts and labor coverage for 5 years Parts, electronics and UPS batteries coverage 24x7 onsite labor coverage, next-day response Next-day shipping Technical support

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.