

SmartOnline SVX Series 60kVA 400/230V 50/60Hz Modular Scalable 3-Phase On-Line Double- Conversion Small-Frame UPS System, No Battery Modules

MODEL NUMBER: **SVX60KS2P0B**



Description

Tripp Lite's SVX60KS2P0B 60kVA/60kW SmartOnline® Small-Frame UPS includes installed input, bypass and output breakers, a static transfer switch (STS) and 2 included 30kVA SVX30PM power modules. This system supports the addition of 1 additional user-installable SVX30PM power module to accommodate increased capacity to 90kW (or 60kW with N+1). No internal or external batteries are included, but up to three SVXBM internal modules may be added. For additional runtime, you may also connect a variety of external battery cabinets, such as BP480V200, BP480V300, BP480V400, BP480V500 and BP480V370 (all sold separately).

Featuring a modular, scalable design with high-efficiency voltage and frequency independent/VFI operation, Tripp Lite's SVX Series SmartOnline UPS systems are ideal for the protection of a wide variety of critical IT systems. Scalable, modular configuration enables UPS capacity upgrades and hot-swap power supply maintenance without costly downtime. Over 95% efficient in standard on-line mode and over 99% efficient in optional economy mode enables reduced operating and cooling costs. Unity power factor configuration provides equal kVA and kW output ratings for up to 25% more wattage capacity than common 0.8 – 0.9 power factor competing designs. Network-grade sine-wave AC output with 1% output voltage regulation and less than 1.5% output total harmonic distortion. Advanced IGBT inverter with Digital Signal Processor (DSP) technology provides for less than 3% input total harmonic distortion (THDi) to support 1:1 generator sizing. Dual-input hardwire design enables operation from one or two input power sources for enhanced system availability. N+1 fault-tolerance is configurable anytime there is an "extra" SVX30PM 30kW power module installed beyond the minimum required quantity. Automatic and manual bypass options keep connected equipment operational during routine maintenance or critical power module failure.

Features

- Tripp Lite's SVX60KS2P0B 60kVA/60kW SmartOnline UPS offers network-grade power protection in a highly configurable small-frame modular, scalable form factor
- Includes 2 SVX30PM 30kW power modules for 60kVA total capacity; open slot for one additional

Highlights

- 60kVA/60kW Modular, Scalable, 3-Phase Small-Frame Tower UPS
- Supports 3-Phase 220/380V, 230/400V or 240/415V AC, 50/60Hz, Wye; scalable to 90kVA
- High-efficiency on-line UPS with DSP/IGBT technology and 1% output voltage regulation
- Pre-installed WEBCARDLX network interface; economy mode option reduces operating and cooling costs
- Does not include internal battery modules, several battery options available; tested to CE for worldwide applications

Package Includes

- SVX60KM2P0B Small-Frame Modular UPS System
- (2) SVX30PM 30kVA Power Modules
- Pre-installed WEBCARDLX network interface
- Owner's manual



SVX30PM power module enables scalable capacity configurations up to 90kW

- No internal or external batteries are included, but up to three SVXBM internal modules may be added
- For additional runtime, choose from a variety of external battery options, such as BP480V200, BP480V300, BP480V400, BP480V500 or BP480V370
- Supports 220/380, 230/400 or 240/415V AC, 3-Phase Wye 4-Wire, plus Earth Hardwire input and output wiring
- Tested to CE for worldwide applications
- Pre-installed WEBCARDLX network interface
- Serial port enables unattended shutdown and UPS monitoring ability
- Modular configuration with hot-swappable power modules enables easy and fast maintenance with zero downtime
- Wide input voltage operating range enables full continuous on-line operation during brownouts as low as 120V (Ph-N) and overvoltages up to 276 (Ph-N)
- Narrow output voltage operating range regulates output voltage within 1% of the selected 220/230/240 nominal output voltage in on-line, double-conversion mode
- Over 95% efficient in on-line, double-conversion mode and over 99% efficient in optional economy-mode enables reduced operating and cooling costs
- Less than 3% input Total Harmonic Distortion (THDi) prevents the need to oversize generator systems relative to UPS capacity
- Dual hardwire input design enables operation from one or two input power sources
- Front-panel combination LCD/LED display offers full UPS condition and status reporting, plus additional configuration options

Specifications

OVERVIEW	
UPC Code	037332242693
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	60kVA Configuration: 110A; Maximum 90kVA N+1 Medium Chassis Configuration: 165A; 40A maximum inrush current
Nominal Input Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Nominal Input Voltage Description	Set of two hardwire input connections enables 3-Phase Wye, 4 wire (3P, N, E) inputs from two separate power sources
UPS Input Connection Type	Hardwire
Input Circuit Breakers	MAIN and ALTERNATE AC inputs are each protected by 400A 3 pole magnetic breakers



Tripp Lite
 1111 W. 35th Street
 Chicago, IL 60609 USA
 Telephone: 773.869.1234
 www.tripplite.com

Input Phase	3-Phase
Input Frequency	40 to 70Hz (online mode); 50/60Hz Auto-selectable
Power Factor (Input)	Greater than 0.99 (full load)
THDi	Less than 3% (full linear load)
OUTPUT	
Output Volt Amp Capacity (VA)	60000
Output kVA Capacity (kVA)	60
Output Watt Capacity (Watts)	60000
Output kW Capacity (kW)	60
Output Capacity Details	OVERLOAD CAPABILITY: Supports 105-110% load for 1 hour, 111-125% load for 10 minutes, 126-150% for 1 minute and Over 150% for 200ms before switching to Bypass; Online operation resumes when load is reduced to 100% or less
Power Factor	1.0
Crest Factor	3:1
Nominal Voltage Details	Output THD full resistive load: <1.5%; Output THD non-linear load: <4%; Max DC offset: $\pm 50\text{mV}$; Max Phase angle deviation: 2°; Max Voltage unbalance deviation: 1%; Output short-circuit protection included
Frequency Compatibility	50 / 60 Hz; Supports 50 to 60 Hz and 60 to 50 Hz conversion
Frequency Compatibility Details	Auto-selectable, user adjustable
Output Receptacle Details	Output wiring: 3P, N, E
Output Circuit Breakers	400A 3 pole magnetic breaker
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Output Receptacles	Hardwire
Output Voltage Regulation	ONLINE, FREQUENCY CONVERSION, BATTERY MODE: 220/230/240V $\pm 1\%$ typical (balanced load); $\pm 2\%$ typical (unbalanced load); ECONOMY MODE: 220/230/240V $\pm 15\%$; BYPASS MODE: +15% (default, adjustable to +10%, +15% or +20%), -20% (default, adjustable to -10%, -20%, -30%)
Output Frequency Regulation	ONLINE MODE: Output frequency is $\pm 0.05\text{Hz}$ of input frequency when input is within $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting; Output frequency is $\pm 0.05\text{Hz}$ the configured 50/60Hz output setting when input is outside $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting; BATTERY MODE: Output frequency is $\pm 0.1\text{Hz}$ of the configured 50/60Hz output setting; FREQUENCY CONVERTER MODE: Output frequency is $\pm 0.1\text{Hz}$ of the configured 50/60Hz output setting; ECONOMY MODE: Output frequency equals input frequency up to $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting (UPS switches to Online mode if frequency goes outside of this range); BYPASS MODE: Output frequency equals input frequency up to $\pm 4\text{Hz}^*$ of the configured 50/60Hz output setting (switches to STANDBY mode if frequency goes outside of this range). *The TRACKING RANGE is factory set to $\pm 4\text{Hz}$ and is user adjustable to $\pm 1\text{Hz}$, $\pm 2\text{Hz}$ or $\pm 4\text{Hz}$; The selected TRACKING RANGE setting controls frequency output tolerances as described above in Online, Economy and Bypass modes
Output Amp Capacity	91A (220/380V); 87A (230/400V); 83A (240/415V)
Individually Controllable Load Banks	No
Modular Upgrade Options	Includes 2 SVX30PM 30kVA power modules; Up to 1 additional SVX30PM 30kVA power module can be added for additional capacity or N+1 availability; Add 1 SVX30PM for 90kVA capacity (or 60kVA with N+1 redundancy)



BATTERY	
Expandable Battery Runtime	Supports extended runtime with optional external battery packs; 100A 3 pole 250VDC breaker recommended for external battery
External Battery Pack Compatibility	 BP480V200 ; BP480V300 ; BP480V400 ; BP480V500 ; BP480V370 ;
Expandable Runtime Description	External battery pack wiring is contractor supplied; All external battery configurations require the disconnection of all internal battery modules
DC System Voltage (VDC)	±240VDC
Battery Recharge Rate (Included Batteries)	User selectable charging current of 1A to 8A (2A factory setting); Recharge rate is dependent on number of external battery packs connected and the selected charge current setting
Battery Replacement Description	Hot-swappable, replaceable batteries
Expandable Runtime	Yes
POWER	
LED Indicators	Front panel LED indicators represent INPUT (green), BYPASS (amber), INVERTER (green), BATTERY (red) and ALARM (red)
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	Maintains continuous output in online mode, without using battery power, during overvoltages to 478V (Ph-Ph), reducing output to within 1% of selected 380/220V, 400/230V, 415/240V nominal output voltage
Undervoltage Correction	Maintains continuous output in online mode, without using battery power, during brownout/undervoltage conditions to 305V (Ph-Ph) at full load and to 208V (Ph-Ph) at 70% output load or less, increasing output to within 1% of selected 380/220V, 400/230V, 415/240V nominal output voltage
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	145mm front panel LCD display with directional scroll and select buttons offers complete operating status display, plus setting and selection options for all UPS functions
Switches	Front panel buttons include ESC (menu escape), UP/LEFT (menu up / left), DOWN/RIGHT (menu down / right), ENTER (confirm selection), HOME (return to home screen) and POWER (on/off power control); Also includes Manual Bypass switch
Alarm Cancel Operation	Audible alarms can be muted using on-screen prompts
Audible Alarm	Unique audible alarms for POWER ON / POWER OFF (alarm sounds for 2 seconds), BATTERY MODE (alarm sounds every 2 seconds), LOW BATTERY (alarm sounds every 0.5 seconds), UPS ALARM (alarm sounds every 1 second), UPS FAULT (continuous alarm)
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	2180
AC Suppression Joule Rating Details	2180 joules (Ph-Ph), 2180 joules (Ph-N), 1560 joules (N-E)



AC Suppression Response Time	Instantaneous
PHYSICAL	
Cooling Method	Fans
Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
Primary UPS Depth (mm)	1,100
Primary UPS Height (mm)	1,475
Primary UPS Width (mm)	600
Shipping Dimensions (hwd / cm)	164.49 x 74.98 x 122.00
Shipping Dimensions (hwd / in.)	64.76 x 29.52 x 48.03
Shipping Weight (kg)	388.50
Shipping Weight (lbs.)	856.50
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, in.)	58.07 x 23.62 x 43.3
UPS Power Module Weight (kg)	640.47
UPS Power Module Weight (lbs.)	1412
ENVIRONMENTAL	
Operating Temperature Range	0° to +40°C (+32° to +104°F); De-rates to 90% capacity at 35°C / 95°F and 80% capacity at 40°C / 104°F
Storage Temperature Range	-15° to +60°C (+5° to +140°F)
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	11458
AC Economy Mode BTU / Hr. (Full Load)	890
AC Mode Efficiency Rating (100% Load)	95%
AC Economy Mode Efficiency Rating (100% Load)	99%
Audible Noise	Less than 73 DBA front-side, 1m
Operating Elevation (m)	Up to 1000m (At elevations over 1000m, output de-rates by 1% per 100m)
COMMUNICATIONS	
Network Management Cards	WEBCARDLX MODBUSCARDSV RELAYCARDSV
Network Monitoring Port Description	Includes pre-installed Tripp Lite WEBCARDLX network interface



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	DB9 cabling included
SNMP Compatibility	Includes pre-installed WEBCARDLX network interface card
Communications Interface	DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode; Less than 20 ms. transfer time in economy mode
Low Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during brownout/undervoltage conditions to 305V (Ph-Ph) Full load or 208V (Ph-Ph) 70% load or less; Below the low transfer voltage point, output is maintained utilizing reserve battery power
High Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during overvoltages to 478V (Ph-Ph), reducing output within 1% of nominal; Above this point, output is maintained utilizing reserve battery power
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries; Auto Probe Monitoring (included); Zero transfer time; On-Line/Double-Conversion
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; High efficiency economy mode operation; Schedulable daily hours of economy mode operation
STANDARDS & COMPLIANCE	
UPS Certifications	CE; ROHS (Restriction of Hazardous Substances)
Certification Details	Agency standards IEC 62040-1:2008+A1:2013; EMI Approvals EN62040-2, 2006 (Category C3)
WARRANTY	
Product Warranty Period (International)	2-year limited warranty
3-Phase Warranty Statement	Tripp Lite 3-Phase UPS Factory Warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>