

## Protect It! 10-Outlet Surge Protector, 6 ft. Cord, 2880 Joules, Black Housing

MODEL NUMBER: TLP1006B



### Highlights

- 10 widely spaced NEMA 5-15R outlets
- 2880-joule surge protection rating
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 6 ft. AC power cord with right-angle NEMA 5-15P plug

### Package Includes

- TLP1006B Protect It! 10-Outlet Surge Protector, Black Housing
- Owner's manual

Safeguard your PC, printer, scanner, router, modem and other home electronics against dangerous surges, spikes and line noise. Recommended for home, office, workstations, dorms and hotel rooms.

### Description

Perfect for your home or office workstation, the TLP1006B Protect It!® 10-Outlet Surge Protector features a surge protection rating of 2880 joules to defend your sensitive electronic components against strong surges and spikes. In fact, Tripp Lite will repair or replace any connected equipment damaged by surges up to \$100,000 for life (valid in the U.S., Canada and Puerto Rico only).

The TLP1006B includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression, as well as technology that filters out EMI/RFI line noise, preventing interference from disrupting your electronics and inflicting damage or data loss.

Your computer and peripherals plug into 10 NEMA 5-15R outlets that are spaced apart to accept bulky transformers without blocking adjacent outlets. Safety covers keep dust and debris away from unused outlets. Integrated 15A circuit breaker protects all outlets and shuts down connected equipment in case of overload. On/off switch provides one-touch control over connected equipment. Diagnostic LED bars indicate power and protection status.

The six-foot (1.8-meter) AC power cord with right-angle NEMA 5-15P plug allows furniture and equipment to be placed flush against the wall. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the black plastic housing.

### Features

**2880-Joule Surge Protection for Home or Office Electronics** Protects your computer, printer, scanner, external hard drive and other sensitive electronics against even the strongest surges and spikes  
Recommended for home, office, workstations, dorms and hotel rooms  
Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression  
Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss  
Exceeds IEEE 587 Category A and B surge suppression specifications

**10 Outlets Accept Wide Range of Electronic Devices** 10 NEMA 5-15R AC outlets accept most computers and peripherals  
Outlets spaced widely apart to accept bulky transformers

**Premium Safety Features** On/off switch provides one-touch control over connected equipment  
Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required  
Diagnostic LED bars show power and protection status at a glance  
Safety covers protect unused outlets from dust and debris

**Fits Effortlessly Into Your Workstation** 6 ft. AC power cord with right-angle NEMA 5-15P plug allows furniture and equipment to be placed flush against the wall  
Keyhole slots on bottom panel provide



convenient wall or desk mounting options Black plastic housing designed for long life

**Backed by Tripp Lite's Ultimate Lifetime Insurance** \$100,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

## Specifications

| OVERVIEW                           |  |
|------------------------------------|--|
| UPC Code                           | 037332200013   |
| INPUT                              |  |
| Nominal Input Voltage(s) Supported | 120V AC  |
| Recommended Electrical Service     | 120V   |
| Input Plug Features                | Right Angle (90D)  |
| Input Cord Gauge Type              | 14 gauge   |
| Input Cord Gauge (AWG)             | 14   |
| Voltage Compatibility (VAC)        | 120  |
| Input Plug Type                    | NEMA 5-15P   |
| Input Cord Length (ft.)            | 6  |
| Right-Angle Plug                   | Yes  |
| Input Cord Length (m)              | 1.83   |
| Integrated Cord Clip               | No   |
| OUTPUT                             |  |
| Frequency Compatibility            | 60 Hz  |
| Output (Watts)                     | 1800   |
| Output Receptacles                 | (10) 5-15R   |
| Circuit Breaker (amps)             | 15   |
| Transformer Accommodation          | (10) Yes   |
| Right-Angle Outlets                | Yes  |
| USER INTERFACE, ALERTS & CONTROLS  |  |
| Diagnostic LED(s)                  | Yes  |
| SURGE / NOISE SUPPRESSION          |  |
| AC Suppression Joule Rating        | 2880   |
| AC Suppression Response Time       | < 1ns  |
| Protection Modes                   | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression |



|   |  |
|---|--|
| UL1449 Let Through Rating                         | 330,400,400  |
| EMI / RFI Filtering                               | Yes  |
| Immunity  | Conforms to IEE 587/ANSI C62.41  |
| Automatic Shut-Off                                | Yes  |
| <b>DATALINE SURGE SUPPRESSION</b>                 |  |
| Cable (Coax) Protection                           | No   |
| Network (Ethernet) Protection                     | No   |
| Telephone/DSL Protection                          | No   |
| <b>PHYSICAL</b>                                   |  |
| Material of Construction                          | Plastic  |
| Antimicrobial                                     | No   |
| Power Cord Color                                  | Black  |
| Housing Color                                     | Black  |
| Mounting Holes or Slots                           | No   |
| Slot or Hole Mount Measurement (Center to Center) | 195 mm   |
| Receptacle Color                                  | Black  |
| Shipping Dimensions (hwd / cm)                    | 4.06 x 22.10 x 34.54   |
| Shipping Dimensions (hwd / in.)                   | 1.60 x 8.70 x 13.60  |
| Shipping Weight (kg)                              | 0.96   |
| Shipping Weight (lbs.)                            | 2.12   |
| Unit Dimensions (hwd / in.)                       | 1.29 x 5.7 x 11.1  |
| Unit Weight (lbs.)                                | 1.71   |
| Unit Weight (kg)                                  | 0.78   |
| Input Cord Color                                  | Black  |
| <b>FEATURES &amp; SPECIFICATIONS</b>              |  |
| Rotatable Outlets                                 | No   |
| <b>STANDARDS &amp; COMPLIANCE</b>                 |  |
| Approvals   | RoHS   |
| UL1449 3rd Edition (AC Suppression)               | UL1363:2018 (5th Ed); UL1449:2014 (4th Ed), CAN/CSA-C22.2 No. 269.3:2017 (2nd Ed); CAN/CSA-C22.2 No.308-14 |
| NOM (Mexico)                                      | NOM  |
| UL1363 (Power Tap)                                | UL1363   |
| UL497A (Communications)                           | No   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

|  |   |
|--|---|
| Industry Canada (Communications)                           | No  |
| <b>WARRANTY</b>  |   |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty   |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$100,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp; |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>