

Protect It! 6-Outlet Surge Protector, 4 USB Ports, 6 ft. Cord, 1080 Joules, Diagnostic LED, Black Housing

MODEL NUMBER: TLP66USBR



Highlights

- 6 NEMA 5-15R outlets for connecting equipment
- 4 USB ports with 3.4A shared for charging
- 1080-joule surge protection rating against surges and spikes
- Filters out EMI/RFI line noise that threatens connected hardware
- 6 ft. AC power cord with NEMA 5-15P plug

Package Includes

- TLP66USBR Protect It! 6-Outlet Surge Protector with USB Charger, Black Housing
- Owner's manual

6-outlet surge suppressor safeguards your computer, printer, router and other small home electronics against surges, spikes and line noise.

Description

Recommended for your home or office workstation, the TLP66USBR Protect It!® 6-Outlet Surge Suppressor features a surge protection rating of 1080 joules to defend your sensitive electronic components against strong surges and spikes. In fact, Tripp Lite will repair or replace any connected equipment damaged by surges up to \$50,000 for life (valid in the U.S., Canada and Puerto Rico only). Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP66USBR protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G). It also filters out electromagnetic interference (EMI) and radio frequency interference (RFI) that can disrupt your electronics and inflict hardware damage or data loss.

This surge protector features six NEMA 5-15R outlets, two of which are spaced to accept bulky transformers without blocking adjacent outlets. A retractable USB charger with 4.5-foot (1.4-meter) cord clamps to your desk or other work surface for easy access. Its four USB-A ports share 3.4 amps for charging connected mobile devices, such as tablets and smartphones.

An integrated 15A circuit breaker protects all outlets and automatically shuts down connected equipment in case of overload. The lighted on/off switch provides one-touch control over connected equipment. The six-foot (1.8-meter) AC power cord with NEMA 5-15P plug reaches nearby outlets to fit easily into your workstation or home theater setup.

Features

1080-Joule Surge Protection for Home or Office Electronics Protects your computer, printer, scanner, router, modem and other small home electronics against surges and spikes
 Recommended for desktop, network or home electronics applications requiring AC line protection
 Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
 Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss
 Exceeds IEEE 587 Category A and B surge suppression specifications

6 Outlets Accept Wide Range of Electronic Devices 6 NEMA 5-15R AC outlets accept most computers and peripherals
 2 outlets specially spaced for bulky transformers without blocking other outlets
 4 USB ports with 3.4A shared

Premium Safety Features Lighted on/off switch provides one-touch control over connected equipment
 Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
 Diagnostic LED confirms protection status at a glance
 Conforms to current UL 1449 3rd Edition safety standards



Fits Effortlessly Into Your Workstation 6 ft. AC power cord with NEMA 5-15P plug reaches nearby outlets
Clip-on or on-site USB charger with 4.5 ft. retractable extender cord
Black plastic housing designed for long life

Backed by Tripp Lite's Ultimate Lifetime Insurance \$50,000 Ultimate Lifetime Insurance covers any connected components damaged by power surge (U.S., Canada and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332210135
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Plug Features	Right Angle (36D)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Right-Angle Outlets	Yes



USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
CHARGING	
Number of Charging Ports	4
Total Charging Watts	17
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(4) 3.4A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	9.65 x 6.69 x 1.77
Shipping Dimensions (hwd / cm)	24.51 x 16.99 x 4.50
Shipping Weight (lbs.)	1.91
Shipping Weight (kg)	0.87



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / in.)	9.6 x 6.7 x 1.8
Unit Dimensions (hwd / cm)	24 x 17 x 4.6
Unit Weight (lbs.)	1.8
Unit Weight (kg)	0.82
Input Cord Color	Black
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Rotatable Outlets	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Industry Canada (Communications)	No
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>