

SmartOnline 80kVA Modular 3-Phase UPS System, On-line Double-Conversion International UPS (not expandable to 120kVA)

MODEL NUMBER: **SU80KX**



Description

Tripp Lite's SU80KX (80kVA) SmartOnline Modular 3-Phase Intelligent, True On-Line UPS System provides 100% system availability with N+1 modular architecture and 1+1 parallel capability. In N+1 configuration, the SU80KX provides four self-contained, redundant 20kVA power modules that can be hot-swapped (load remaining powered) if maintenance is required. In 1+1 configuration, two SU80KX models connected in parallel can provide fail-safe redundancy (two 80kVA models supporting a 80kVA load) or increased capacity (two 80kVA models supporting a 160kVA load). Large capacity 80,000VA/64,000W UPS continually converts incoming AC power into filtered DC power, and then resynthesizes it back into AC power with a pure sine wave. Perfectly regulated, continuous sine wave output with zero transfer time assures compatibility with all equipment types. High input power factor, advanced IGBT inverter technology and Digital Signal Processor (DSP) technology produce less than 3% input total harmonic distortion (THDi). With low THDi, generators run cooler and last longer, allowing managers to save installation costs by installing a generator with a capacity equal to the equipment load (1:1 ratio). Extremely efficient operation (up to 97%) saves money by lowering electricity consumption. Hardwire input and output connections. Frequency is 50 or 60 Hz (auto-selectable). SU80KX power modules are housed in a single small-footprint tower compartment. Battery module (Model BP480V40C) is housed in a separate stand-alone hardwired external battery compartment (required for UPS operation/backup battery support; order separately). Battery runtime can be extended with additional stand-alone hardwired external battery modules. A manual bypass breaker and an automatic bypass function ensure 100% availability of connected equipment by safely passing through AC power if the UPS requires maintenance.

Features

- N+1 configuration: If maintenance is required, four self-contained, redundant 20kVA power modules can be hot-swapped with the load remaining powered
- 1+1 configuration: Two SU80KX can be connected in parallel to provide either fail-safe redundancy or increased capacity

Highlights

- 80,000 VA (80kVA) 3-phase tower UPS
- N+1 redundant modular architecture helps assure 100% availability
- 1+1 parallel capability allows for system redundancy or increased capacity
- Low THDi reduces installation costs by permitting 1:1 generator sizing
- 3-phase hardwire (220/380V, 230/400V or 240/415V AC, 3-phase, 4-wire + ground, wye) input/output
- IGBT technology and zero transfer time, on-line, double-conversion operation
- Runtime is expandable via external battery cabinet options

Package Includes

- SU80KX UPS System
- Serial cable
- Instruction manual
- Warranty information



- High input power factor, advanced IGBT inverter technology and Digital Signal Processor (DSP) technology produce low input total harmonic distortion (THDi)
- Low THDi (less than 3%) reduces installation costs by allowing 1:1 generator sizing
- Extremely efficient operation (up to 97%) saves money by reducing electricity consumption
- True on-line, double-conversion UPS with IGBT technology provides pure sine wave AC output at all times
- Maintains continuous operation with zero transfer time through blackouts, voltage fluctuations and surges
- Removes harmonic distortion, electrical impulses, frequency variations and other hard-to-solve power problems
- 80,000VA/64,000W power capacity with 3-phase, hardwire input/output connections
- Wide input voltage correction range: 173-300V/276-477V AC
- Precision +/-1% output voltage regulation
- Battery modules (Model BP480V40C) are housed in a separate, stand-alone hardwired external battery compartment (required for UPS operation/backup battery support; order separately)
- Battery runtime can be extended with additional stand-alone hardwired external battery modules (Model BP480V40C; order separately)
- Front panel combination LCD/LED display includes a real-time event log screen with up to 500 events listed
- Dynamic battery management screen optimizes battery function to lengthen service life and allow cold restart of the UPS
- Serial port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- Compatible Tripp Lite UPS management card options TLNETCARD, WEBCARDLX and SNMPWEBCARD support a wide variety of UPS control and monitoring capabilities
- Emergency Power Off button turns UPS output OFF and disables Bypass output
- Built-in Emergency Power Off (EPO) dry-contact interface supports remote emergency shutdown in large facilities

Specifications

OVERVIEW	
UPC Code	037332141422
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	121A / 116A / 111A
Nominal Input Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Nominal Input Voltage Description	3-Phase Wye, 4 wire (L1, L2, L3, N, G)
UPS Input Connection Type	Hardwire
Input Phase	3-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	80000
Output Capacity (kVA)	80



Output Watt Capacity (Watts)	64000
Output kW Capacity (kW)	64
Power Factor	0.8
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz
Output Voltage Regulation (Line Mode)	+/-1%
Output Voltage Regulation (Battery Mode)	+/-1%
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Output Receptacles	Hardwire
Individually Controllable Load Banks	No
BATTERY	
Expandable Battery Runtime	Battery set sold separate
Expandable Runtime	Yes
Expandable Runtime Description	External battery pack wiring is contractor supplied
External Battery Pack Compatibility	 BP480V200 BP480V300 BP480V400 BP480V40C BP480V500
DC System Voltage (VDC)	+/- 240VDC
Battery Replacement Description	Hot-swappable, replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	Maintains continuous operation without using battery power during overvoltages to 276-477 (3-phase, 4-wire, wye), reducing output within 1% of nominal
Undervoltage Correction	Maintains continuous operation without using battery power during brownout/undervoltage conditions to 173-300 (3-phase, 4-wire, wye)
USER INTERFACE, ALERTS & CONTROLS	
Switches	ON button turns UPS inverter on. OFF button turns UPS inverter off. LCD Display Control Buttons browse through and select items displayed on LCD screen. EPO (Emergency Power Off) button turns UPS output off and disables Bypass output
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Alarms signal a variety of operational conditions: low-battery, overload, shutdown, bypass and more



LED Indicators	4-LED Display: Displays normal AC input, on battery power, bypass input and fault conditions
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	5950
AC Suppression Response Time	Instantaneous
PHYSICAL	
Primary Form Factor	Tower
Cooling Method	Fans
Installation Form Factors Supported with Included Accessories	Tower
Primary UPS Depth (mm)	856
Primary UPS Height (mm)	1,168
Primary UPS Width (mm)	521
Shipping Dimensions (hwd / cm)	139.70 x 72.39 x 107.95
Shipping Dimensions (hwd / in.)	55.00 x 28.50 x 42.50
Shipping Weight (kg)	311.98
Shipping Weight (lbs.)	687.80
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	116.84 x 52.07 x 85.60
UPS Power Module Dimensions (hwd, in.)	46 x 20.5 x 33.7
UPS Power Module Weight (kg)	244.03
UPS Power Module Weight (lbs.)	538
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	14016
Battery Mode BTU / Hr. (Full Load)	13951
COMMUNICATIONS	
Network Management Cards	 SNMPWEBCARD ; TLNETCARD ; WEBCARDLX



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	DB9 cabling included
Communications Interface	DB9 Serial; Slot for SNMP/Web interface
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during brownout/undervoltage conditions to 173-300V AC (3-phase, 4-wire, wye). Below this point, output is maintained utilizing reserve battery power
High Voltage Transfer to Battery Power (Setpoint)	Maintains continuous operation without using battery power during overvoltages to 276-477V AC (3-phase, 4-wire, wye), reducing output within 1% of nominal. Above this point, output is maintained utilizing reserve battery power
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries
Green Energy-Saving Features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
STANDARDS & COMPLIANCE	
UPS Certifications	CE
WARRANTY	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty
3-Phase Warranty Statement	Tripp Lite 3-Phase UPS Factory Warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>