

USB 2.0 A to B Cable (M/M), 3 ft. (0.91 m)

MODEL NUMBER: U021-003



Description

Tripp Lite's 3-ft. (0.91 m) USB2.0 A/B device cable has been tested meets or exceed the USB2.0 performance criteria. Connects a USB device to a USB port on a computer or hub. Backward compatible — can be used with older USB1.1 applications as well. All Tripp Lite USB 2.0 cabling include superior foil shielding for reliable, error-free data communications. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) make them perfect for multimedia applications. Features gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- USB 2.0 Tested
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Gold plated copper contacts for superior conductivity
- Molded connectors and integral strain relief for extra durability and long life

Specifications

OVERVIEW	
UPC Code	037332119421
Technology	USB 2.0 (High Speed)
Cable Type	Passive
PHYSICAL	
Cable Jacket Color	Gray
Cable Length (ft.)	3

Highlights

- Includes superior foil shielding for reliable, error-free data communications
- Features gold plated copper contacts for superior conductivity
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Molded connectors and integral strain relief for extra durability and long life

System Requirements

- Any USB device requiring a USB cable
- USB 2.0 performance only when used with USB 2.0 device and USB 2.0 controller

Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.09
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 0.24
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB B (MALE)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty