

3-Breaker Parallel Tie Cabinet with Maintenance Bypass Switch (for SU80KX 3-Phase UPS)

MODEL NUMBER: SUPC4MBP80KX



Highlights

- 3 breaker parallel tie cabinet accessory for four Tripp Lite 80kVA 3 phase UPS systems
- Links the output of four UPS systems for 320kVA non-redundant operation
- Integral Maintenance Bypass switch enables UPS maintenance or replacement
- 3 built-in circuit breakers, heavy duty copper buswork
- Compatible with Tripp Lite SU80KX 3 phase UPS systems

Description

Tripp Lite's parallel tie cabinet provides a means for safely paralleling two UPS systems for non-redundant combined mode operation. Non-redundant configuration combines the output of four UPS systems to support four times the output current. Built-in Maintenance Bypass Switch enables UPS maintenance and repair of with no disruption in power to connected equipment. Two input breakers receive incoming power from the UPS and are connected to heavy duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined. See owners manual and [Tripp Lite Parallel Tie Cabinet with Bypass Panel](#) download for detailed specifications, dimensional drawings, operational flow charts and technical descriptions.

Compatible with four Tripp Lite SU80KX UPS systems.

Features

- Provides a means for safely paralleling two UPS systems for non-redundant combined mode operation
- Non-redundant configuration combines the output of four UPS systems to support four times the output current
- Built-in Maintenance Bypass Switch enables UPS maintenance and repair of with no disruption in power to connected equipment
- Two input breakers receive incoming power from the UPS and are connected to heavy duty copper buswork and an output breaker rated for the total UPS capacity of the two UPS systems combined
- Compatible with four Tripp Lite SU80KX UPS systems

Specifications

OVERVIEW



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPC Code	037332167231
INPUT	
Nominal Input Voltage(s) Supported	380V AC; 400V AC; 415V AC
Voltage Compatibility (VAC)	380; 400; 415
PHYSICAL	
Form Factors Supported	Wallmount
Shipping Dimensions (hwd / cm)	178.44 x 98.76 x 31.75
Shipping Dimensions (hwd / in.)	70.25 x 38.88 x 12.50
Shipping Weight (kg)	222.26
Shipping Weight (lbs.)	490.00
Unit Dimensions (hwd / cm)	176.5 x 96.8 x 30
Unit Dimensions (hwd / in.)	69.5 x 38.1 x 11.8
Unit Weight (kg)	219.99
Unit Weight (lbs.)	485
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>