



# USB to Null Modem Serial FTDI Adapter Cable with COM Retention (USB-A to DB9 M/F), 18-in. (45.72 cm)

# MODEL NUMBER: U209-18N-NULL











Connect a RS-232 Null Modem serial device to the USB-A port on your computer, laptop or tablet.

#### **Features**

#### Converts USB Port into RS-232 Null Modem Serial Port

- Solves DCE/DTE conflicts without additional cross-wired serial cables or adapters
- Supports data transfer speeds up to 256 Kbps—twice as fast as a built-in serial port
- No external power source required
- Portable 18 in. design fits perfectly into laptop bag
- COM retention for automatic reassigning of COM values to ports in case of disconnection or reboot
- Integrated FTDI FT232RL chipset

#### First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors with gold-plated contacts for optimal signal quality
- Integral strain relief for long life
- Flexible PVC jacket easy to install in tight spaces

## **Broad Compatibility**

Compatible with Windows, Mac and Linux operating systems

# **Specifications**

OVERVIEW		
UPC Code	037332198297	
INPUT		

#### **Highlights**

- Supports data transfer speeds up to 256 Kbps
- Premium foil and braid shielding reduces EMI/RFI line noise
- Compatible with Windows®, Mac® and Linux®
- No external power source required
- Integrated FTDI FT232RL chipset

#### **System Requirements**

 Computer or other device with available USB port and Windows XP or later, Mac OS X 10.3 or later, or Linux

## **Package Includes**

- U209-18N-NULL USB to Null Modem Serial FTDI Adapter Cable (USB-A to DB9 M/F), 18 in.
- Driver CD
- · Owner's manual





Bus Powered	Yes	
Due i emerca		
POWER		
Power Consumption (Watts)	0.5	
CONNECTIONS		
Number of Ports	1	
Side A - Connector 1	USB A (MALE)	
Side B - Connector 1	DB9 (FEMALE)	
Connector Plating	Nickel	
PHYSICAL		
Color	Black; Silver	
Material of Construction	PVC	
Cable Jacket Color	Black	
Cable Jacket Rating	VW-1	
Cable Length (ft.)	1.5	
Cable Length (m)	0.46	
Shipping Dimensions (hwd / in.)	1.50 x 3.70 x 4.50	
Shipping Dimensions (hwd / cm)	3.81 x 9.40 x 11.43	
Shipping Weight (lbs.)	0.30	
Shipping Weight (kg)	0.14	
Unit Packaging Type	Вох	
Unit Weight (lbs.)	0.07	
Unit Weight (kg)	0.03	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	14° to 131°F (-10° to 55°C)	
Relative Humidity	5% to 90% RH, Non-Condensing	
BTUs	1.7 BTU/Hr	
FEATURES & SPECIFICATIONS		
USB Specification	USB 2.0 (up to 480 Mbps)	
Driver Required	Yes	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)	
·		





WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.