


TAA-Compliant Protect It! 7-Outlet Surge Protector, 7 ft. Cord, 2450 Joules, Black Housing

MODEL NUMBER: **SUPER7BTAA**



Highlights

- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases
- 7 outlets/7 ft. cord
- 2450 joule rating

Package Includes

- SUPER7BTAA Surge Suppressor
- Instruction manual with warranty information

Description

Tripp Lite's Super7BTAA is compliant with the Federal Trade Agreement Act (TAA) for GSA schedule purchases. The SUPER7B Surge Suppressor from Tripp Lite has 7 outlets, a 7-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2450 joules to handle the strongest surges. \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- Compliant with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases
- 7 outlets
- 7-ft. cord with space-saving right-angle plug
- Surge suppression rating: 2450 joules
- Child Safety Covers
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
- EMI/RFI noise filtering
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting

Specifications

OVERVIEW	
UPC Code	037332183422



INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	7
Right-Angle Plug	Yes
Input Cord Length (m)	2.13
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2450
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400 L-G, 400 L-N, 400 N-G
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No



Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Color	Black
Color (AC Line Cord)	Black
Housing Color	Black
Integrated Keyhole Mounting Slots	Yes
Material of Construction	Plastic
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	0.00 x 0.00 x 0.00
Shipping Dimensions (hwd / in.)	0.00 x 0.00 x 0.00
Shipping Weight (kg)	0.00
Shipping Weight (lbs.)	0.00
Unit Dimensions (hwd / cm)	5.1 x 6.2 x 33.7
Unit Dimensions (hwd / in.)	2.4 x 2.0 x 13.3
Unit Weight (kg)	0.54
Unit Weight (lbs.)	1.2
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance