

7-Port USB 2.0 Hub, Tower

MODEL NUMBER: U222-007-R



Description

This 7-port USB 2.0 hub allows you to connect up to seven USB devices to a single USB port on your computer. This unit meets or exceeds USB 2.0 specifications for Hi-Speed data transmission rates up to 480 Mbps. Perfect for both the mobile and desktop user. While the hub will function perfectly in virtually all cases without needing external power, a compact, multi-voltage AC adapter (100-240V) has been provided for the rare circumstance when connecting a power-hungry device. This USB 2.0 device is backwards compatible so that it will function with both USB 2.0 and USB 1.1 devices. Over-current protection safeguards connected equipment from overvoltages. Includes stand for upright positioning.

Features

- USB2.0 7-Port Hub
- Supports data transfer rates up to 480Mbps
- Connect up to 7 USB devices to a single USB port on your computer
- Compact design is ideal for use with a laptop/notebook computer
- Does not require external power, software, or complicated set-up procedures
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- Per-port overcurrent protection
- Bus-powered or self-powered
- Supports USB 2.0 spec up to 500mA per port
- On bus-power, 500mA from the USB 2.0 computer port is shared between the hub ports
- The included external power supply provides 2.5A of power, to be shared between the hub ports (up to 500mA per port)
- Compact, multi-voltage power supply (100-240V) provided
- Compatible with all major operating systems

Highlights

- Connect up to 7 USB 2.0 devices
- Hi-Speed 480Mbps data transfer
- Backward compatible with USB 1.1 devices
- Over-current protection safeguards connected equipment from overvoltages
- Supports USB 2.0 spec up to 500mA per port
- Includes base stand for upright positioning
- Compatible with all major operating systems

System Requirements

- USB 2.0 port
- Compatible with all major operating systems

Package Includes

- U222-007-R USB 2.0 7-Port Mini Hub
- Compact External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2.5A)
- 4 ft. extension cable

Specifications

OVERVIEW	
UPC Code	037332126733

Product Type	Hub
Technology	USB 2.0 (High Speed)
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(7) USB A (FEMALE)
Data Ports Details	(7) USB-A - USB 2.0
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
AC Power Adapter Output Specs (V / A)	5V / 2.5A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	No
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2.5A
DC Barrel Plug	OD: 3.5 x 1.35 x 9.5mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	7
Side A - Connector 1	USB B (FEMALE)
Side B - Connector 1	(7) USB A (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red - Power
PHYSICAL	
Color	Black; White



Powering Business Worldwide



Material of Construction	Plastic
Shipping Dimensions (hwd / in.)	8.90 x 5.60 x 2.50
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	3.500 x 1.000 x 2.750
Unit Packaging Type	Clamshell
Unit Weight (lbs.)	0.2
Unit Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Relative Humidity	0% to 90 RH, Non-Condensing
BTUs	8.5 BTU/Hr
FEATURES & SPECIFICATIONS	
Over Current Protection	Yes
USB Hub Ports	Yes
Number of USB Hub Ports	7
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
External Power Supply Certifications	FCC; UL; cUL; RoHS
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.