

4-Port Industrial-Grade USB 2.0 Hub - 15kV ESD Immunity, Metal Case, Mountable

MODEL NUMBER: **U223-004-IND**



Heavy-duty USB 2.0 hub for industrial applications.

Description

Tripp Lite's U223-004-IND is a rugged, all metal constructed USB 4-Port hub for use in data centers, work areas, and Industrial applications. Can be mounted on a wall or din-rail with included mounting hardware. Supports Hi-Speed USB 2.0 transfer rates at 480mbps, but is also backward compatible to USB 1.1 (12mbps). Hub is bus-powered through the computer connection, or can self power with an external adapter (not included) or via the included 3-wire terminal block connector (9-36V).

Features

- Industrial-grade, rugged all metal 4-port USB hub
- Supports USB 1.1 and 2.0 transfer speeds (12 - 480mbps)
- Wall or Din Rail mountable - hardware included
- Bus Powered or optional 3-Wire DC Terminal Block
- Over-current detection and protection circuit design
- ESD protected to $\pm 15kV$
- Automatic link and speed detection
- Plug-and-Play; no software or drivers
- Compatible with all major operating systems

Specifications

OVERVIEW	
UPC Code	037332174284

Highlights

- Industrial-grade, rugged metal enclosure
- ESD Protected to $\pm 15 kV$
- USB 2.0 Compliant - 480Mbps
- Compatible with all major operating systems

System Requirements

- Compatible with all major operating systems

Package Includes

- U223-004-IND
- 6ft USB cable x 1
- 3-pin power terminal block
- DIN rail mounting hardware
- Wallmount hardware



Over Current Protection	Yes
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 9.5mm, Positive Pin, Negative Sleeve
Bus Powered	Yes
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.00 x 6.30 x 9.10
Shipping Dimensions (hwd / cm)	7.62 x 16.00 x 23.11
Shipping Weight (lbs.)	1.40
Shipping Weight (kg)	0.64
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	1 x 5.6 x 2.5
Unit Weight (lbs.)	1
Unit Weight (kg)	0.45
Material of Construction	Iron
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 to 140 F (0 to 60 C)
Storage Temperature Range	14 to 176 F (-10 to 80 C)
Relative Humidity	5% to 95% RH, Non-Condensing
BTUs	8.5 BTU/Hr
Power Consumption (Watts)	2.5
Power Provided to Connected Device(s)	5V 0.5A (2.5W) Output per USB Port
CONNECTIONS	
Ports	4
Side A - Connector 1	USB B (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Driver Required	No
Technology	USB 2.0 (High Speed); USB
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>