

10-Port USB Charging Station with Storage Brackets - 6 USB-C and 4 USB-A Ports, 120W USB Charger Output

MODEL NUMBER: U280-010-ST6C4A



Charges up to 10 tablets, smartphones and other compatible devices with 120W charging output simultaneously

Features

Charges Up to 10 Devices at Once

Whether you're at home, in the office, or managing a busy retail or medical environment, the U280-010-ST6C4A keeps your devices powered and organized. With 10 total ports, including 6 USB-C and 4 USB-A, you can charge smartphones, tablets, e-readers, POS systems, and more at the same time.

Designed for High-Demand Environments

This charging hub is ideal for homes, classrooms, clinics, and retail counters where multiple devices are in constant use. Simply plug it into any standard AC outlet and you're ready to charge. No computer is required.

Fast, Safe, and Powerful Charging

Keep all your devices powered with 120 watts of total output. Each USB-C port supports up to 30 watts and each USB-A port supports up to 18 watts for fast and efficient charging. Built-in protections help prevent overheating, overcharging, and power surges to keep your devices safe.

Stay Organized with Built-In Storage Brackets

Avoid tangled cords and cluttered desks. The integrated dividers hold your devices upright and separated while they charge, making this a smart solution for shared spaces.

Portable and Easy to Use

Compact and lightweight, this desktop charging station is easy to move and set up wherever you need it. Just bring your own cables and plug into any wall outlet.

Highlights

- Charges up to 10 devices at once with 6 USB-C and 4 USB-A ports, including smartphones, tablets, and more
- Perfect for high-demand environments like retail, healthcare, and classrooms where devices are always in use
- Built-in safety features protect your devices from overheating, overcharging, and power surges
- Integrated storage brackets keep devices upright, separated, and organized to avoid tangled cables and clutter
- Plugs into any available AC outlet for fast, efficient device charging

Package Includes

- U280-010-ST6C4A 10-Port USB Charging Station
- External power supply (Input: 100–240V, 50/60 Hz, 2.5A Max; Output: 21V 7.1A) with NEMA 5-15P plug and 4 ft. cord
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332291226
Product Type	Charging Station
Charging Form Factor	Charging Hub



Powering Business Worldwide

TRIPP LITE
SERIES

Charger Functions	Charge
Device Compatibility	Amazon Kindle; Headphones; Phone; Tablet; Video Game System; Watch
Technology	USB
Country/Region	North America
Host Connector	USB C (FEMALE)
Device Slots	10
INPUT	
AC Power Adapter Plug(s)	NEMA 5-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 3A
AC Power Adapter Output Specs (V / A)	21V / 7.1A
AC Power Adapter Cord Length (ft.)	3.94
AC Power Adapter Cord Length (m)	1
Nominal Input Voltage(s) Supported	21V DC
Maximum Input Amps	1
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50/60 Hz
Input Plug Type	DC Plug (Barrel type)
Input Current	100-240V, 2.4A (Max)
OUTPUT	
Output (Watts)	USB-A: 18W (Max); USB-C: 30W (Max)
Overload Protection	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
Power Source Type	AC Adapter
DC Barrel Plug	OD: 4.5 x 0.6 x 10.5mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	34.00
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0
CONNECTIONS	
Number of Ports	10



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	(6) USB C (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
CHARGING	
Number of Charging Ports	10
Total Charging Amps	4.8
Total Charging Watts	120
Charging Method	USB
Charging Port Type	(4) USB A (FEMALE); (6) USB C (FEMALE)
Charging Ports	(4) USB-A: 5V 3.6A (18W); (6) USB-C: 30W (15V 2A) Power Delivery (PD 3.0)
Charging Ports Details	The following charging outputs are supported: Single Port Output: USB-C1/C2/C3/C4/C5/C6 = PD Charging 5.0V/3A (15W); 9V/3A (27W); 15V/2A (30W)USB-A1/A2 = QC 3.0 Charging 3.6-6V/3A, 6.0-9.0V/2A, 9.0-12V/1.5A (18W Max)USB-A3/A4 = 5V/2.4A (12W) Multiple Ports Output: USB-C1/C2 + USB-C3/C4 + USB-C5/C6 + USB-A1/A2 + USB-A3/A4 = 30W + 30W + 18W + 12WUSB-C1 + C2 = 5V/4.8A (24W Max); USB-C3 + C4 = 5V/4.8A (24W Max); USB-C5 + C6 = 5V/4.8A (24W Max)USB-A1 + A2 = 5V/3.6A (18W Max); USB-A3 + A4 = 5V/2.4A (12W)
Magnetic Charging	No
Wireless Charging	No
Overcharge Protection	Yes
Compatible Devices	Smartphone; Tablet; Video Game Console
PHYSICAL	
Color	Black
Material of Construction	PC + ABS
Plug Color	Black
Charging Station Form Factor	Charging Hub
Power Cord Color	Black
Total Number of Ports	10
Shipping Dimensions (hwd / in.)	2.87 x 13.50 x 6.69
Shipping Dimensions (hwd / cm)	7.29 x 34.29 x 16.99
Shipping Weight (lbs.)	1.01
Shipping Weight (kg)	0.46
Unit Dimensions (hwd / in.)	0.984 x 9.370 x 5.276
Unit Dimensions (hwd / cm)	6.72 x 21.0 x 14.0
Unit Dimensions (hwd / mm)	67.2 x 210 x 140
Unit Packaging Type	Box
Unit Weight (lbs.)	1.014



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (kg)	0.46
ENVIRONMENTAL	
Operating Temperature Range	32° to 86°F (0° to 30°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	30% to 90% RH (NON-CONDENSING)
Storage Humidity Range	10% to 90% RH (NON-CONDENSING)
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Quick Charge Compliant	3.0
IP68 Rated	No
IP20 Rated	No
Driver Required	No
Qi Compliant	No
Over Temperature Protection	Yes
STANDARDS & COMPLIANCE	
External Power Supply Certifications	DOE; FCC; UL; WEEE; cUL
Product Certifications	CAN/CSA-C22.2 No. 62368-1 (Canada); ICES (Canada); UL 62368-1
Product Compliance	FCC Part 15 Class B (USA); ICES-003 Issue 7; RoHS; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.