


Protect It! 8-Outlet Home Computer Surge Protector, 8 ft. (2.43 m) Cord, 1080 Joules, Child Safety Covers

MODEL NUMBER: **SUPER8**



Highlights

- 8 outlets / 8-ft. (2.43 m) cord
- 1080 joule rating

Package Includes

- SUPER8 Surge Suppressor
- Child Safety Covers
- Color-coded cord identifiers
- Warranty information and Instruction manual

Description

The SUPER8 Surge Suppressor from Tripp Lite has 8 outlets and an 8-ft. (2.43 m) cord with a space-saving right-angle plug. The unit has 1080 joules of surge energy absorption to handle the strongest surges. Diagnostic LEDs alert the user to potential power problems. \$35,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico Only). The SUPER8 comes with child safety covers and color-coded cord identifiers.

Features

- 8 outlets with child safety covers
- 8-ft. (2.43 m) cord with space-saving right-angle plug
- \$35,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Surge energy absorption: 1080 joules; 54,500 amps
- 15 amp circuit breaker
- 3 diagnostic LEDs indicate AC present, line fault & protection present
- EMI/RFI noise filtering
- Keyhole supports for wall mounting
- Recessed and lighted power switch
- Color-coded cord identifiers

Specifications

OVERVIEW	
UPC Code	037332010018



INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position red illuminated on/off power switch
Diagnostic LED Details	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
AC Suppression Surge Current Rating	54,500 amps
UL1449 Let Through Rating	400V - UL Verified
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No



Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Light Gray
Material of Construction	Plastic
Antimicrobial	No
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Receptacle Color	Light gray
Shipping Dimensions (hwd / cm)	36.83 x 13.97 x 4.44
Shipping Dimensions (hwd / in.)	14.50 x 5.50 x 1.75
Shipping Weight (kg)	0.91
Shipping Weight (lbs.)	2.00
Unit Dimensions (hwd / cm)	33 x 7 x 4.45
Unit Dimensions (hwd / in.)	13 x 2.75 x 1.75
Unit Weight (kg)	0.79
Unit Weight (lbs.)	1.75
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Canada	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$35,000 Ultimate Lifetime Insurance