

## USB 3.0 SuperSpeed Active Extension Repeater Cable (USB-A M/F), 15M (49.21 ft.)

MODEL NUMBER: U330-15M



Connects to any computer, device and/or cable with USB-A connectors to increase the length of a device cable with no decrease in signal or performance. Extends beyond the 10 ft. limit of conventional USB 3.0 cables.

### Description

This U330-15M USB 3.0 SuperSpeed Active Extension Repeater Cable (M/F) increases the length of a device cable up to 49 feet (15 meters) with no worry of signal loss. By daisy-chaining two cables, you can extend the length between USB devices up to 98 feet (30 meters). Connect the male plug to a USB port on your computer or hub and the female end to a USB device cable. A built-in bus-powered signal booster ensures peak performance. Backward compatible with previous USB generations, this cable supports data transfer rates up to 5 Gbps.

The U330-15M works with all computers, devices and cables with USB-A connectors, and provides up to 388mA of power to a connected device (a 5V 2A external power supply is required for power applications stronger than 388mA). Premium foil and braid shielding delivers top-of-the-line signal quality and protection from EMI/RFI interference. Nickel-plated USB connectors with gold-plated copper contacts ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time.

### Features

#### Extends Connections Between 2 USB-A Devices and/or Cables

- Increases length of device cable up to 49-ft. (14.93 m)
- Daisy-chain 2 cables for maximum distance up to 98-ft. (29.87 m)
- Supports data transfer rates up to 5 Gbps
- Built-in bus-powered signal booster for peak performance
- Provides up to 388mA of power to connected device
- Backward compatible with previous USB generations

#### Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding protects against EMI/RFI
- Nickel-plated connectors with gold-plated copper contacts ensure excellent conductivity
- Works with all computers, devices and cables with USB-A connectors
- 5V, 2A external power supply required for power applications stronger than 388mA

### Highlights

- Daisy-chain 2 cables for max distance up to 98-ft. (29.87 m)
- Supports data transfer rates up to 5 Gbps
- Built-in signal booster for peak performance
- Provides up to 388mA of power to connected device
- Backward compatible with previous USB generations

### System Requirements

- USB 3.0 computer port and USB 3.0 device required to meet USB 3.0 speeds
- 5V, 2A power supply with 3.5 x 1.35 mm DC jack required for power applications above 388mA. Output plug requires positive tip and negative sleeve.

### Package Includes

- U330-15M USB 3.0 SuperSpeed Active Extension Repeater Cable (M/F), 15 m



Powering Business Worldwide



## Specifications

OVERVIEW	
UPC Code	037332199706
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	49.2
Cable Length (m)	15.00
Shipping Dimensions (hwd / in.)	17.00 x 14.30 x 0.50
Shipping Dimensions (hwd / cm)	43.18 x 36.32 x 1.27
Shipping Weight (lbs.)	2.30
Shipping Weight (kg)	1.04
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.