

## USB 3.0 SuperSpeed to SATA/IDE Adapter with Built-In USB Cable, 2.5 in., 3.5 in. and 5.25 in. Hard Drives

MODEL NUMBER: **U338-06N**



Connects a 2.5, 3.5 or 5.25 in. SATA or IDE (PATA) hard drive to your laptop or computer's USB port for extra storage, quick disk formatting and fast data transfer.

### Description

The U338-06N USB 3.0 SuperSpeed to SATA/IDE Adapter connects a 2.5-, 3.5- or 5.25-inch SATA or IDE hard drive to an available USB port on your laptop or computer. This lets you back up important data, retrieve data from an old hard drive, or store information on an external drive that you can take with you to another computer.

This adapter with built-in USB cable supports USB 3.0 data transfer rates up to 5 Gbps. Perfect for storing and sharing large files, such as music and video files, the U338-06N is compatible with SATA and IDE drives up to 4 TB. It features 40- and 44-pin IDE ports, as well as 7-pin SATA data and 15-pin SATA power (via adapter cable) connectors. Necessary SATA and Molex cables are included.

LEDs indicate a successful connection. The U338-06N accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives, as well as USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds. It supports USB Mass Storage Class Bulk-Only Transport. No software or drivers are required. Compatible with all USB-enabled operating systems.

### Features

#### Quickly Connects a SATA and/or IDE Drive to Your Computer's USB Port

- Recommended for backing up, retrieving and storing large data files
- LEDs indicate successful connection
- Built-in USB 3.0 cable supports data transfer rates up to 5 Gbps
- Backward compatible with previous USB generations

### Highlights

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Compatible with SATA and IDE hard drives up to 4 TB
- Backward compatible with earlier USB generations
- Plug-and-play—no external power supply required
- Compatible with all USB-enabled operating systems

### System Requirements

- Any USB-enabled operating system
- Available USB port (USB 3.0 required to achieve USB 3.0 speeds)
- 2.5 in., 3.5 in. or 5.25 in. SATA or IDE drive

### Package Includes

- U338-06N USB 3.0 SuperSpeed to SATA/IDE Adapter
- 7-pin SATA data cable
- 15-pin SATA power cable
- 4-pin Molex power cable
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 12V, 2A)
- Power supply adapter
- Owner's manual



#### Compatible with 2.5 in., 3.5 in. and 5.25 in. SATA and IDE Drives Up to 4 TB

- Accepts SATA III, SATA II and SATA I drives
- Features 40-pin and 44-pin IDE connectors and 7-pin SATA data and 15-pin SATA power (via adapter cable) connectors
- Supports USB Mass Storage Class Bulk-Only Transport

#### Easy to Use

- Plug-and-play—no software or drivers needed
- Compatible with all USB-enabled operating systems
- SATA and Molex cables included

## Specifications

OVERVIEW	
UPC Code	037332199744
AC Adapter	Input: 100-240V, 50/60Hz, 0.6A; Output: 12V, 2A
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
External Power Supply Output Specs (V / A)	12V / 2A
External Power Supply Cord Length (ft.)	4.9
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	NEMA 1-15P North America
External Power Supply Certifications	FCC; UL; cUL; RoHS
Bus Powered	No
Product Length (in.)	21.6
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Read, Write, Power)
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black



Material of Construction	ABS
Shipping Dimensions (hwd / cm)	4.83 x 13.21 x 17.02
Shipping Dimensions (hwd / in.)	1.90 x 5.20 x 6.70
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
Unit Dimensions (hwd / cm)	1.4 x 6.3 x 4.2
Unit Dimensions (hwd / in.)	0.55 x 2.5 x 1.7
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.08
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	50 to 122 F (10 to 50 C)
Storage Temperature Range	32 to 149 F (0 to 65 C)
Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	81.9 BTU/Hr
Power Consumption (Watts)	24
<b>CONNECTIONS</b>	
Ports	3
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	7 PIN SATA (MALE)
Side B - Connector 2	40 POS. SOCKET (FEMALE)
Side B - Connector 3	44 Header IDC (Female)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Technology	USB 3.0 (SuperSpeed); SATA/eSATA; USB
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>