

Note: The cloning function will not work if the U339-004 is connected to a computer or any other source via a USB cable.

4-Bay USB 3.2 Gen1/eSATA to SATA Docking Station with Cloning, 2.5 in. to 3.5 in. SATA Hard Drives

MODEL NUMBER: **U339-004**



Connects up to four 2.5 in. or 3.5 in. SATA HDD or SSD to your laptop or computer's USB or eSATA port for extra storage, quick disk formatting and fast data transfer.

Description

The U339-004 4-Bay USB 3.2 Gen1/eSATA to SATA Docking Station connects up to four 2.5- or 3.5-inch SATA hard disk drives (HDD) or solid state drives (SSD) to an available USB or eSATA port on your laptop or computer. This lets you back up important data, retrieve data from an old hard drive, or store information on an external drive that you can take with you to another computer.

Not only can you quickly access hard drive content without time-consuming internal installation, you can also clone a drive to as many as three others simultaneously. Cloning does not require the U339-004 to be connected to a host computer. Just insert the master drive into the master bay, insert the slave drive(s) into the slave bay(s), and press the Clone button twice. Red LEDs monitor cloning progress. The U339-004 accepts 2.5- and 3.5-inch SATA III, II and I hard drives up to 6 TB and will work with larger drives as they become available.

This docking station supports USB 3.2 Gen1 data transfer rates up to 5 Gbps, as well as eSATA rates up to 6 Gbps. Its UASP (USB Attached SCSI Protocol) feature reduces latency and allows the cable to perform up to 70% faster when connected to a UASP-enabled host controller.

The U339-004 requires no software or drivers. It's compatible with all USB- and/or eSATA-enabled operating systems and backward-compatible with previous USB generations.

Features

Connects Up to 4 SATA Drives to Your Computer's USB or eSATA Port

- Recommended for backing up, retrieving and storing large data files
- Supports USB 3.2 Gen1 data transfer rates up to 5 Gbps
- Supports eSATA data transfer rates up to 6 Gbps
- Features UASP for performance up to 70% faster when connected to UASP-enabled host controller

Provides Offline Disk Cloning

- Duplicates a hard drive on up to 3 others simultaneously
- Offline cloning requires no computer connection

Compatible with 2.5 in. and 3.5 in. SATA HDDs and SSDs Up to 6 TB

Highlights

- Supports USB 3.2 Gen1 data transfer rates up to 5 Gbps
- Supports eSATA data transfer rates up to 6 Gbps
- Compatible with SATA HDDs and SSDs up to 6 TB
- Works with all USB/eSATA-enabled operating systems
- Offline cloning requires no computer connection

System Requirements

- Any USB- and/or eSATA-enabled operating system (cloning functionality will not work if the U339-004 is connected to a computer)
- Available USB or eSATA port (USB 3.2 Gen1 required to achieve USB 3.2 Gen1 speeds. SATA III eSATA port required to achieve eSATA speeds.)
- 2.5 in. or 3.5 in. SATA drive
- UASP-enabled host controller required for UASP performance

Package Includes

- U339-004 4-Bay USB 3.2 Gen1/eSATA to SATA Docking Station
- USB 3.2 Gen1 cable, 2.5 ft.
- eSATA cable, 2 ft.
- External power supply w/NEMA 1-15P plug (Input: 100–240V, 50/60 Hz, 1.2A; Output: 12V, 5A)
- Owner's manual



- Accepts SATA III, SATA II and SATA I drives
- Backward-compatible with previous USB generations
- Will work with larger SATA drives as they become available

Easy to Use

- Plug-and-play—no software or drivers
- No time-consuming internal installation required
- Compatible with all USB- and/or eSATA-enabled operating systems
- USB 3.2 Gen1 and eSATA cables included

Specifications

OVERVIEW	
UPC Code	037332198709
AC Adapter	Input: 100-240V, 50/60Hz, 1.2A; Output: 12V, 5A
Technology	SATA/eSATA
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
Bus Powered	No
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.5A
External Power Supply Output Specs (V / A)	12V / 5A
External Power Supply Cord Length (ft.)	4.9
External Power Supply Cord Length (m.)	1.5
DC Barrel Plug	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CE; FCC; UL; PSE; GS; RoHS; China RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Read, Write, Power); Green (Clone)
PHYSICAL	
Color	Black
Material of Construction	ABS, Steel
Shipping Dimensions (hwd / cm)	7.11 x 17.02 x 24.38
Shipping Dimensions (hwd / in.)	2.80 x 6.70 x 9.60



Shipping Weight (kg)	1.09
Shipping Weight (lbs.)	2.40
Unit Dimensions (hwd / in.)	2.6 x 6.5 x 5
Unit Dimensions (hwd / cm)	6.5 x 16.5 x 12.7
Unit Packaging Type	Box
Unit Weight (lbs.)	1
Unit Weight (kg)	0.45
ENVIRONMENTAL	
Operating Temperature Range	50 to 122 F (10 to 50 C)
Storage Temperature Range	32 to 149 F (0 to 65 C)
Relative Humidity	10% to 80% RH, Non-Condensing
BTUs	204.7 BTU/Hr
Power Consumption (Watts)	60
CONNECTIONS	
Ports	4
Side A - Connector 1	7 PIN ESATA (MALE); USB A (MALE)
Side B - Connector 1	(4) 22 PIN SATA + POWER (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
UASP Support	Yes
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>