

USB 3.0 Docking Station for Microsoft Surface and Surface Pro, USB-A, HDMI and Gigabit Ethernet Ports, 4K UHD

MODEL NUMBER: U342-HGU3



Adds 3 USB 3.0 ports, an RJ45 Gigabit Ethernet jack and an external HDMI 4K monitor to your Microsoft Surface or Surface Pro. Recommended for transferring data, accessing printers and scanners, or watching movies.

Description

The U342-HGU3 USB 3.0 Docking Station expands the capabilities of your Microsoft® Surface® or Surface Pro by adding Gigabit Ethernet access, a 4K-enabled HDMI monitor, and up to three USB peripherals, such as a printer, scanner and external hard drive. It's compatible with all Surface models and versions. Its built-in stretching bracket allows it to fit perfectly on the Surface kickstand. No software or drivers are needed.

Access a 10/100/1000 Mbps wired network without an internal Ethernet card. The RJ45 Gigabit Ethernet connection complies with IEEE 802.3, 802.3u and 802.3ab standards and supports IEEE 802.3az Energy Efficient Ethernet, as well as full- and half-duplex operations, Wake-on-LAN, jumbo frames, VLAN tagging and auto-MDIX. It also supports Checksum Offload Engine (COE) to reduce CPU loading.

The USB 3.0 ports achieve data transfer speeds up to 5 Gbps without compromising signal quality. They're backward compatible with previous USB generations.

You can also stream movies, video games and other video content from your Surface device to a larger 4K-enabled television or monitor. Just connect the included Mini DisplayPort™ cable between the U342-HGU3's Mini DisplayPort and your Surface. Then connect an HDMI cable (sold separately) between the U342-HGU3 and the television or monitor to see UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/25/30Hz.

Features

Highlights

- Supports HDMI video resolutions up to 3840 x 2160 (4K x 2K) @ 24/25/30Hz
- Supports data transfer rates up to 5 Gbps
- Ensures true 10/100/1000 Mbps Ethernet network speeds
- Fits perfectly on Surface kickstand
- Plug and play with no software or drivers needed

System Requirements

- Any model Microsoft Surface or Surface Pro

Package Includes

- U342-HGU3 USB 3.0 Docking Station
- Mini DisplayPort cable, 7 in.
- External Power Supply with 1-15P Plug (Input: 100–240V, 50/60 Hz, 0.4A Max; Output: 5V, 2A)
- Owner's manual



Compatible with All Surface Models and Versions

- Plug and play with no software or drivers needed
- Fits perfectly on Surface kickstand
- Recommended for accessing a Gigabit Ethernet LAN, transferring data, watching videos or connecting a printer or scanner

Add Up to 3 USB-A Devices to Your Surface

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Backward compatible with previous USB generations

Join a Wired Gigabit Ethernet Network

- Ensures true 10/100/1000 Mbps Ethernet network speeds
- Complies with IEEE 802.3, 802.3u, 802.3ab and 802.3az standards
- Supports full- and half-duplex, Wake-on-LAN, jumbo frames, VLAN tagging and auto-MDIX
- Supports IPv4/IPv6 COE to reduce CPU loading

Watch 4K Content on a Larger Screen

- Supports HDMI video resolutions up to 3840 x 2160 (4K x 2K) @ 24/25/30Hz
- Mini DisplayPort cable included
- HDMI cable sold separately

Specifications

OVERVIEW	
UPC Code	037332198501
AC Adapter	Input: 100V-240V, 50/60Hz, 0.4A Max Output: 5V 2A
Technology	USB 3.0 (SuperSpeed)
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
Bus Powered	No
Product Length (ft.)	1.5
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.4A
External Power Supply Output Specs (V / A)	5V / 2A



External Power Supply Cord Length (ft.)	5.0
External Power Supply DC Barrel Connector Specs	OD: 3.5 x 1.35 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; UL; cUL; RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Link); Yellow (Activity)
PHYSICAL	
Cable Jacket Rating	VW-1
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / cm)	4.32 x 10.92 x 27.69
Shipping Dimensions (hwd / in.)	1.70 x 4.30 x 10.90
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
Unit Dimensions (hwd / in.)	1 x 8.8 x 1.3
Unit Packaging Type	Box
Unit Weight (kg)	0.16
Unit Weight (lbs.)	0.35
ENVIRONMENTAL	
Operating Temperature Range	-4 to 158 F (-20 to 70 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	6.4 BTU/Hr
Power Consumption (Watts)	1.9
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output per USB Port
COMMUNICATIONS	
Network Speed	1Gbps
IEEE Standards Supported	802.3; 802.3u; 802.3ab; 802.3az
CONNECTIONS	
Ports	6
PC/Server Connections	USB
Side A - Connector 1	USB 3.0 A (MALE)



Side A - Connector 2	MINI DISPLAYPORT (MALE)
Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	HDMI (FEMALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	4K x 2K (3840 x 2160) @30Hz
Displayport Specification	1.2
HDMI Specification	1.4b
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>