


USB-C to Gigabit Network Adapter with Right Angle USB-C, Thunderbolt 3 Compatibility - White

MODEL NUMBER: U436-06N-GBW-RA



Connects the USB-C or Thunderbolt 3 port on your computer, laptop, MacBook, Chromebook or tablet to a wired Gigabit Ethernet network.

Features

USB-C to Gigabit Ethernet Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 Port This USB Type-C to Gigabit Ethernet NIC Network Adapter (M/F) allows your computer, tablet, laptop, notebook, MacBook, Chromebook, Ultrabook or smartphone to connect to a wired Ethernet network. Connect the right-angle USB-C connector to your device's USB-C or Thunderbolt 3 port, and connect the RJ45 port to a UTP cable (such as N201-Series, sold separately). Ideal for settings in which no Wi-Fi is available or when a wired connection offers faster speeds, this USB 3.1 Gen 1 adapter lets you enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers and audio/video streaming.

Built-In USB-C Cable Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Right-Angle USB-C Plug Makes Connecting in Tight Spaces Easier The space-saving right-angle USB-C plug is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Ready to Use Right Out of the Package The plug-and-play network adapter requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go. Plug it into your laptop for instant network connection.

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332214157 |
| INPUT | |

Highlights

- Connect to a wired 10/100/1000 Mbps network where Wi-Fi is weak or unavailable
- More convenient, less expensive than installing or upgrading an internal Ethernet card
- Widely compatible with Windows, Mac and Chromium operating systems
- Right-angle USB-C plug allows easier connection in confined or hard-to-reach spaces
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your MacBook or download data from the Ethernet at true 10/100/1000 Mbps speeds

System Requirements

- Laptop or computer with an available USB-C port
- Ethernet network and a Cat6 cable to connect to it.

Package Includes

- U436-06N-GBW-RA Right-Angle USB-C to Gigabit Ethernet Network Adapter (M/F), White
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--|--|
| Built-In Cable Length (ft.) | 0.328 |
| Built-In Cable Length (m) | 0.1 |
| Built-In Cable Length (in.) | 3.94 |
| Bus Powered | Yes |
| Product Length (in.) | 6 |
| Product Length (cm.) | 15.24 |
| Product Length (ft.) | 0.5 |
| Product Length (m) | 0.15 |
| BATTERY | |
| Battery Charging (5V/1.5A Port) | No |
| CONNECTIONS | |
| Number of Ports | 1 |
| Side A - Connector 1 | USB C (MALE) - RIGHT ANGLE |
| Side B - Connector 1 | RJ45 (FEMALE) |
| Connector Plating | Nickel |
| Contact Plating | Gold |
| USER INTERFACE, ALERTS & CONTROLS | |
| LED Indicators | Network cable connected = Green; Data transmitting = Green |
| PHYSICAL | |
| Color | White |
| Material of Construction | ABS, PVC |
| Cable Jacket Rating | VW-1 |
| Unit Dimensions (hwd / in.) | 0.630 x 6.000 x 1.060 |
| Unit Dimensions (hwd / mm) | 16 x 150 x 27 |
| Unit Packaging Type | Box |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 113°F (0° to 45°C) |
| Storage Temperature Range | 14° to 176°F (-10° to 80°C) |
| Operating Humidity Range | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range | 5% to 90% RH, Non-Condensing |
| COMMUNICATIONS | |
| Network Compatibility | 1 Gbps (Gigabit) |



Powering Business Worldwide

TRIPP LITE
SERIES

| FEATURES & SPECIFICATIONS | |
|-------------------------------------|-------------------------------------|
| USB Specification | USB 3.1 Gen 1 (up to 5 Gbps) |
| Driver Required | No |
| Recommended Category Cable | Cat6 Cables |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.