

USB-C to 3.5 mm Headphone Jack Adapter Cable (M/M), 3 ft. (0.9 m)

MODEL NUMBER: U437-MM1-03



Adapter cable connects a microphone or stereo headphones to the USB-C port on your MacBook Pro, Windows laptop or Chromebook.

Features

3.5 mm Audio Adapter Cable Connects to Your Laptop's USB-C or Thunderbolt 3 Port

Most current USB-C devices, such as Windows laptops, Chromebooks and MacBook Pros, rely on Bluetooth technology for audio and do not come with a 3.5 mm stereo audio jack. The U437-MM1-03 lets you connect a microphone, earbuds, headphones or speakers directly to your laptop or tablet's USB-C port. You can also use this adapter cable to bypass a defective sound card or audio jack on an older device. It's ideal for streaming audio, playing music or listening to your favorite podcasts.

Supports High-Fidelity Stereo Audio Formats

This stereo DAC (Digital-to-Analog Converter) supports 94 dB SNR for audio output and 44.1/48/88.2/96/192 KHz sample rate (16/24-bit). The 3.5 mm audio plug supports max 192 KHz/16-bit and 96 kHz/24-bit sample rates that are ideal for listening to music or streaming.

Ready to Use Right Out of the Package

The three-foot (0.9-meter) audio adapter is plug-and-play, so it requires no software or external power. The cable fits easily into a pocket, purse, backpack, briefcase or laptop bag for connecting on the go. It is compatible with Android, Windows and macOS operating systems, including iPads with a USB-C port.

Specifications

OVERVIEW	
UPC Code	037332300652
Product Type	Passive Cable
Device Compatibility	Chromebook; Computer; Headphones; Laptop; Phone; Tablet; Video Game System
Technology	Stereo Audio; USB
Country/Region	Global
Host Connector	USB C (MALE)

Highlights

- Connects USB-C devices to headphones, speakers or audio systems with a 3.5 mm jack
- Lets you bypass a defective sound card or audio jack on an older USB-C device
- Supports clear, distortion-free, high-fidelity audio for music, calls and streaming
- 3 ft. cable fits into a backpack or laptop bag for convenient listening anywhere
- Compatible with Android, Windows and macOS, including iPads with USB-C port

System Requirements

- Microphone, headphones, earbuds and/or speakers with 3.5 mm plug
- Android, Windows or macOS (including iPad with USB-C port)

Package Includes

- U437-MM1-03 USB-C to 3.5 mm Headphone Jack Adapter, M/M, 3 ft. (0.9 m)
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Type	Passive
AUDIO	
Audio Ports	3.5MM (MALE)
Audio Ports Details	Supports stereo digital-to-analog converter with 94dB SNR for audio outputDAC supports 44.1/48/88.2/96/192KHz Sample Rate, 16/24-Bit3.5mm Audio plug supports max 192KHz/16-bit and 96KHz/24-bit sampling rate3-Pole 3.5mm Audio Jack for Fixed-Type/Global/Universal Audio Jack designReversible connection
Audio Input	USB-C
Audio Output	3.5mm
Audio Specification	DAC Supports 44.1/48/88.2/96/192KHz Sample Rate, 16/24-bit; 3.5mm Audio plug supports max 192KHz/16-bit and 96KHz/24-bit Sampling Rate
INPUT	
Bus Powered	Yes
Product Length (in.)	36
Product Length (cm.)	91.5
Product Length (ft.)	3
Product Length (m)	0.9
Power Source	Bus
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
Power Source Type	Bus
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	3.5MM (MALE)
PHYSICAL	
Color	Black; Gray
Material of Construction	TPE + ALUMINUM
Cable Jacket Color	Black
Connector Color	Gray
Cable Jacket Material	TPE
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.0mm
Wire Gauge (AWG)	28
Cable Length (ft.)	3



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (m)	0.91
Cable Length (in.)	36
Cable Length (cm)	91.5
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
Unit Dimensions (hwd / in.)	0.510 x 1.100 x 1.810
Unit Dimensions (hwd / cm)	1.3 x 2.8 x 4.6
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.04
Unit Weight (kg)	0.02
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	20 ~ 80% RH
Operating Humidity Range	10% to 85% RH, NON-CONDENSING
Storage Humidity Range	5% to 90% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.