

1-Port USB 2.0 Desktop Extension Cable (M/F), 5 ft. (1.52 m)

MODEL NUMBER: U024-005-DSK1



Extends your desktop computer's existing USB-A port up to 5 ft. away. Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices.

Features

Extends an Existing USB-A Port an Extra 5 ft.

- Move a hard-to-reach USB port within easy access
- Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices
- Supports data transfer rates up to 480 Mbps
- Backward compatible with earlier USB generations

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors for optimal signal quality
- Integral strain relief for long life
- Flexible PVC jacket for easy installation in tight spaces
- Black padded non-sliding base

Specifications

OVERVIEW	
UPC Code	037332199331
Technology	USB; USB 2.0 (High Speed)
Cable Type	Passive
INPUT	
Maximum Input Amps	1

Highlights

- Supports data transfer rates up to 480 Mbps
- Premium foil and braid shielding
- Backward compatible with earlier USB generations
- Flexible PVC jacket for easy installation in tight spaces
- Black padded non-sliding base

System Requirements

- Computer, laptop or other device with USB-A port

Package Includes

- U024-005-DSK1 1-Port USB 2.0 Hi-Speed Desktop Extension Cable (M/F), 5 ft.



Powering Business Worldwide



CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
CHARGING	
Total Charging Watts	5
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5mm
Cable Length (ft.)	5
Cable Length (m)	1.52
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	14 to 131 F (-10 to 55 C)
Relative Humidity	5% to 90% RH, Non-Condensing
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	5W (5V/1A)
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Data Transfer Rate	480 Mbps
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.