


Safe-IT USB-A to USB Micro-B Antibacterial Cable (M/M), USB 2.0, White, 3-ft. (0.91 m)

MODEL NUMBER: **U050AB-003-WH**



USB cable with antibacterial properties connects mobile devices to your computer while helping to protect you from harmful bacteria.

Features

Durable USB-A to USB Micro-B Cable Transfers Important Data at USB 2.0 Speeds

This USB cable (M/M) connects a smartphone, GPS unit, digital camera or other USB Micro-B peripheral to the USB-A port on your computer, laptop or wall charger. It charges and powers your smartphone through its Micro-B port. It also transfers data at USB 2.0 speeds up to 480 Mbps for use with low-speed and high-speed devices, including multimedia applications. The cable is backward compatible with earlier USB generations.

Provides Extra Protection Against Certain Bacteria

The molded connectors and PVC jacket are constructed using an antibacterial material that is 99.9% effective in inhibiting Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this cable an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

Premium Construction for Superior Performance

Manufactured with twisted 28 AWG data lines and 28 AWG power lines, the U050AB-003-WH also features molded nickel-plated connectors for excellent conductivity. Integral strain relief gives the cable extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

White Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The cable has a white PVC jacket, which is easy to identify quickly in a crowded computer or hub and helps prevent the cable from becoming accidentally disconnected.

Highlights

- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Made with antibacterial material proven 99.9% effective in inhibiting E. coli and staph
- Foil and braid shielding protects against EMI/RFI noise that can distort or destroy data
- Molded nickel-plated connectors provide excellent conductivity
- White jacket permits fast, easy identification in a crowded hub or computer

Applications

- Connect a computer or laptop and a USB Micro-B peripheral in a home or office network
- Charge and sync your smartphone from a USB computer or wall charger
- Provide extra protection against bacteria to give cable installers and IT personnel peace of mind during installation

Package Includes

U050AB-003-WH USB-A to USB Micro-B Antibacterial Cable (M/M), White, 3-ft. (0.91 m)

Specifications

OVERVIEW	
UPC Code	037332260673
Technology	USB 2.0 (High Speed); USB
PHYSICAL	



Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.8mm
Wire Gauge (AWG)	28/28
Cable Length (ft.)	3
Cable Length (m)	0.9
Cable Length (in.)	36
Material of Construction	PVC
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
SPECIAL FEATURES	
Antibacterial	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>