

USB-A to RJ45 Serial Rollover Cable (M/M) - Cisco Compatible, 250 Kbps, 6 ft. (1.83 m), Gray

MODEL NUMBER: U209-006-RJ45-X



Connects your computer or laptop's USB port to your Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port.

Features

Connects Computer's USB Port to Cisco Device Connect computer or laptop to Cisco modem, router, firewall, switch or other serial-based Cisco device with a console port
Works with older and new Cisco models
6 ft. long

Top-of-the-Line Performance Supports data transfer rates up to 250 Kbps
Supports remote wake-up and power management
Utilizes FTDI chipset.

Premium Double Shielding Eliminates crosstalk and reduces EMI/RFI line noise that could negatively affect transfer speeds and data

Easy to Use No other cables or adapters needed
No external power required
Driver CD included (drivers also available online for download if your computer has no CD drive)

Highlights

- Supports data transfer rates up to 250 Kbps
- Supports remote wake-up and power management
- Double shielding reduces crosstalk and EMI/RFI line noise
- Compatible with Windows, Mac and Linux
- No cables, adapters or external power required

System Requirements

- Computer with available USB port
- Cisco device with available RJ45 console port
- Windows, Mac or Linux operating system

Package Includes

- U209-006-RJ45-X USB to RJ45 Cisco Serial Rollover Cable
- Driver CD
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332190017
Technology	USB
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
PHYSICAL	



Cable Jacket Material	PVC
Cable Outer Diameter (OD)	2.5 mm
Color	Gray
Material of Construction	PVC
Shipping Dimensions (hwd / cm)	3.05 x 11.94 x 10.41
Shipping Dimensions (hwd / in.)	1.20 x 4.70 x 4.10
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.24
Unit Packaging Type	Box
Unit Weight (kg)	0.11
Unit Weight (lbs.)	0.2425
Wire Gauge (AWG)	26
ENVIRONMENTAL	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	-4 to 140°F (-20 to 60°C)
Relative Humidity	0% to 90% RH (Non-Condensing)
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Plating	Gold
FEATURES & SPECIFICATIONS	
Driver Required	Yes
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>