

2-Port USB 2.0 Printer/Peripheral Sharing Switch

MODEL NUMBER: U215-002



Allows 2 computers to share one USB 2.0 peripheral, such as a printer, scanner or external hard drive, saving you money, space and time.

Description

The U215-002 2-Port USB 2.0 Hi-Speed Printer/Peripheral Sharing Switch saves you money, time and precious workspace by letting you connect two computers to a single USB peripheral. Recommended for home and small offices, this sharing switch eliminates the cost of buying two printers, two scanners, two hard drives, etc., as well as the problem of where to put them and their cables.

One-touch port switching lets you switch between computers using a mouse, hotkeys or manual pushbutton. Idle time-out switching ensures all data is sent from the active printer buffer before switching ports.

A taskbar icon indicates the connected device's status. LEDs on the unit indicate which computer currently controls the device. The U215-002 is compatible with USB 2.0 and USB 1.1 devices and supports data transfer rates up to 480 Mbps.

No external power supply required. Switch is compatible with all USB-enabled Operating Systems. Optional CD software is compatible with Windows (XP and later) and Mac (OS X 10.3 and later).

NOTE: Customers are encourage to use the 1.5 ft. USB cables provided between the source (e.g. PC) and switch. Using longer cables could cause an intermittent or connection loss.

Features

Connect 2 Computers to a Single USB Device

- Recommended for printers, scanners, hard drives and other USB peripherals
- Saves money, time and workspace
- Ideal for home and small offices
- Compatible with USB 2.0 and USB 1.1 peripherals
- Supports data transfer rates up to 480 Mbps

One-Touch Port Switching

- Switch between computers with mouse, hotkey or manual pushbutton
- All data sent from active printer buffer before switching ports
- Taskbar icon indicates device status
- LEDs indicate computer control

Easy Setup and Broad Compatibility

- Switch is compatible with all USB-enabled Operating Systems
- Optional software is compatible with Windows (XP and later) and Mac (OS X 10.3 and later)

Highlights

- Switch between computers via mouse, hotkey or manual button
- Supports data transfer rates up to 480 Mbps
- Easy setup with included optional software CD
- No power adapter required

System Requirements

- 1 or 2 computers with available USB ports
- Switch is compatible with all USB-enabled operating systems
- Optional software is compatible with Windows (XP and later) and Mac (OS X 10.3 and later)

Package Includes

- U215-002 2-Port USB 2.0 Hi-Speed Printer/Peripheral Sharing Switch
- (2) USB 2.0 cables (A/B), 1.5 ft.
- Installation CD
- Owner's manual

- No external power supply required

Specifications

OVERVIEW	
UPC Code	037332198631
Technology	USB 2.0 (High Speed)
Host Connector	USB A (MALE)
VIDEO	
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	USB A (FEMALE)
INPUT	
Bus Powered	Yes
POWER	
Power Consumption (Watts)	0.5
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	(2) USB B (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (1, 2)
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	1.50 x 4.40 x 3.74
Shipping Dimensions (hwd / cm)	3.81 x 11.18 x 9.50
Shipping Weight (lbs.)	0.26
Shipping Weight (kg)	0.12
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000



Powering Business Worldwide



Unit Packaging Type	Box
Unit Weight (lbs.)	0
Unit Weight (kg)	0.00
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 131°F (-10° to 55°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	1
USB Specification	USB 2.0 (up to 480 Mbps)
Port Selection	Pushbutton; Hotkey; Mouse
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.